

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Input solid-state relay, transmission frequency: 100 kHz, with LED and protective circuit in input and output circuits, input: 24 V DC, output: 4 - 30 V DC/50 mA

The illustration shows version DEK-OE- 5 DC/ 24 DC/100 KHZ

Why buy this product

- With capacitor on the input side for interference suppression
- ☑ Includes signal inputs on PLC counter boards



Key Commercial Data

Packing unit	10 STK
GTIN	4 017918 107413
GTIN	4017918107413
Weight per Piece (excluding packing)	20.980 g
Custom tariff number	85364190
Country of origin	China

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area	
Dimensions		

Dimensions

Width	6.2 mm
Height	80 mm
Depth	56 mm

Ambient conditions



Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C 60 °C
Ambient temperature (storage/transport)	-20 °C 70 °C

Input data

·	
Nominal input voltage U _N	24 V DC
Input voltage range in reference to U _N	0.8 1.2
Input voltage range	19.2 V DC 28.8 V DC
Switching threshold "0" signal in reference to U _N	≤ 0.4
Switching threshold "1" signal in reference to U _N	≥ 0.8
Typical input current at U _N	6 mA
Typical response time	1.5 µs
Typical turn-off time	2 μs
Operating voltage display	Yellow LED
Type of protection	Reverse polarity protection
	Surge protection
Protective circuit/component	Polarity protection diode
Transmission frequency	100 kHz
Power dissipation for nominal condition	3 mW

Output data

Output voltage range	4 V DC 30 V DC
Limiting continuous current	50 mA
Quiescent current	4.3 mA
Voltage drop at max. limiting continuous current	≤ 0.5 V DC
Output circuit	3-conductor, ground-referenced
Type of protection	Surge protection
Protective circuit/component	Suppressor diode

Connection data, input side

Connection name	Input side
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm² 4 mm²
Conductor cross section flexible	0.2 mm² 2.5 mm²
Conductor cross section AWG	24 12
Torque	0.5 Nm

Connection data, output side

Connection name	Output side
Connection method	Screw connection



Technical data

Connection data, output side

Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm² 4 mm²
Conductor cross section flexible	0.2 mm² 2.5 mm²
Conductor cross section AWG	24 12
Torque	0.5 Nm

General

Test voltage input/output	2.5 kV AC
Mounting position	any
Assembly instructions	In rows with zero spacing
Operating mode	100% operating factor
Standards/regulations	IEC 60664
	EN 50178
	IEC 62103
Rated surge voltage/insulation	Basic insulation
Degree of pollution	2
Overvoltage category	II

Standards and Regulations


Standards/regulations	IEC 60664
	EN 50178
	IEC 62103
Rated surge voltage/insulation	Basic insulation
Degree of pollution	2
Overvoltage category	Ш

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Circuit diagram





Classifications

eCl@ss

eCl@ss 5.1	27371001
eCl@ss 6.0	27371604
eCl@ss 7.0	27371604
eCl@ss 8.0	27371604
eCl@ss 9.0	27371604

ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504
ETIM 5.0	EC001504
ETIM 6.0	EC001504

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121542
UNSPSC 11	39121542
UNSPSC 12.01	39121542
UNSPSC 13.2	39122326

Approvals

Α	n	n	rc	Ì۷	ıa	ls

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC []

EAC-Zulassung



Accessories

Accessories

Insertion bridge

Insertion bridge - EB 2- DIK RD - 2716693



Insertion bridge, Pitch: 6.15 mm, Number of positions: 2, Color: red

Insertion bridge - EB 3- DIK RD - 2716745



Insertion bridge, Pitch: 6.15 mm, Number of positions: 3, Color: red

Insertion bridge - EB 4- DIK RD - 2716758



Insertion bridge, Pitch: 6.15 mm, Number of positions: 4, Color: red

Insertion bridge - EB 5- DIK RD - 2716761



Insertion bridge, Pitch: 6.15 mm, Number of positions: 5, Color: red

Insertion bridge - EB 10- DIK RD - 2716774



Insertion bridge, Pitch: 6.15 mm, Number of positions: 10, Color: red



Accessories

Insertion bridge - EB 2- DIK BU - 2716648



Insertion bridge, Pitch: 6.15 mm, Number of positions: 2, Color: blue

Insertion bridge - EB 3- DIK BU - 2716651



Insertion bridge, Pitch: 6.15 mm, Number of positions: 3, Color: blue

Insertion bridge - EB 4- DIK BU - 2716664



Insertion bridge, Pitch: 6.15 mm, Number of positions: 4, Color: blue

Insertion bridge - EB 5- DIK BU - 2716677



Insertion bridge, Pitch: 6.15 mm, Number of positions: 5, Color: blue

Insertion bridge - EB 10- DIK BU - 2716680



Insertion bridge, Pitch: 6.15 mm, Number of positions: 10, Color: blue



Accessories

Insertion bridge - EB 80- DIK BU - 2715940



Insertion bridge, Pitch: 6.2 mm, Number of positions: 80, Color: blue

Insertion bridge - EB 80- DIK RD - 2715953



Insertion bridge, Pitch: 6.2 mm, Number of positions: 80, Color: red

Insertion bridge - EB 80- DIK WH - 2715788



Insertion bridge, Pitch: 6.15 mm, Number of positions: 80, Color: white

Labeled terminal marker

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016



Zack marker strip, Strip, white, labeled, can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Partition plate

Separating plate - D-DEK 1,5 GN - 2716949



Cover for setting the end of a terminal row, color: green

Sensor/actuator terminal block



Accessories

Sensor/actuator terminal block - DIKD 1,5 - 2715979



Sensor/actuator terminal block, Connection type: Screw connection, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Terminal marking

Zack marker strip - ZB 6:UNBEDRUCKT - 1051003



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Zack marker strip - ZB 6/WH-100:UNBEDRUCKT - 5060935



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: $6.15 \times 10.5 \text{ mm}$

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com