


11700A2 Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, PVC inner jacket, rip cord, industrial grade PVC outer jacket. Sequential marking at two foot intervals.

Usage (Overall)

Suitable Applications:

Industrial Ethernet Cable, Harsh Environments, EtherNet/IP, 350MHz Enhanced Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, CMX - Outdoor, RJ-45 Compatible, Extra Protection, OIL RES I & II

Physical Characteristics (Overall)

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material | Dia. (in.) |
|---------|-----|-----------|--------------------|------------|
| 4 | 24 | Solid | BC - Bare Copper | .020 |

Total Number of Conductors: 8

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (in.) | Dia. (in.) |
|---------------------|----------------------|------------|
| PO - Polyolefin | .009 | .035 |

Inner Jacket

Inner Jacket Material:

| Inner Jacket Material | Nom. Dia. (in.) |
|--------------------------|-----------------|
| PVC - Polyvinyl Chloride | .200 |

Inner Jacket Ripcord: Yes

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material | Nom. Wall Thickness (in.) |
|---|---------------------------|
| Industrial Grade PVC - Polyvinyl Chloride | .035 |

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.285 in.

Pair

Pair Color Code Chart:

| Number | Color |
|--------|------------------------------|
| 1 | White/Blue Stripe & Blue |
| 2 | White/Orange Stripe & Orange |
| 3 | White/Green Stripe & Green |
| 4 | White/Brown Stripe & Brown |

Mechanical Characteristics (Overall)

Installation Temperature Range: +5°C To +75°C

Operating Temperature Range: -10°C To +75°C

Bulk Cable Weight: 35 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius/Minor Axis: 0.290 in.

11700A2 Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| | |
|---------------------------------------|--|
| NEC/(UL) Specification: | CMR, UL444 |
| CEC/C(UL) Specification: | CMR |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 01/01/2004 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| Other Specification: | NEMA WC-63.1 Category 5e, UL verified to Category 5e |

Applicable Patents:

| | |
|---------|------------------|
| Country | www.belden.com/p |
|---------|------------------|

Flame Test

| | |
|-----------------|--------------|
| UL Flame Test: | UL1666 Riser |
| CSA Flame Test: | FT4 |

Suitability

| | |
|------------------------|-----|
| Suitability - Indoor: | Yes |
| Suitability - Outdoor: | Yes |
| Sunlight Resistance: | Yes |
| Oil Resistance: | Yes |

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

| | |
|---------------------|----|
| Capacitance (pF/ft) | 15 |
|---------------------|----|

| | |
|---|----|
| Maximum Capacitance Unbalance (pF/100 m): | 66 |
|---|----|

Nominal Velocity of Propagation:

| | |
|--------|----|
| VP (%) | 70 |
|--------|----|

Maximum Delay:

| | |
|------------------|-----|
| Delay (ns/100 m) | 510 |
|------------------|-----|

Max. Delay Skew:

| | |
|-----------------------|----|
| Delay Skew (ns/100 m) | 25 |
|-----------------------|----|

Maximum Conductor DC Resistance:

| | |
|------------------------|---|
| DCR @ 20°C (Ohm/100 m) | 9 |
|------------------------|---|

Max. Operating Voltage - UL:

| | |
|---------|-----------|
| Voltage | 300 V RMS |
|---------|-----------|

Maximum DCR Unbalanced:

| | |
|--------------------------|---|
| DCR Unbalance @ 20°C (%) | 3 |
|--------------------------|---|

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

| Freq. (MHz) | Max. Attenuation (dB/100 m) | Min. NEXT (dB) | Min. PSNEXT (dB) | Min. ACR (dB) | Min. PSACR (dB) | Min RL (dB) |
|-------------|-----------------------------|----------------|------------------|---------------|-----------------|-------------|
| 1 | 2.0 | 65.3 | 65.3 | 63.3 | 63.3 | 20.0 |
| 4 | 4.0 | 56.3 | 56.3 | 52.3 | 52.3 | 23.0 |

11700A2 Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

| | | | | | | |
|-------|------|------|------|------|------|------|
| 8 | 5.7 | 51.8 | 51.8 | 46.1 | 46.1 | 24.5 |
| 10 | 6.4 | 50.3 | 50.3 | 43.9 | 43.9 | 25.0 |
| 16 | 8.1 | 47.3 | 47.3 | 39.1 | 39.1 | 25.0 |
| 20 | 9.2 | 45.8 | 45.8 | 35.2 | 35.2 | 25.0 |
| 25 | 10.3 | 44.3 | 44.3 | 34.1 | 34.1 | 24.3 |
| 31.25 | 11.6 | 42.9 | 42.9 | 31.3 | 31.3 | 23.6 |
| 62.5 | 16.8 | 38.4 | 38.4 | 21.6 | 21.6 | 21.5 |
| 100 | 21.7 | 35.3 | 35.3 | 17.1 | 17.1 | 20.1 |
| 155 | 27.7 | 32.5 | 32.5 | 4.7 | 4.7 | 19.0 |
| 200 | 32.0 | 30.8 | 30.8 | 3.0 | 3.0 | 19.0 |
| 250 | 36.4 | 29.3 | 29.3 | >0 | >0 | 18.0 |
| 300 | 40.5 | 28.2 | 28.2 | >0 | >0 | 18.0 |
| 310 | 41.3 | 27.9 | 27.9 | | | 18.0 |
| 350 | 44.3 | 27.2 | 27.2 | | | 17.0 |

Premise Cable Electrical Table 2:

| Freq. (MHz) | Input (Unfitted) Imp. (Ohms) | Fitted Impedance | Min. ELFEXT (dB) | Min. PSELFEXT (dB) |
|-------------|------------------------------|------------------|------------------|--------------------|
| 1 | 100 ± 12 | 105 ± 10 | 63.8 | 60.8 |
| 4 | 100 ± 12 | 100 ± 10 | 51.7 | 48.7 |
| 8 | 100 ± 12 | 100 ± 10 | 45.7 | 42.7 |
| 10 | 100 ± 12 | 100 ± 10 | 43.8 | 40.8 |
| 16 | 100 ± 12 | 100 ± 10 | 39.7 | 36.7 |
| 20 | 100 ± 12 | 100 ± 10 | 37.7 | 34.7 |
| 25 | 100 ± 15 | 100 ± 10 | 35.8 | 32.8 |
| 31.25 | 100 ± 15 | 100 ± 10 | 33.9 | 30.9 |
| 62.5 | 100 ± 15 | 100 ± 10 | 27.8 | 24.8 |
| 100 | 100 ± 15 | 100 ± 10 | 23.8 | 20.8 |
| 155 | 100 ± 18 | 100 ± 10 | 19.9 | 16.9 |
| 200 | 100 ± 20 | 100 ± 10 | 17.7 | 14.7 |
| 250 | 100 ± 20 | 100 ± 10 | 15.8 | 12.8 |
| 300 | 100 ± 20 | 100 ± 10 | 14.2 | 11.2 |
| 310 | 100 ± 20 | 100 ± 10 | 13.9 | 10.9 |
| 350 | 100 ± 22 | 100 ± 10 | 12.9 | 9.9 |

Notes (Overall)

Notes: Operating temperatures are subject to length de-rating. Cable passes -10C Cold Bend per UL 1581. Outer Shield Separator Material: Polyester.

Notes (Cont'd.):

T568A Plug Compatible Part Number: R301603 T568B Plug Compatible Part Number: R301604

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|-----------------|----------|-------------|-------------|-------|-------------------------|
| 11700A2 0061000 | 1,000 FT | 43.000 LB | BLUE, LIGHT | C | 4 PR #24 PP FRPVC FRPVC |
| 11700A2 0102000 | 2,000 FT | 86.000 LB | BLACK | C | 4 PR #24 PP FRPVC FRPVC |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 07-19-2016

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.