## D120/42.FF



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

General Information

Extended Product Type: D120/42.FF

 Product ID:
 1SNA190003R2200

 EAN:
 3472591900033

Catalog Description: D120/42.FF Stud Terminal Block - Feed-through - Grey

Long Description: - Rated cross section up to 300 mm2 / 1000 Kcmil, IP20 protection cover, - Holding foot on

DIN 3 rail with two position for easy mounting, lug mounting in accordance with NF C 20-13

0 and DIN 46234, various marking options, rail or base mounting.

## Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
Ambient Temperature:	-5 +40 °C
CB Certificate:	1SND165003A0200
Color:	Grey
Connecting Capacity UL/CSA:	Stranded 300 AWG
Connecting Capacity Main Circuit:	Stud / Rigid 1x 6 120 mm²
Connection Type:	Stud
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225010U1000
EAC Certificate:	1SND161009A1100
EAN:	3472591900033
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220043E1002
Flammability According to UL94:	V0
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Insulation Material:	Polyamide
Invoice Description:	D120/42.FF Stud Terminal Block - Feed-through - Grey
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	1 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	1 piece
Package Level 1 EAN:	3472591900033
Package Level 1 Gross Weight:	0.423 kg
Package Level 1 Height:	45 mm
Package Level 1 Length:	141 mm

Package Level 1 Units:	1 piece
Package Level 1 Width:	80 mm
Package Level 2 Gross Weight:	10.850 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	25 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	1200 piece
Pollution Degree:	3
Product Main Type:	D120/42.FF
Product Name:	Terminal Block
Product Net Depth:	100 mm
Product Net Height:	197 mm
Product Net Weight:	423 g
Product Net Width:	42 mm
Product Packing Type:	Box
Rated Cross-Section:	120 mm²
Rated Current (I <sub>n</sub> ):	Main Circuit 269 A
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 8000 A
Rated Voltage (U <sub>r</sub> ):	1000 V
RoHS Date:	20140212
RoHS Information:	1SND230022F0204
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Short Description:	grey Power Terminal Blocks D120/42.FF 2 studs M10
Spacing:	42 mm
Sub-Function 3:	2 connections
Tightening Torque:	Cable Lug 20 N·m Central Bolt 12 N·m

