

General Information

Extended Product Type:	BJDL5-2
Product ID:	1SNA291102R2300
EAN:	3472592911021
Catalog Description:	BJDL5-2 Jumper Bars - Orange
Long Description:	- Jumper bar for spring blocks with the same spacing, - Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C
Color:	Orange
Country of Origin:	France (FR)
Customs Tariff Number:	39269097
Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAN:	3472592911021
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Function:	Jumper Bars
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
Insulation Material:	Polyamide
Invoice Description:	BJDL5-2 Jumper Bars - Orange
Minimum Order Quantity:	50 piece
Number of Poles:	2
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472592911021
Package Level 1 Gross Weight:	0.05 kg
Package Level 1 Length:	250 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	168 mm
Package Level 2 Units:	5000 piece
Package Level 3 Units:	420000 piece
Product Main Type:	BJDL
Product Name:	Jumper Bar
Product Net Depth:	10.1 mm
Product Net Height:	18.3 mm
Product Net Weight:	1 g
Product Net Width:	5 mm
Product Packing Type:	Bag
Rated Current (I_n):	Main Circuit 24 A

RoHS Date:	18 08 2005
RoHS Information:	1SND230492F0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	Jumper Bars BJDL5-2
Spacing:	5 mm
Sub-Function:	Assembled jumper bar
Suitable For:	D2.5/5.2L D2.5/5.2L.2L D2.5/5.3L D2.5/5.4L D2.5/5.A.L.L D2.5/5.A.L.L.L D2.5/5.A.L.L.P.L D2.5/5.A.N.L D2.5/5.A.N.L.L D2.5/5.A.N.L.P.L D2.5/5.A.N.T.L.P.L D2.5/5.C3.L D2.5/5.C4.L D2.5/5.D2.L D2.5/5.DD.L D2.5/5.DE1.D.L D2.5/5.DE1.L D2.5/5.DE2.D2.L D2.5/5.DE2.L D2.5/5.DL.L D2.5/5.I.3L D2.5/5.L.L D2.5/5.LL.L D2.5/5.LLP.L D2.5/5.N.L D2.5/5.NL.L D2.5/5.NLP.L D2.5/5.NT.L D2.5/5.NTLP.L D2.5/5.SB.2L D2.5/5.SB.4L D2.5/5.SNB.2L D2.5/5.SNB.4L D2.5/5.SNBT.2L D2.5/5.SNBT.4L D2.5/5.T1.L D2.5/5.T1.P.L D2.5/5.T3.L D2.5/5.T3.P.L DB2.5/5.2L DH2.5/5.2L DR2.5/5.2L DS2.5/5.2L

