

LUTM-UP81162P

LUMINESCENCE SENSORS





Ordering information

Туре	Part no.
LUTM-UP81162P	1067295

Other models and accessories → www.sick.com/LUTM



Detailed technical data

Features

Dimensions (W x H x D)	12 mm x 31.5 mm x 21 mm
Sensing distance	12.5 mm ¹⁾
Housing design (light emission)	Rectangular
Operating range	8 mm 20 mm
Light source	LED, Ultraviolet light ²⁾
Wave length	370 nm
Light emission	Long side
Light spot size	2 mm x 2.5 mm ³⁾
Light spot direction	Vertical
Receiving range	450 nm 750 nm
Adjustment	Teach-in button
Teach-in mode	2-point teach-in static/dynamic
Output function	Light/dark switching ⁴⁾

 $^{^{1)}}$ From front edge of lens.

Mechanics/electronics

Supply voltage	12 V DC 24 V DC ¹⁾
Ripple	≤ 5 V _{pp} ²⁾

 $^{^{1)}}$ Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %). Operation in short-circuit protected network max. 8 A.

²⁾ Average service life: 100,000 h at T_U = +25 °C.

 $^{^{}m 3)}$ At sensing distance.

 $^{^{4)}\,\}mathrm{L/D}$ switching via teach-in.

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\sc V}}$ tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.

 $^{^{6)}}$ At supply voltage > 24 V, I $_{max}$ = 30 mA. I $_{max}$ is consumption count of all Q $_{n}$.

Power consumption ≤ 50 mA ³) Switching frequency 6 kHz ⁴) Response time 80 μs 5) Jitter 40 μs Output type PNP Switching output (voltage) PNP: HIGH = V _S - ≤ 2 V / LOW approx. 0 V Switching output Light/dark switching Output current I _{max} . < 100 mA 6) Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight 70 g Housing material ABS		
Response time 80 μs 5) Jitter 40 μs Output type PNP Switching output (voltage) PNP: HIGH = V _S - ≤ 2 V / LOW approx. 0 V Switching output Light/dark switching Output current I _{max} . < 100 mA 6) Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protected Output Q short-circuit protected Interference pulse suppression IP67 Enclosure rating IP67 Weight 70 g	Power consumption	\leq 50 mA $^{3)}$
Jitter 40 μs Output type PNP Switching output (voltage) PNP: HIGH = V _S − ≤ 2 V / LOW approx. 0 V Switching output Light/dark switching Output current I_{max} . < 100 mA 6) Input, teach-in (ET) PNP	Switching frequency	6 kHz ⁴⁾
Output type PNP Switching output (voltage) PNP: HIGH = V _S − ≤ 2 V / LOW approx. 0 V Switching output Light/dark switching Output current I _{max} . < 100 mA ⁶⁾ Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V	Response time	80 μs ⁵⁾
Switching output (voltage) PNP: HIGH = V _S − ≤ 2 V / LOW approx. 0 V Switching output Light/dark switching Output current I _{max} . < 100 mA ⁶⁾ Input, teach-in (ET) PNP	Jitter	40 μs
Switching output Output current I _{max} . Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight	Output type	PNP
Output current I _{max} . Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight	Switching output (voltage)	PNP: HIGH = V_S $\leq 2 \text{ V}$ / LOW approx. 0 V
Input, teach-in (ET) PNP Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight PNP Teach: U = 10 V < U _V Output Q male connector, 4-pin, 0.2 m U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression IP67	Switching output	Light/dark switching
Teach: U = 10 V < U _V Run: U < 2 V Connection type Cable with M12 male connector, 4-pin, 0.2 m Protection class III Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight Teach: U = 10 V < U _V Run: U < 2 V Cable with M12 male connector, 4-pin, 0.2 m III U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression	Output current I _{max.}	< 100 mA ⁶⁾
Protection class Circuit protection Uv connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight 70 g	Input, teach-in (ET)	Teach: U = 10 V < U _V
Circuit protection U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight 70 g	Connection type	Cable with M12 male connector, 4-pin, 0.2 m
Output Q short-circuit protected Interference pulse suppression Enclosure rating IP67 Weight 70 g	Protection class	III
Weight 70 g	Circuit protection	Output Q short-circuit protected
	Enclosure rating	IP67
Housing material ABS	Weight	70 g
	Housing material	ABS

 $^{^{1)}}$ Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %) . Operation in short-circuit protected network max. 8 A.

Ambient data

Ambient operating temperature	-10 °C +55 °C
Ambient storage temperature	-20 °C +75 °C
Shock load	According to IEC 60068
UL File No.	NRKH.E348498 & NRKH7.E348498

Classifications

ECI@ss 5.0	27270908
ECI@ss 5.1.4	27270908
ECI@ss 6.0	27270908
ECI@ss 6.2	27270908
ECI@ss 7.0	27270908
ECI@ss 8.0	27270908
ECI@ss 8.1	27270908
ECI@ss 9.0	27270908
ETIM 5.0	EC001822
ETIM 6.0	EC001822
UNSPSC 16.0901	39121528

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.


³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.


 $^{^{6)}}$ At supply voltage > 24 V, I_{max} = 30 mA. I_{max} is consumption count of all Q_{n}

Dimensional drawing (Dimensions in mm (inch))



- ① Optical axis receiver
- ② Optical axis sender
- 3 M3 mounting hole
- ④ Cable with male connector

Adjustments



- ① Status indicator LED, yellow: Status switching output Q
- ② LED indicator green: Supply voltage active
- 3 Teach-in button

Connection diagram

Cd-023




Concept of operation


Setting the switching threshold (dynamic)

1. Position background


Move at least the fluorecent mark and background using the light spot.




Press the teach-in button and keep it pressed. LED flashing slowly.



Keep the teach-in button > 3 < 30 s pressed.




Release the teach-in button.



Yellow LED will illuminate, when emitted light is on the fluorecent mark.

Sensitivity setting



Switching characteristics

Static teach-in: light/dark setting is defined using teach-in sequence.

Dynamic teach-in: switching output active on fluorecent mark, if background is longer in the field of view during the teach-in. The switching threshold is set automatically between the background and the mark.


Teach-in can also be performed using an external control signal (only dynamic teach-in).

Keylock activation and deactivation: hold down teach-in button > 30 s.

Teach-in failure: yellow LED indicator and the transmitted light of the sensor flashing quickly. For dynamic teach-in with ET signal (5 Hz) via switching output Q.


Setting the switching threshold (static)

1. Position fluorecent mark




Press and hold teach-in button > 1 < 3 s. Yellow LED flashes slowly.

2. Position background



Press and hold teach-in button < 3 s. Yellow LED goes out.

Characteristic curve



Recommended accessories

Other models and accessories → www.sick.com/LUTM

	Brief description	Туре	Part no.
Universal bar	Universal bar clamp systems		
	Universal clamp bracket for rod mounting, steel, zinc coated, without mounting hardware	BEF-KHS-KH1	2022726
	Plate L for universal clamp bracket, steel, zinc coated, universal clamp and mounting hardware included	BEF-KHS-L01	2023057
	Plate N08 for universal clamp bracket, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware	BEF-KHS-N08	2051607
6.	Plate N08N for universal clamp bracket, Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp), Universal clamp (5322626), mounting hardware	BEF-KHS-N08N	2051616
	Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-A	4056054
	Mounting bar, straight, 300 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-B	4056055
	Mounting bar, L-shaped, 150 mm x 150 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-A	4056052
	Mounting bar, L-shaped, 250 x 250 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-B	4056053
Device protection (mechanical)			
	Stainless steel 1.4301 (SVS 304), 3 mm thick protective sleeve for G6, stainless steel 1.4301, mounting hardware included	BEF-SG-G6	2069044

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
	Mounting bracket for wall mounting, Stainless steel, mounting hardware included	BEF-W100-A	5311520	
15	Mounting bracket for floor mounting, steel, zinc coated, mounting hardware included	BEF-W100-B	5311521	
2	Mounting bracket for W100 with specific bore-hole arrangements, steel, zinc coated	BEF-WN-W100-S01	4073866	
"A" A,	Adapter plate KT3 to KTM, Stainless steel, fastening screws included	BEF-AP-KTMS01	2068786	
Plug connect	ors and cables			
	Head A: female connector, M12, 4-pin, straight Head B: cable Cable: PVC, unshielded, 2 m	DOL-1204-G02M	6009382	
	Head A: female connector, M12, 4-pin, straight Head B: cable Cable: PVC, unshielded, 5 m	DOL-1204-G05M	6009866	
	Head A: female connector, M12, 4-pin, angled Head B: cable Cable: PVC, unshielded, 2 m	DOL-1204-W02M	6009383	
	Head A: female connector, M12, 4-pin, angled Head B: cable Cable: PVC, unshielded, 5 m	DOL-1204-W05M	6009867	
	Head A: female connector, M12, 4-pin, straight Head B: - Cable: unshielded	DOS-1204-G	6007302	
	Head A: female connector, M12, 4-pin, angled Head B: - Cable: unshielded	DOS-1204-W	6007303	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

