


## Strip Block for Snap-in Mounting with up to 7 IEC Appliance Outlets F

MISSING PICTURE: \\192.168.100.135\  
EPIMFS\produktion\export\Da-  
tasheets\_PrGrp\DS\_PrGrp\_Con-  
nection\DS\_PrGrp\_PG07\_1\_Ex-

MISSING PICTURE: \\192.168.100.135\  
EPIMFS\produktion\export\Da-  
tasheets\_PrGrp\DS\_PrGrp\_Con-  
nection\DS\_PrGrp\_PG07\_1\_Ex-

MISSING PICTURE: \\192.168.100.135\  
EPIMFS\produktion\export\Da-  
tasheets\_PrGrp\DS\_PrGrp\_Con-  
nection\DS\_PrGrp\_PG07\_1\_Ex-

**Description**

- Panel Mount
- Snap-in version from front side
- 1 Function
- Module of 2 up to 7 outlets ,
- Pin temperature 70 °C , Protection class I
- Solder terminals

**Approvals**

- Approval Reference Type: 0909
- VDE Certificate Number: 40030907
- UL File Number: E103791

**Characteristics**

- Suitable for use in equipment according to IEC/UL 60950

**Other versions on request**

- Other panel thickness

**Weblinks**

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)


**Technical Data**

|                                 |   |
|---------------------------------|---|
| Ratings IEC                     | 10A / 250VAC; 50Hz  |
| Ratings UL/CSA                  | 15A / 250VAC; 60Hz  |
| Dielectric Strength             | > 2 kVAC between L-N<br>> 2 kVAC between L/N-PE<br>(1 min/50Hz)   |
| Allowable Operation Temperature | -25 °C to 70 °C   |
| IP-Protection                   | from front side IP 30 acc. to IEC 60529                           |
| Insulation cover                | Suitable for appliances with protection class I acc. to IEC 61140 |
| Terminal                        | Solder terminals  |
| Panel Thickness s               | Snap-in 1.5mm<br>tolerance +0.0/-0.1                              |
| Material: Housing               | Thermoplastic, black, UL 94V-0                                    |

|                         |  |
|-------------------------|--|
| appliance inlet/-outlet | F acc. to IEC 60320-1,<br>UL 498 CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I |
|-------------------------|--|

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

Dimensions



All Variants

| Panel Thickness [mm] | Connector | Length L1 [mm] | Length L2 [mm] | Packaging unit | Order Number |
|----------------------|-----------|----------------|----------------|----------------|--------------|
| 1.5                  | 2         | 51.2 mm        | 48.3 mm        | 120            | 0909.0001    |
| 1.5                  | 3         | 75.2 mm        | 72.3 mm        | 80             | 0909.0011    |
| 1.5                  | 4         | 99.2 mm        | 96.3 mm        | 60             | 0909.0021    |
| 1.5                  | 5         | 123.2 mm       | 120.3 mm       | 40             | 0909.0031    |
| 1.5                  | 6         | 147.2 mm       | 144.4 mm       | 40             | 0909.0041    |
| 1.5                  | 7         | 171.2 mm       | 168.4 mm       | 32             | 0909.0051    |

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Mating Inlets/Plugs

Category / Description

Plug Overview complete



|   |      |
|---|------|
| IEC Plug E, Cord Connector (Rewireable), Straight, max. cable Diameter 8.5 mm | 4732 |
| IEC Plug E, Cord Connector (Rewireable), Straight, max. Cable Diameter 10 mm  | 4735 |
| IEC Plug E, Cord Connector (Rewireable), Straight                             | 9009 |
| IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 8.5 mm   | 4733 |
| IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 10 mm    | 4736 |

Plug further types to 0909

...