



- O IP68 rated
- O IP69K, Tested in accordance with DIN 40050/Part 9 IP6k9k
- O Cat 5e compliant
- O PUR jacket on cable
- Shielded system
- O Cat 5e shielded coupler
- O Shroud on RJ45
- Screw coupling
- Rewireable flex connector
- O PCB mounted panel connector
- O IDC termination panel connector
- O Earth lead version of panel adaptor
- O EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1

- O Dust and waterproof sealing when mated
- O Data rate up to 100MHz
- O Good chemical resistance, flame retardant
- O High noise immunity and EMI protection
- Maintains shielding
- O Protection from abuse and mis-mating
- O Secure, proven locking system
- Ability to 'field' terminate
- O Direct PCB mount panel connector
- Simple termination
- Continuous screening of panel mount connector




Patch Cord Flex Connector - PUR Jacket





- Mates with all panel mounting connectors
- O Patchcords with IP68 connector
- O Supplied with shielded RJ45 plug
- Single or double end terminated
- O Standard lengths: 2m, 3m & 5m
- S-FTP cable construction
- PUR jacket cable
- Wiring configuration to 568-B
- C Exceeds EIA/TIA Cat 5e

PX0836

Part no.	Туре	Length	Description
PX0836/2M00	Wire end	2m	IP68 RJ45 Buccaneer to bare end
PX0836/3M00	Wire end	3m	IP68 RJ45 Buccaneer to bare end
PX0836/5M00	Wire end	5m	IP68 RJ45 Buccaneer to bare end
PX0837/2M00	Single ended	2m	IP68 RJ45 Buccaneer to Shielded RJ45
PX0837/3M00	Single ended	3m	IP68 RJ45 Buccaneer to Shielded RJ45
PX0837/5M00	Single ended	5m	IP68 RJ45 Buccaneer to Shielded RJ45
PX0838/2M00	Double ended	2m	IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0838/3M00	Double ended	3m	IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0838/5M00	Double ended	5m	IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer








Re wireable Flex Connector



PX0834

- Mates with all panel mounting connectors
- Supplied with shielded RJ45 plug
- Two versions: for PUR jacket cable (Cat 5e) for other cable sizes from 3.5 to 8mm dia.



Part no. Description


PX0834/A Cable glands optimised for PUR jacket cable to maintain Cat 5e performance PX0834/B Suitable for use with cables from 3.5 to 8mm diameter

Panel Mounting Connector



PX0833

- O Cat 5e shielded coupler
- Mates with PX0836, PX0837,
- PX0838 and PX0834 flex
- connectors
- Standard RJ45 patchcord can be plugged into rear
- Version with earth wire available
- Single hole fixing
- Complete with panel sealing gasket



Part no. Description Fixing PX0833 Cat 5e coupler Front panel mounted PX0833/E Cat 5e coupler + earth wire Front panel mounted

BUCCANEER FOR DATA

Standard Buccaneer - Ethernet




Flanged Mounting Connector



PX0870

- Cat 5e shielded coupler
- PX0838 and PX0834 flex connectors
- Standard RJ45 patchcord can be plugged into rear
- Version with earth wire available
- Flange fixing
- Complete with panel sealing gasket & screw sealing washers



Part no.	Description	Fixing	

PX0870 PX0870/E Cat 5e coupler

Cat 5e coupler + earth wire


Flange mounting Flange mounting

PCB Mounting Connector



PX0839/PC

- O Cat 5e shielded RJ45 interface
- Rear of panel mounted
- Mates with PX0836, PX0837,
- PX0838 and PX0834 flex connectors
- For direct vertical mounting to
- O PCB, straight pins
- Complete with panel sealing
- O PX0839/PC gasket



Part no. Description Fixing

PX0839/PC

Cat 5e connector - PC


Rear panel mounted

PCB Mounting Connector




PX0839/90

- O Cat 5e shielded RJ45 interface
- Rear of panel mounted
- O Mates with PX0836, PX0837,
- O PX0838 and PX0834 flex connectors
- For direct horizontal mounting to PCB, 90° pins
- Complete with panel sealing PX0839/90 gasket



Part no.	Description	Fixing	
PX0839/90	Cat 5e connector - PC	Rear panel mounted	






Panel Mounting Connector



PX0839/IDC

- O Cat 5e shielded RJ45 interface
- O Rear of panel mounted
- Mates with PX0836, PX0837,
- O PX0838 and PX0834 flex connectors
- Two IDC blocks for discrete termination
- O Complete with panel sealing



Part no. Des

Description

PX0839/IDC Cat 5e coupler

Rear panel mounted


Fixing

Shield Back Shell Accessory



PX0888

- Maintains RJ45 coupler screening directly to panel
- Shielding can is fixed to rear of panel mount connector
- O For use on PX0833



Part no. Description


PX0888 Shielding backshell accessory

Accessories



Sealing Caps

- Sealing caps to maintain IP68 rating when connectors are not in use
- O Replacement shielded RJ45s
- Hand crimp tool for shielded RJ45
- Patch cord cable available in 50m reels



Part no. Description

PX0835	Sealing Cap for flex connectors (PX0834, PX0836-838)
PX0733	Sealing Cap for panel mounting connector (PX0833, PX0870)
PX0711	Sealing Cap for rear panel mounting connector (PX0839)
14151	Hand crimp tooling + die set
14199	PUR Jacket Cable - 50m reel
14150	Replacement shielded RJ45



Connectors

Sealing IP69K, Tested in accordance with

DIN 40050/Part 9 IP6k9k

IP68, EN60529:1992+A2:2013

(10m depth for 2 weeks)

Operating Temperature -20°C to +70°C

Materials - Overmoulded

Overmould material PVC (black) Flammability rating UL94V-0

Salt Mist EN60068-2-52 Test Kb Salt Mist

(Cyclic) Marine Severity Level 1

Materials - Re-wireable and Panel Connectors

Connector body & locking ring Polyester
Panel connector Nylon 6
Flammability rating UL94V-0
'O' rings Silicone
Panel Gasket - round Silicone
Panel Gasket - flange Neoprene
ROHS Compliant

Stranded S-FTP Patch cord cable - PUR Jacket

Polyurethane (PUR) jacket cable with internal construction exceeding Cat 5e performance levels. The PUR jacket has excellent abrasion, chemical and ozone resistance, low smoke, low halogen flame retardant construction suitable for internal and external industrial environments.

Cable

Conductors 24AWG (7/0.2mm) bare copper

Insulation HD-PE

Pair 2 of the above cores twisted Core 4 of the above cores

Tape 1 lap mylar tape

Screen 1 layer mylar and aluminium tape, 0.12mm

Sheath tinned copper braid
Op Temperature PUR Jacket Black
Min. bend radius -25°C to +85°C
Min. bend radius 10 x o/d (installation)
Diameter 6 x o/d (installed)

6.1mm nominal

Electrical @ 20°C

Characteristic

Impedance $100 \Omega \pm 15 \Omega$ @ 100 MHz

Capacitance 330pF/km

Conductor Loop

resistance $29/\Omega100m$ maximum Skew 45 nsec/100m @ 100MHz

TIA/EIA Rating Cat 5e

Cable construction - PX0836, PX0837, PX0838 and 14199



Polyurethane (PUR) Jacket

RJ45 Plug

Materials

Moulding Polycarbonate
Flammability UL94V-0
Contact material Phosphor Bronze
Contact plating 50 micron gold
Operating Temperature -40°C to +70°C
Mating cycles 1,000 cycles
ROHS Compliant

Electrical

No. Conductors 8

Conductor types 24-28AWG, solid or

multistranded

Current rating 1.5A

Voltage rating 30V ac, 42V dc Contact resistance Performance 30N ac, 42V dc 10mΩ max. Cat 5e

RJ45 Coupler

Materials

Coupler Shell Copper Alloy
Coupler Plating Nickel
Moulding ABS
Flammability UL94V-0
Contact material Phosphor Bronze

Contact material Phosphor Bronze
Contact plating 50 micron gold
Operating Temperature -40°C to +70°C
Mating cycles 1,000 cycles
ROHS Compliant

Electrical

No. Conductors 8
Current rating 1.5A

Voltage rating
Contact resistance
Performance

30V ac, 42V dc
10mV max.
Cat 5e

RJ45 PCB Connector

Materials

Coupler Shell Copper Alloy
Coupler Plating Nickel
Moulding ABS
Flammability UL94V-0

Contact material Phosphor Bronze
Contact plating 50 micron gold
PC Pins Tin plated
Operating Temperature -40°C to +70°C
Mating cycles 1,000 cycles
ROHS Compliant

Electrical

No. Conductors 8
Current rating 1.5A

Voltage rating 30V ac, 42V dc Contact resistance 10mΩ max.
Performance Cat 5e

BUCCANEER FOR DATA

Standard Buccaneer - Ethernet





Cable Joiner



PX0777

- O IP68 Rating
- O For Sealed In-Line RJ45 Connections
- O Supplied Complete with Coupler
- Shielded (STP) & Unshielded
- (UTP) versionsCat5e Shielded Coupler also available
- O Cable Range 3.5 8mm (with glands supplied)





Specifications	PX0777/UTP	PX0777/STP	PX0777/CAT5ESTP
Rating: No. of Conductors: Coupler Type: Cable Range:	1.5A, 30V a.c., 42V d.c. 8 Unshielded 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)	1.5A, 30V a.c., 42V d.c. 8 Shielded 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)	1.5A, 30V a.c., 42V d.c. 8 Shielded CAT5e performance 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)
Material:	Glass Filled Polyamide	Glass Filled Polyamide	Glass Filled Polyamide
	UL94V-0	UL94V0	UL94V0
Sealing:	IP68 to BSEN	IP68 to BSEN	IP68 to BSEN
	60529:1992+A2:2013	60529:1992+A2:2013	60529:1992+A2:2013
	(10m depth for 2 weeks)	(10m depth for 2 weeks)	(10m depth for 2 weeks)
Salt Mist	EN60068-2-52 Test Kb Salt Mist	EN60068-2-52 Test Kb Salt Mist	EN60068-2-52 Test Kb Salt Mist
	(Cyclic)	(Cyclic)	(Cyclic)
	Marine Severity Level 1	Marine Severity Level 1	Marine Severity Level 1
Operating Temp Range:	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Colour:	Black	Black	Black
RoHS	Compliant	Compliant	Compliant