




Platinum Resistance Pt100 Wire-Wound Detector Elements

Pt100 platinum resistance thermometer elements in a choice of sizes – single & dual element



What is the difference between a RTD and PRT sensor?

Nothing. RTD means resistance thermometer detector (the sensing element) and PRT means Platinum resistance thermometer (the whole assembly) i.e. a PRT uses a RTD.

- Pt100 elements to IEC 60751 Class A or B
- 100Ω Ohms @ 0°C
- Single or dual element
- Platinum coil wire-wound construction sealed inside a high purity alumina ceramic body
- Optimum performance & stability
- Temperature range -200°C to +650°C

Specifications:

Sensor type: Pt100 (100 Ohms @ 0°C)
Construction: Wire-Wound, 10mm tails

Temperature range: -200°C to +650°C

Ice point resistance: 100Ω

Fundamental interval (0°C to 100°C): 38.5 Ω (nominal) Self-heating: 0.02 to 0.3°C/mW

Thermal response: <0.4s (secs. to 63% of final value – in water @ 1m/s)

Measuring current: 1m/

Tolerance Class: In accordance with IEC 60751

W0.15 (Class A) -100°C to +450°C W0.3 (Class B) -196°C to +660°C

136/0617

Single element:

| Resistance | Tolerance Class | Diameter ('D') | Length ('L') | order code |
|----------------|------------------------|----------------|--------------|--------------------------|
| Pt100 | Class B | 1.5mm | 8mm | XF-986-FAR |
| Pt100 Pt100 | Class A Class B | 1.5mm 1.5mm | 8mm 15mm | XF-988-FAR XF-987-FAR |
| Pt100 Pt100 | Class A Class B | 1.5mm 2.8mm | 15mm 15mm | XF-984-FAR XF-983-FAR |
| Pt100 Pt100 | Class A | 2.8mm | 15mm | XF-985-FAR |
| Pt100 | Class A | 2.8mm | 25mm | XF-982-FAR |
| Dual element: | | | | |
| Pt100 (x2) | Class A | 1.5mm | 15mm | XF-980-FAR |

