

## Internet Office 120V 50/60Hz 300VA 150W Standby UPS, Ultra-Compact Desktop 6 Outlets, Tel/DSL/Ethernet Protection, TAA

MODEL NUMBER: INTERNETOFFICE300



### Highlights

- 300VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets
- TAA Compliant

### Package Includes

- INTERNETOFFICE300 UPS System
- Phone cable
- Instruction manual

### Description

Tripp Lite's INTERNETOFFICE300 UPS System provides complete power protection for your entire computer set-up. 300 VA power capacity maintains your Internet connection allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only outlets) and diagnostic LEDs. Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment. A 6-ft. telephone cord is also included. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment.

### Features

- 300 VA output power rating (150 watts)
- Up to 11 minutes backup time (single PC; 15-in monitor)
- Battery run time: 10 minutes half load/4 minutes full load
- 6 protected outlets (3 UPS & surge + 3 surge-only outlets); 6-ft. cord
- Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment; 6-ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- 5 diagnostic LEDs indicate AC present, line fault, on battery, overload and battery low/replace
- Optional [PDUB15](#) bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	300
Output Watt Capacity (Watts)	150



Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Output Circuit Breakers	15A
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Phase	Single-Phase
<b>BATTERY</b>	
Full Load Runtime (min.)	4 min. (150w)
Half Load Runtime (min.)	10 min. (75w)
DC System Voltage (VDC)	12
Expandable Runtime	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Power off / on switch
LED Indicators	5 LEDs indicate complete UPS operational status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	380



UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	380
AC Suppression Response Time	Instantaneous
Dataline Suppression	1 line TEL / DSL or 10Base T Ethernet protection
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	2.6 x 11 x 4.5
UPS Power Module Dimensions (hwd, cm)	6.60 x 27.94 x 11.43
UPS Power Module Weight (lbs.)	4
UPS Power Module Weight (kg)	1.81
UPS Shipping Dimensions (hwd / in.)	4.5 x 13 x 8.2
UPS Shipping Dimensions (hwd / cm)	11.43 x 33.02 x 20.83
Shipping Weight (lbs.)	5.4
Shipping Weight (kg)	2.5
UPS Housing Material	ABS
Primary UPS Height (mm)	66
Primary UPS Width (mm)	279
Primary UPS Depth (mm)	114
Shipping Height (mm)	114
Shipping Width (mm)	330
Shipping Depth (mm)	208
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode Efficiency Rating (100% Load)	94%
<b>COMMUNICATIONS</b>	



Communications Interface	None
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99V
High Voltage Transfer to Battery Power (Setpoint)	141V
<b>CERTIFICATIONS</b>	
UPS Certifications	Meets FCC Part 15 Category B (EMI); TAA Compliant; Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>