

External 24V 2U Rack-mount Battery Pack for select Tripp Lite UPS Systems (BP24V28-2U)

MODEL NUMBER: **BP24V28-2U**



Highlights

- Extends the runtime of expandable 24V DC Tripp Lite UPS Systems
- Supports 2U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and wallmount installation available

Package Includes

- BP24V28-2U external battery pack with attached DC cabling
- 4 post compatible rack mounting hardware
- 8 rubber feet for flat floor mounting
- Owner's manual

Description

BP24V28-2U rackmount external battery pack offers extended battery runtime when used in conjunction with expandable 24V Tripp Lite rackmount UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2-point front-rail mounting, 2 post center-mounting and wallmount installation available.

Compatible with these UPS Systems - [SMART750RML2U](#), [SU750RTL2U](#), [SU750RTLCD2U](#), [SU1000RTL2UA](#), [SU1000RTLCD2U](#), [SU1000RTL2UA](#) and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports 2 point front-rail rackmount installation without rear supports
- [2POSTRMKITWM](#) option supports balanced 2 point center-mounting in 2 post equipment racks
- [2POSTRMKITWM](#) option also enables wallmount installation
- NOTE: LIMIT OF 1 BP24V28-2U PER UPS, SEE [BP24V70-3U](#) or [BP24V36-2US](#) FOR MULTI-PACK COMPATIBILITY

Specifications

BATTERY	
DC System Voltage (VDC)	24
UPS Connection	Attached cable with red/black 75 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)



PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITWM); 2-4 post front rail rackmount(UPSHDEARKIT); Wallmount(2POSTRMKITWM)
Optional Mounting Accessory Notes	Wallmount installation using 2POSTRMKITWM requires that the plastic front bezel of the battery pack face upward. Flat floor mounting supported with included rubber feet.
Installation Form Factor Notes	Upright vertical tower configuration is not recommended for this model
Minimum Required Rack Depth (inches)	17
Minimum Required Rack Depth (cm)	43.18
Shipping Dimensions (hwd / in.)	9 x 23.75 x 20.25
Shipping Dimensions (hwd / cm)	22.9 x 60.3 x 51.4
Shipping Weight (lbs.)	64.3
Shipping Weight (kg)	29.2
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 14
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 35.6
Unit Weight (lbs.)	53.9
Unit Weight (kg)	24.45
Material of Construction	Steel
External Battery Pack Form Factor	Rack
Minimum Required Rack Depth (mm)	432
CERTIFICATIONS	
Certifications	CE
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com