




## Heat Shrinkable Tubing 3:1 in a Kit

### ShrinKit 321 Universal Basic

With ShrinKit 321 HellermannTyton has set a new standard in heat shrink tubing: ShrinKit tubings cover many applications with their ideal shrink ratio of 3:1.


#### Features and Benefits

- Compact and handy kit
- Black and coloured tubing
- Application range from 1 mm up to 16 mm



ShrinKit 321 Universal Basic.

<b>MATERIAL</b>	Polyolefin, cross-linked (PO-X)
<b>Shrink Ratio</b>	3:1
<b>Operating Temperature</b>	-55 °C to +135 °C
<b>Minimum Shrink Temperature</b>	+90 °C
<b>Longitudinal change after shrinkage</b>	+5 %/-10 % max.
<b>Dielectric Strength</b>	20 kV/mm according to ASTM D 2671
<b>Flammability</b>	Self extinguishing
<b>Insulation Class</b>	B (VDE 0530)
<b>Specifications</b>	SAE - AMS - DTL-23053/5 Class 1



Heat Shrinkable Tubing 3:1

RoHS

COMP.	Supplied Ø D min.	Recov. Ø d max.	Length (L)	Wall (WT)	Colour	Content	Article-No.
1	12.0	4.0	35.0	0.70	Black (BK)	12	380-03005
2	6.0	2.0	80.0	0.70	Blue (BU)	5	
	6.0	2.0	80.0	0.70	Red (RD)	5	
	6.0	2.0	80.0	0.70	White (WH)	5	
	12.0	4.0	80.0	0.70	Black (BK)	2	
	12.0	4.0	80.0	0.70	Blue (BU)	2	
	12.0	4.0	80.0	0.70	Red (RD)	2	
3	6.0	2.0	35.0	0.70	Blue (BU)	10	
	6.0	2.0	35.0	0.70	Red (RD)	10	
	6.0	2.0	35.0	0.70	White (WH)	10	
4	9.0	3.0	35.0	0.70	Green/Yellow (GNYE)	15	
5	9.0	3.0	35.0	0.70	Black (BK)	20	
6	3.0	1.0	35.0	0.55	Black (BK)	10	
	3.0	1.0	35.0	0.55	Blue (BU)	10	
	3.0	1.0	35.0	0.55	Red (RD)	10	
	3.0	1.0	35.0	0.55	White (WH)	10	
7	6.0	2.0	35.0	0.70	Black (BK)	20	
	6.0	2.0	35.0	0.70	Green/Yellow (GNYE)	10	
8	18.0	6.0	160.0	0.80	Black (BK)	3	
	18.0	6.0	160.0	0.80	Green/Yellow (GNYE)	3	
	18.0	6.0	160.0	0.80	White (WH)	3	

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.