

Data Sheet

Total Power: 1000 W # of Outputs: Single Outputs: 12 V to 48 V Optional 5.0 V standby

SPECIAL FEATURES

- 1000 W output power
- Low cost
- 2.5" x 5.2" x 10.0"
- 7.7 Watts per cubic inch
- Industrial/Medical safety
- -40 °C to 70 °C with derating
- Optional 5 V @ 2 A housekeeping
- High efficiency: 90% typical
- Variable speed "Smart Fans"
- DSP controlled
- Full rating with reverse airflow
- Conformal coat option
- ± 10% adjustment range
- Margin programming
- OR-ing FET
- Low acoustic noise

COMPLIANCE

- EMI Class A; Class B with internal modification option
- EN61000 Immunity
- RoHS 2

SAFETY


- ULcUL Recognized ITE (UL60950-1)
- ULcUL Recognized Medical (ANSI/AAMI ES60601-1)
- TUV-SuD ITE + Medical (EN60950-1 and EN60601-1)
- CE LVD (EN60950-1 + ROHS)
- BSMI
- CB Report
 - through Demko for IEC60950-1
 - through TUV-SuD for IEC60601-1
- CCC Approval

LCM1000

1000 Watt Bulk Front End



Electrical Specifications						
Input						
Input range	90 - 264 Vac (Operating) 115/230 Vac (Nominal) TERMINAL BLOCK					
Frequency	47 - 440 Hz, Nominal 50/60					
Input fusing	Internal 30 A fuses, both lines fused					
Inrush current	≤ 25 A peak, either hot or cold start					
Power factor	0.99 typical, meets EN61000-3-2					
Harmonics	Meets IEC 1000-3-2 requirements					
Input current	12 A RMS max input current, at 100 Vac					
Hold up time	20 ms minimum for Main O/P, at full rated load					
Efficiency	> 90% typical at full load / 230 Vac nominal					
Leakage current	< 300 μA @ 240 Vac					
ON/OFF power switch	N/A					
Power line transient	MOV directly after the fuse					
Isolation	PRI-Chassis 2500 Vdc Basic PRI-SEC 4000 VAC Reinforced 2xMOPP SEC-Chassis 500 Vdc					





Electrical Specifications								
Output								
Output rating	See table 1	90 - 264 Vac						
Set point	± 0.5%	90 - 264 Vac						
Total regulation range	Main output ± 2% 5 Vsb ± 1%	Combined line/load/transient when measured at output terminal						
Rated load	1000 W maximum	Derate linear to 50% from 50 °C to 70 °C						
Minimum load	Main output @ 0.0 A 5 Vsb @ 0.0 A	No loss of regulation						
Output noise (PARD)	1% max p-p 50 mV max p-p	Main output 5 Vsb output Measured with a 0.1 μF Ceramic and 10 μF Tantalum Capacitor on any output, 20 MHz						
Output voltage overshoot		No overshoot/undershoot outside the regulation band during on or off cycle						
Transient response	< 300 μSec	50% load step @ 1 A/µs Step load valid between 10% to 100% of output rating Recovery time to within 1% of set point at onset of transient						
Max units in parallel		Up to 10						
Short circuit protection	Protected, no damage to occur	Bounce mode						
Remote sense		Compensation up to 500 mV						
Output isolation		Standard per safety requirements						
Forced load sharing	To within 10% of all shared outputs	Analog sharing control						
Overload protection (OCP)	105% to 125% 120% to 170%	Main output 5 Vsb output						
Overvoltage protection (OVP)	125% to 145% 110% to 125%	12 V output 5 Vsb output						
Overtemp protection	10 - 15 °C above safe operating area	Both PFC and output converter monitored						


Environmental Specifications							
Operating temperature	-40 °C to +70 °C, linear derating to 75% from 60 °C to 70 °C						
Storage temperature	-40 °C to +85 °C						
Humidity	20 to 90%, non-condensing. Operating. Conformal coat option available.						
Fan noise	<45 dBA, 100% load at 30C						
Altitude	Operating - 16,405 feet (5,000 m) Storage - 30,000 feet						
Shock	MIL-STD-810F 516.5, Procedure I, VI. Storage						
Vibration	MIL-STD-810F 514.5, Cat. 4, 10. Storage						


Pin Assignment							
Signals	Name Description	Pin Number(s)					
+Vout	Power rail	SK3					
GND	Power GND	SK4					
Signals	Name Description	SK2 Pin Number					
A2	EEPROM Address	1					
-VPROG	Return connection of external supply for Margin Programming	2					
A1	EEPROM Address	3					
-Vsense	Remote Sense Return	4					
ISHARE	Load share voltage	5					
AO	EEPROM Address	6					
SDA1	Serial Data Signal (I2C)	7					
+VPROG	Positive connection of external supply for Margin Programming	8					
SCL1	Serial Clock Signal (I2C)	9					
+Vsense	Remote Sense Positive	10					
5VSB	5V standby	11					
GND	5V standby Return	12					
5VSB	5V standby	13					
G_DCOK_C	Global DCOK Collector	14					
N/A	Unused Pin	15					
G_DCOK_E	Global DCOK Emitter (GND)	16					
GND	Return Ground for output signal and I2C communication	17					
G_ACOK_C	Global ACOK Collector	18					
INH_EN	Turn Off Main Output	19					
G_ACOK_E	Global ACOK Emitter (GND)	20					


11-11-11

Note: Mating connector for SK2 is:

LANDWIN: PN 2050S2000 Housing and PN 2053T021V Contact CIVILUX: PN CI0120SD000 Housing and PN CI01TD21PE0 Contact







Signal Output Signal Connectors (SK2)

LED INDICATORS

2 provided are clearly visible up to a 45 degree offset from vertical with office environment ambient lighting. The status is reflected in the indicator color.

The DC_OK LED shall light green if the DC output is within specification, and shall be off if the output falls out of specification.

The AC_OK LED is green if the AC is within specification and off when out of specification.

CONTROL SIGNALS

AC_OK Open collector 0.5 V maximum at 10 mA. Both emitter and collector access provided.


DC_OK Open collector 0.5 V maximum at 10 mA. Both emitter and collector access provided.

PS_INHIBIT/ENABLE Signal 0.0 - 0.5 V contact closure, output OFF


Ordering Information Table 1										
Model		Nominal Output	Set Point		Cur	rent	Output Ripple	Max Continuous	Combined Line/	
Number*	Output	Voltage Set Point	Tolerance	Adjustment Range	Min	Max	P/P (0-50 °C)	Power	Load Regulation	
LCM1000L	12 V	12 V	±0.5%	10.8 - 13.2 V	0 A	83.3 A	120 mV	1000 W	2%	
LCM1000N	15 V	15 V	±0.5%	13.5 - 16.5 V	0 A	66.7 A	150 mV	1000 W	2%	
LCM1000Q	24 V	24 V	±0.5%	21.6 - 26.4 V	0 A	41.7 A	240 mV	1000 W	2%	
LCM1000U	36 V	36 V	±0.5%	32.4 - 39.6 V	0 A	27.8 A	360 mV	1000 W	2%	
LCM1000W	48 V	48 V	±0.5%	43.2 - 52.8 V	0 A	20.8 A	480 mV	1000 W	2%	

Ordering Information Table 2									
LCMXXXXY		-	А	-	В	-	С	-	###
Case Size			Input Termination		Acoustic Noise		Option Codes		Hardware Code
1-Phase input where XXXX =									
1000 = 2.4" x 5.2" x 10.0", 1000W					Blank = Standard		Blank = No Options		Factory Assigned for Modified standards
			T = Terminal Block				1 = Conformal Coat		
Voltage Code Y =	Voltage Code Y =						4 = 5 V Standby		
Code							5 = Opt 1 + 4		
L	12								
N	15								
Q	24								
U	36								
W	48								

Mechanical Drawings (LCM1000Q-T, LCM1000U-T and LCM1000W-T)




Mechanical Drawings (LCM1000L-T, LCM1000N-T)




Notes:

- 1. Parts must be completely assembled.
- 2. For label printing details, refer to ips.
- 3. Quality controlled dimensions. These dimensions to be included in the mechanical cpk of 1.33
- 4. Casing parts used must have matching color. In order to ensure color matching of parts, it is required that the raw material that will be processed by the fabricator will come from the same supplier and the sheetmetal fabricator for all matching parts must be the same. To avoid color variations on the same lot delivered, all parts with matching color requirement should be delivered as a set by the fabricator.
- 5. Sheared edges visible to the customer should have no rust formation. If rust formation is present then a concealing layer of silver ink or some other substitute should be applied on the rusted area.
- 6. Mounting locations screw penetration depth is 4.6Mm max.
- 7. Recommended screw torque:
 - M3.5X0.6P = 6-8kgf-cm
 - M4.0X0.7P = 8-10kfg-cm
- 8. Input: terminal block type. M4 screw torque value of 16kgf-cm using wire gauge 18-10 (13mm centers)
- Suitable mating connectors:
 - 9.1 For sk2:
 - A) 764-002569-0000 mat-kit hsg-20way (landwin)
 - 451-004792-0000 Hsg-dr 20ckt (lwe pn: 2050s2000)
 - 451-000709-0000 Crimp term (lwe pn: 2053t021v)
 - B) 764-003275-0000 mat-kit hsg-20way (civilux)
 - 451-004793-0000 Hsg-20way (cx pn: ci0120sd000)
 - 451-000703-0000 Term-#22~28 (cx pn: ci01td21pe0)

Accessories



Order kit part number 73-788-001 for control connector interface with .3m wires attached



In the In

Order kit part number 73-788-002 for control connector interface with unloaded housing and 20 pins

Miscellaneous Specifications

BURN-IN

100% Burn-in at 45 °C, at 80 - 90 % load. Duration of burn-in determined by Quality Assurance Procedures.

MTBF

The power supply has a minimum MTBF of 300K hours using the Bell core 332, issue 6 specification @ 25 °C and 40 °C, ambient, at full load. With the power supply installed in a system in a 25 °C ambient environment and operating at full load, capacitor life shall be 10 years, minimum for ALL electrolytic capacitors contained within this power supply. The power supply shall demonstrate a MTBF level of > 500,000 hours.

QUALITY ASSURANCE

Full QAV testing shall be conducted in accordance with Artesyn Embedded Technologies Standards with reports available upon request.

WARRANTY

Artesyn Embedded Technologies shall warrant the power supply to be free of defects in materials and workmanship for a minimum period of three years from the date of shipment, when operated within specifications. The warranty shall be fully transferable to the end owner of the equipment powered by the supply.

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way Tempe, AZ 85282 USA +1 888 412 7832

Europe (UK)

Waterfront Business Park Merry Hill, Dudley West Midlands, DY5 1LX United Kingdom +44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong +852 2176 3333



www.artesyn.com

For more information: www.artesyn.com/power For support: productsupport.ep@artesyn.com

LCM1000 DS 07Jun2017