

1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 1- Product and Company Identification

Product Type: Solvent Cleaner
Product Name: **DE-OX-ID**
Part Number(s): **19-1902**

Emergency Contact: Chemtrec
Phone: (800) 424-9300

SECTION 2- Hazard(s) Identification

***** EMERGENCY OVERVIEW ***:** Extremely flammable liquid and vapor. May be fatal if inhaled. May be fatal if swallowed. Suspect cancer hazard.

GHS Classification

Carc. 2, Eye Irrit. 2B, Flam. Liq. 2, STOT SE 3 NE, STOT SE 3 RTI, Skin Irrit. 2

Symbol(s) of Product



Signal Word

Danger

GHS HAZARD STATEMENTS

Flammable Liquid, category 2	H225	Highly flammable liquid and vapor.
Skin Irritation, category 2	H315	Causes skin irritation.
STOT, single exposure, category 3, RTI	H335	May cause respiratory irritation.
STOT, single exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Carcinogenicity, category 2	H351	Suspected of causing cancer.
Eye Irritation, category 2B	H320	Causes eye irritation



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 2- Hazard(s) Identification (Continued)

GHS PRECAUTIONARY STATEMENTS

P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P240	Ground/bond container and receiving equipment.
P241	Use explosion-proof electrical/ventilating/lighting/equipment.
P242	Use only non-sparking tools.
P243	Take precautionary measures against static discharge.
P261	Avoid breathing dust/fume/gas/mist/vapors/spray.
P264	Wash thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352	IF ON SKIN: Wash with plenty of water
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P313	IF exposed or concerned: Get medical advice/attention.
P312	Call a POISON CENTER/doctor/physician if you feel unwell.
P321	Specific treatment (see first aid section on this label).
P332+P313	If skin irritation occurs: Get medical advice/attention.
P337+P313	If eye irritation persists: Get medical advice/attention.
P362+P364	Take off contaminated clothing and wash it before reuse.
P370+P378	In case of fire: Use appropriate method to extinguish.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P403+P235	Store in a well-ventilated place. Keep cool.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 3. Composition/Information on Ingredients

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Aliphatic Hydrocarbon	64742-49-0	50-75	GHS02-GHS06	H225-315-331-336
Kerosene (Petroleum)	8008-20-6	25-50	GHS02-GHS07- GHS08	H226-315-320-335-336-351
Naphthalene	91-20-3	0.1-1.0	GHS02-GHS06- GHS08	H226-302-315-320-330-351
Ethylbenzene	100-41-4	0.1-1.0	GHS02-GHS07- GHS08	H225-315-319-332-335-351-373
Xylene	1330-20-7	0.1-1.0	GHS02-GHS07- GHS08	H226-315-319-332-335-351-373

The text for GHS Hazard Statements shown above (if any) is given in the "Other information" Section.

SECTION 4. First-Aid Measures



FIRST AID - EYE CONTACT: Immediately flush eyes with water. Flush eyes with water for a minimum of 15 minutes, occasionally lifting and lowering upper lids. Get medical attention promptly. Remove contact lenses if worn.

FIRST AID - SKIN CONTACT: Immediately flush skin with plenty of water. Remove clothing. Get medical attention immediately. Wash clothing separately and clean shoes before reuse.

FIRST AID - INHALATION: Rescuers should put on appropriate protective gear. Remove from area of exposure. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Keep victim warm. Get immediate medical attention. To prevent aspiration, keep head below knees.

FIRST AID - INGESTION: Do not induce vomiting. Do not give liquids. Obtain emergency medical attention.

SECTION 5. Fire-Fighting Measures

UNUSUAL FIRE AND EXPLOSION HAZARDS: Extremely flammable liquid and vapor. Can release vapors that form explosive mixtures at or above the flashpoint. Vapors/dust may form explosive mixture with air. Vapors can travel to a source of ignition and flash back. Empty containers retain product residue (liquid and/or vapor) and can be dangerous. DO NOT pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, static electricity, or other sources of ignition. Also, do not reuse container without commercial cleaning or reconditioning. Closed container may explode under extreme heat.

SPECIAL FIREFIGHTING PROCEDURES: As in any fire, wear self-contained breathing apparatus pressure-demand (MSHA/NIOSH approved or equivalent) and full protective gear. Avoid use of solid water streams. Use water with caution. Material will float and may ignite on surface of water. Water may be ineffective in fighting the fire. Water spray to cool containers or protect personnel. Use with caution. Water spray and foam must be applied carefully to avoid frothing. Water runoff can cause environmental damage. Dike and collect water used to fight fire. For large fires: Water fog, use fog to control vapors; For small fires: dry chemical, carbon dioxide, and foam. Small fire: dry chemicals, carbon dioxide, foam, water fog, or inert gas (nitrogen); Large fire: Foam, water fog, or water spray.

EXTINGUISHING MEDIA: Carbon Dioxide, Dry Chemical, Foam, Water Fog



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

MSDS Number: 109
 Revision Date: 3/18/2015
 Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 6. Accidental Release Measures

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED: Wear appropriate personal protective equipment. (See Exposure Controls / Personal Protection Section.) Eliminate all ignition sources. Evacuate unnecessary personnel. Prevent additional discharge of material if able to do so safely. Do not touch or walk through spilled material. Avoid runoff into storm sewers and ditches which lead to waterways. Ventilate spill area. Stay upwind of spill. A vapor suppressing foam may be used to reduce vapors. If leak or spill has not ignited, use water spray to disperse the vapors. Collect spilled materials for disposal. Use only non-combustible material for clean-up. Use clean, non-sparking tools to collect absorbed materials. Remove from surface by skimming or with suitable absorbents. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Recover by pumping (use an explosion proof or hand pump).

SECTION 7. Handling and Storage



HANDLING: Use only in a well ventilated area. Avoid breathing vapor, fumes or mist. Avoid contact with eyes, skin, and clothing. Take precautionary measures against static discharge. When transferring, follow proper grounding procedures. Use spark-resistant tools. Do not load into compartments adjacent to heated cargo. Use explosion proof equipment. Always open containers slowly to allow any excess pressure to vent. Follow all MSDS/label precautions even after containers are emptied because they may retain product residues.

STORAGE: Keep away from heat, sparks, and flame. Containers can build up pressure if exposed to heat (fire). Store containers in a cool, well ventilated place. Keep container closed when not in use. Protect from direct sunlight. Static Discharge, materials can accumulate static charges which can cause an incendiary electrical discharge. Material is a static accumulator which has the potential of forming ignitable vapor-air mixtures in storage tanks.

SECTION 8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH-TLV STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>
Aliphatic Hydrocarbon	5 mg/m ³	N.D.	5 mg/m ³	N.D.
Kerosene (Petroleum)	100 mg/m ³	150 ppm	150 ppm	N.A.
Naphthalene	10 ppm	15 ppm	10 ppm	15 ppm
Ethylbenzene	100ppm	125ppm	100ppm	N.D.
Xylene	100 ppm	150 ppm	100 ppm	N.D.

1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 8. Exposure Controls/Personal Protection (Continued)

Personal Protection



RESPIRATORY PROTECTION: Wear a MSHA/NIOSH approved (or equivalent) full-facepiece airline respirator in the positive pressure mode with emergency escape provisions.



SKIN PROTECTION: Wear impervious gloves to prevent contact with the skin. Wear long sleeves when contact is likely to occur. Wear protective gear as needed - apron, suit, boots. Where contact is likely, wear chemical resistant gloves, a chemical suit, rubber boots, and chemical safety goggles plus a face shield.



EYE PROTECTION: Wear safety glasses with side shields (or goggles) and a face shield.



OTHER PROTECTIVE EQUIPMENT: Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower.



HYGIENIC PRACTICES: Do not eat, drink, or smoke in areas where this material is used. Avoid breathing vapors. Remove contaminated clothing and wash before reuse. Wash thoroughly after handling. Wash hands before eating.

SECTION 9. Physical and Chemical Properties

Appearance:	Liquid	Physical State:	Liquid
Odor:	Wintergreen	Odor Threshold:	N.D.
Density, g/cm³:	0.782	pH:	N.D.
Freeze Point, °F:	N.D.	Viscosity:	N.D.
Solubility in Water:	Partial	Explosive Limits, vol%:	1.3 - 10.2
Boiling Range, °F:	245 - 581	Flash Point, °F:	65
Evaporation Rate:	N.D.	Auto-ignition Temp., °F:	N.D.
Vapor Density:	N.D.	Vapor Pressure:	N.D.

(See "Other information" Section for abbreviation legend)



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 10. Stability and Reactivity

STABILITY: No Information

CONDITIONS TO AVOID: Avoid impact, friction, heat, sparks, flame and source of ignition.

INCOMPATIBILITY: Keep separate from alkalis. Prevent contact with strong oxidizing agents. Keep away from acids.

HAZARDOUS DECOMPOSITION PRODUCTS: Toxic gases/fumes are given off during burning or thermal decomposition. During combustion carbon monoxide may be formed. During combustion carbon dioxide may be formed.

HAZARDOUS POLYMERIZATION: No Information

SECTION 11. Toxicological Information



Information on Toxicological Effects

EFFECTS OF OVEREXPOSURE - INHALATION: May be fatal if inhaled. Vapors can reduce the oxygen content in the air. Vapors can cause irritation of the respiratory tract. High concentrations can cause headache, nausea, weakness, lightheadedness, and stupor (CNS depression). May cause dizziness and drowsiness. Causes delayed lung injury.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Contact with skin may cause mild irritation. Harmful if absorbed through skin. Can be absorbed through skin and produce central nervous system effects. Prolonged or repeated contact can result in defatting and drying of the skin which may result in skin irritation and dermatitis (rash). Personnel with pre-existing skin disorders should avoid contact with this product.

EFFECTS OF OVEREXPOSURE - EYE CONTACT: May cause eye irritation. Contact with the eye may cause moderate irritation. Symptoms may include stinging, tearing, redness and swelling.

EFFECTS OF OVEREXPOSURE - INGESTION: May be fatal if swallowed. Harmful or fatal if liquid is aspirated into lungs. Irritating to mouth, throat, and stomach. Ingestion may cause gastrointestinal tract irritation. Can be readily absorbed by the stomach and intestinal tract. Symptoms include burning sensation of the mouth and esophagus, nausea, vomiting, diarrhea, dizziness, staggering gait, drowsiness, loss of consciousness and delirium as well as additional central nervous system effects. May cause nausea and diarrhea.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: Suspect cancer hazard. Possible brain damage from overexposure. The International Agency for Research on Cancer has evaluated ethylbenzene and classified it as a possible human carcinogen (Group 2B) based on sufficient evidence for carcinogenicity in experimental animals, but inadequate evidence for cancer in exposed humans. This product contains naphthalene. A National Toxicology Program (NTP) draft report states that lifetime inhalation exposure to naphthalene resulted in increases in tumors of the nose in rats. In a previous NTP study, lifetime inhalation exposure to naphthalene increased lung tumors in female mice. The relevance of the rodent findings to humans is questionable. Overexposure may cause nervous system damage. May cause delayed lung damage. Chronic effects of ingestion and subsequent aspiration into the lungs may cause pneumatocele (lung cavity) formation and chronic lung dysfunction. A component of this product is a potential hazard to the fetus. Significant exposure to this chemical may adversely affect people with chronic disease of the respiratory system, skin, and/or eyes. Significant exposure to this chemical may adversely affect people with chronic disease of the central nervous system.

Primary Route(s) of Entry: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 11. Toxicological Information (Continued)

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Name according to EEC</u>	<u>Oral LD50, mg/kg</u>	<u>Dermal LD50, mg/kg</u>	<u>Vapor LC50</u>
64742-49-0	Aliphatic Hydrocarbon	>5,170	>2,000	>7.63
8008-20-6	Kerosene (Petroleum)	>5,000	>2,000	>5,000
91-20-3	Naphthalene	490	20000	>0.340
100-41-4	Ethylbenzene	3500	15433	>20.0
1330-20-7	Xylene	>3523	>4200	>20.0

SECTION 12. Ecological Information

ECOLOGICAL INFORMATION: No Information

SECTION 13. Disposal Considerations



Always dispose of any waste in accordance with all local, state, and federal regulations.

DISPOSAL METHOD: Dispose of waste in accordance with all local, state and federal regulations.

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED: Wear appropriate personal protective equipment. (See Exposure Controls / Personal Protection Section.) Eliminate all ignition sources. Evacuate unnecessary personnel. Prevent additional discharge of material if able to do so safely. Do not touch or walk through spilled material. Avoid runoff into storm sewers and ditches which lead to waterways. Ventilate spill area. Stay upwind of spill. A vapor suppressing foam may be used to reduce vapors. If leak or spill has not ignited, use water spray to disperse the vapors. Collect spilled materials for disposal. Use only non-combustible material for clean-up. Use clean, non-sparking tools to collect absorbed materials. Remove from surface by skimming or with suitable absorbents. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Recover by pumping (use an explosion proof or hand pump).

SECTION 14. Transport Information

DOT Proper Shipping Name:	Flammable liquids, n.o.s. (naphtha solvents, kerosene)	Packing Group:	II
DOT Hazard Class:	3	Hazard SubClass:	No Information
DOT UN/NA Number:	UN1993	Resp. Guide Page:	128



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

MSDS Number: 109
 Revision Date: 3/18/2015
 Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Fire Hazard, Acute Health Hazard, Chronic Health Hazard

SARA SECTION 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Naphthalene	91-20-3
Ethylbenzene	100-41-4
Xylene	1330-20-7

TOXIC SUBSTANCES CONTROL ACT:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(B) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
white mineral oil	8042-47-5
methyl salicylate	119-36-8
Naphthalene	91-20-3

U.S. State Regulations:

NEW JERSEY RIGHT-TO-KNOW:

The following materials are non-hazardous, but are among the top five components in this product.

<u>Chemical Name</u>	<u>CAS-No.</u>
white mineral oil	8042-47-5
methyl salicylate	119-36-8

PENNSYLVANIA RIGHT-TO-KNOW

The following non-hazardous ingredients are present in the product are at or greater than 3%.

<u>Chemical Name</u>	<u>CAS-No.</u>
white mineral oil	8042-47-5



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

MSDS Number: 109
Revision Date: 3/18/2015
Supersedes Date: 7/25/2012

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 15. Regulatory Information (Continued)

CALIFORNIA PROPOSITION 65 CARCINOGENS

Warning: The following ingredients present in the product are known to the state of California to cause Cancer:

<u>Chemical Name</u>	<u>CAS-No.</u>
Naphthalene	91-20-3
Ethylbenzene	100-41-4

CALIFORNIA PROPOSITION 65 REPRODUCTIVE TOXINS

Warning: The following ingredients present in the product are known to the state of California to cause birth defects, or other reproductive hazards.

No Proposition 65 Reproductive Toxins exist in this product.

International Regulations: As follows -

CANADIAN WHMIS:

This MSDS has been prepared in compliance with Controlled Product Regulations except for the use of the 16 headings.

WHMIS Class: No Information

SECTION 16. Other Information

Revision Date: 11/11/2014

HMIS Ratings:

Health:	1	Flammability:	3	Reactivity:	0 - No Hazard	Personal Protection:	X
----------------	---	----------------------	---	--------------------	---------------	-----------------------------	---

Volatile Organic Compounds, gr/ltr: 506

DISCLAIMER: THE VOLATILE ORGANIC COMPOUND (VOC) CONTENT REPORTED HEREIN, IF ANY, IS BASED ON A MATERIAL VOC CALCULATION. NOTE THAT SEVERAL METHODS ARE USED FOR CALCULATING VOC CONTENT AND THAT STANDARDS/ REQUIREMENTS REGARDING VOC CONTENT VARY BY LOCATION/JURISDICTION. ACCORDINGLY, EMCO MAKES NO REPRESENTATIONS OR WARRANTIES, EXPRESS OR IMPLIED, REGARDING THIS MATERIAL'S COMPLIANCE WITH VOC STANDARDS/ REQUIREMENTS APPLICABLE IN LOCATIONS/JURISDICTIONS WHERE THIS MATERIAL MAY BE SOLD OR USED.

Text for GHS Hazard Statements shown in Section 3 describing each ingredient:

H225 Highly flammable liquid and vapor.

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: DE-OX-ID

SECTION 16. Other Information (Continued)

H226	Flammable liquid and vapor.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H320	Causes eye irritation
H330	Fatal if inhaled.
H331	Toxic if inhaled.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H351	Suspected of causing cancer.
H373	May cause damage to organs through prolonged or repeated exposure.

Icons for GHS Pictograms shown in Section 3 describing each ingredient:

GHS02



GHS07



GHS06



GHS08



GC Electronics believes that the information contained herein is accurate and reliable as of the date of this material safety data sheet, but no representation guarantee or warranty, express or implied, is made as to the accuracy, reliability or completeness of the information. Persons receiving information are encouraged to make their own determination as to the information's suitability and completeness for their particular application. NO INFORMATION CONTAINED HEREIN CONSTITUTES A PRODUCT WARRANTY OF ANY KIND, WHETHER EXPRESS OR IMPLIED; AND ALL IMPLIED WARRANTIES OF MERCHANT ABILITY AND OF FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED BY GC ELECTRONICS.