

## **ANSI Mineral Insulated Thermocouples with Threaded Pot**

Type 'K' with threaded pot & tails – 310 stainless steel or Inconel<sup>®</sup> Alloy 600 sheath



- Mineral insulated Type 'K' Thermocouple
- Choice of 310 stainless steel or Inconel® Alloy 600 sheath
- Highly flexible, sheath can be bent/formed to suit many applications and processes
- Diameters include 1.0, 1.5, 3.0 & 6.0mm
- Insulated hot junction
- Probe temperature range -40°C to +1100°C
- M8 x 1.0mm fine pitch threaded pot seal (200°C)
- 100mm tails, PFA twin twisted 7/0.2mm, colour coded to ANSI MC96.1.

## Specifications

Sensor type: Construction:	Type 'K' (Nickel Chromium/Nickel Aluminium) to ANSI MC96.1 Flexible mineral insulated probe with 310 stainless steel or Inconel® Alloy 600 sheath with M8 x 1.0mm fine pitch threaded pot seal & tails
Element/hot junction:	Single element, junction insulated from sheath (offers protection against spurious electrical signals)
Termination:	100mm PFA twin twisted 7/0.2mm tails, +yellow/-white colour coded in accordance with ANSI MC96.1
Probe temperature range:	-40°C to +1100°C >1.0mm diameter -40°C to +750°C – 1.0mm diameter and below
Pot seal rating:	200°C

**310 stainless steel:** Good corrosion & oxidation resistance to suit a wide range of processes, satisfactorily operates in sulphur bearing atmospheres

Typical applications include brick & cement kilns, glass industry, heat treatment & annealing furnaces, power stations, flues, heat exchangers etc.

Т/С	Probe	Probe	Sheath	+Positive	-Negative	order
Туре	Dia. (mm)	Length (mm)		tail wire	tail wire	code
K	1.5	150	310SS	Yellow	White	XF-1035-FAR
K	1.5	250	310SS	Yellow	White	XF-1036-FAR
K	3.0	150	310SS	Yellow	White	XF-1038-FAR
K	3.0	250	310SS	Yellow	White	XF-1037-FAR

**Inconel®** Alloy 600: Excellent oxidation resistance to 1100°C (not suitable for sulphur bearing atmospheres above 550°C)

Typical applications include heat treatment processes, annealing furnaces, chemical reactors, man -made fibre & synthetic material production, steam boilers, paper industry etc.

Т/С	Probe	Probe	Sheath	+Positive	-Negative	RS order
Туре	Dia. (mm)	Length (mm)		tail wire	tail wire	code
К	3.0	3000	ALLOY 600	Yellow	White	XF-1034-FAR