

Overview

The VideoEase VGA Balun II eliminates costly and bulky VGA cable, allowing a VGA source to be connected to a VGA monitor via one (1) 4pair Cat 5 unshielded twisted pair (UTP) cable. Used in pairs, the VGA Balun II allows VGA video to be transmitted up to 350ft (107m) via Cat 5 at 800 x 600 resolution. Each VGA connection requires p/n 500040 at the source and either p/n 500041 or 500042 at the display. The VGA Balun II works in conjunction with laptops, PCs, plasmas, CRT, LCD monitors and DLP projectors.

Typical applications include digital signage, boardroom systems, classroom video instruction and custom audio-video systems. The product features a “reset” button that may be required when used in conjunction with certain sync-sensitive displays.



Features & Benefits

- Fully supports Cat5 unshielded twisted pair (UTP)*
- Cost efficient versus VGA cable
- Use existing structured cabling system
- Save conduit space

* Reset button on units may be required with certain sync-sensitive displays.

Specifications	
Environment	VGA. VESA VP&D 1.0, VIP ver 2.0.
Devices	CRT & LCD monitors, plasma screens, PCs, laptops and multimedia projectors.
Transmission	Transparent to the user.
Bandwidth	DC to 60MHz
Input Signals	Video: 1.1Vp-p Horizontal sync: TTL standard. 300kHz max. bandwidth Vertical sync: TTL standard. 300kHz max. bandwidth
Insertion Loss	Less than 3 dB per pair over the frequency range.
Common Mode Rejection (CMMR)	15kHz -60dB typ. 100kHz to 10MHz -40dB typ. 200MHz -20dB typ.
Return Loss	-15dB max from DC to 60MHz
Connectors	500040/500042: DB15 HD Plug, RJ45 Shielded 500041: DB15 HD Receptacle, RJ45 Shielded
Max. Distance via Cat 5 Twisted Pair	VGA: 640x480 pixels (15MHz) 450ft (137m) SVGA: 800x600 pixels (30MHz) 350ft (107m) XGA: 1024x768 pixels (60MHz) 250ft (76m) SXGA: 1280x1024 pixels (100MHz) 200ft (61m)
RJ45 Pin Configuration EIA 568 (A or B) Reverse Polarity Sensitive	Pin 1 (R) Pin 2 (T) Balanced - Red Pin 4 (R) Pin 5 (T) Balanced - Green Pin 7 (R) Pin 8 (T) Unbalanced - Blue (7 signal, 8 ground) Pin 3 (R) Pin 6 (T) Unbalanced - H & V Sync
Compatibility	Not compatible with 500010, 500011, 500014, 500035 or 500036 Does not support VGA handshaking (DDC) signals.
Reset button	May be required when used with sync-sensitive displays.
Grounding screw	Grounding screw for optional use.
Cable	Cat 5 or better unshielded twisted pair (UTP)
Impedance	Input: RGB 75 ohms (DB15 HD) Unbalanced Output: RGB 100 ohms (RJ45 shielded) Balanced Horizontal and vertical sync: Balanced
Temperature	Operating: 0° to 55° C. Storage:-20° to 85° C. Humidity: up to 95% non-cond.
Enclosure	ABS fire retardant plastic
Dimensions	2.40" x 2.25 x 1.00" (6.1 x 5.7 x 2.54 cm). Plus 6" (15.2cm) lead on 500040 and 500042
Weight	500041: 2.34 oz (66 gms). 500040/500042: 3.87 oz (110 gms)
Mounting	Free-standing. Separate Velcro mounting pad included
Warranty	Lifetime
Order Information	500040 VGA Balun II, DB15 HD Plug, PC Side 500041 VGA Balun II, DB15 HD Receptacle, Monitor Side 500042 VGA Balun II, DB15 HD Plug, Monitor Side

Typical Application

