



Model #: D-2801XL-M01

ITEMS:	SPECIFICATION:	VOICE COIL:
Diameter	1 1/8" Diaphragm	Diameter 28 (mm)
Impedance	6 ohms	Winding Length 2.4 (mm)
Input	RMS 50 W, MAX 100 W	Layer 2
Free air resonance	N/A	Former material Aluminum ASV
Sensitivity	90 dB ± 2 2.45 V	Wire material Copper clad Aluminum CCAW
Frequency range	2000 ~ 20000 Hz	CONE: Silk
Sine wave test	2.83 V	SURROUND: Silk
Weight	1.35 lbs.	MAGNET: (1) (2)
Face plate: (aluminum)		Diameter 70 (mm)
		Height 15 (mm)
		Material Ferrite Y35
		Quantity 1 Pcs
		Weight 228 (grams)
		Gap(H) 3 (mm)

PARAMETERS:					
DC resistance	Re:	5.2	(Ω)	Moving mass	Mms: (grams)
Resonance frequency	Fs:	900	(Hz)	Equivalent volume	Vas: (l)
Maximum impedance	Zm:		(Ω)	Sensitivity	SPL: (dB)
Mechanical Q factor	Qms:			Suspension compliance	Cms: (mm/N)
Electrical Q factor	Qes:			BL product	Bl: (N/A)
Total Q factor	Qts:			Driver piston diameter	D: (mm)
Linear Displacement	Xmax:		(mm)	Voice Coil Inductance	Le(1K): (mH)



Qty	3: D-2801XL				
Notes					
Data Measured: Sep. 2, 2015 Wed 1:58 pm					
LMS	4.6.0.371 2/12/2007	Person: Company:	Project: File: D-2801XL.F-IB	Rev 19, 2015 Thu 9:31 am	LINEAR



Qty	52: D-2801XL				
Notes					
Data Measured: Sep. 9, 2015 Tue 11:37 am					
LMS	4.6.0.371 2/12/2007	Person: Company:	Project: File: D-2801XL.F-IB	Rev 19, 2015 Thu 9:31 am	LINEAR

