

PRO-ELEC



Model No. PEL00590

**LED ILLUMINATED ELECTRONIC
OUTDOOR TIME DELAY SWITCH**

Please read these instructions carefully before starting installation and retain for future reference.

IMPORTANT SAFETY INFORMATION

RISK OF ELECTRICAL SHOCK. ALWAYS ISOLATE THE POWER AT THE MAINS BEFORE INSTALLING OR MAINTAINING THIS SWITCH.

- This product must be installed by a competent person in accordance with the Building Regulations and the current edition of the IET Wiring Regulations (BS7671).
- This product is suitable for use with 220-240V~ 50Hz.
- This product is suitable for indoor and outdoor use..
- This product is double insulated and does not require connecting to ground.
- This product will switch incandescent lighting loads of up to 16A maximum, fluorescent lighting loads up to 6A and compact fluorescent / low energy lighting loads also low voltage lighting / fans and ventilation equipment loads up to 3A maximum.
- If using this product to switch fluorescent lighting, the light fittings must have a high power factor, or if your light fittings strike inconsistently a power factor correction capacitor may be required to be fitted.
- Refer to the lighting manufacturers or power factor correction capacitors literature to determine the exact specification required for your installation. A minimum of 1 μ F for each fitting may be connected. Maximum capacitance not exceeding 40 μ F .

INSTALLATION

NOTE: Before drilling into walls, check that there are no hidden obstructions behind the mounting surface such as pipes or cables.

- The timer can be triggered by applying a live connection to the 'TRIGGER' terminal. This can be done using a momentary switch in lighting applications for example, or an unswitched link for applications such as an extractor fan over-run.
 - For switching multiple loads, connect two or more switches in parallel using the same mains power supply connection.
1. Isolate the mains power to the circuit you are connecting this switch into.
 2. Provide a mains supply according to building regulations with reference to IEE wiring regulations (BS7671).
 3. Remove the 4 mounting screws at each corner of the front part of the casing.
 4. Mark the position of the 4 mounting holes as indicated on the outer face of the rear casing (62mm x 92mm centres), drill holes and fit wall plugs as required.
 5. Whether you are using cable glands or conduit, you will need to make appropriate hole(s) in the rear half of the casing to suit your chosen system.
 6. Secure the rear casing to the wall using suitable fixings.
 7. Feed the wiring in through the glands or conduit connections and connect to the terminal block on the front part of the switch casing as shown on Figure 1.
 - Brown – Live terminal 'L' in and 'L1' out
 - Blue – Neutral terminal 'N'.
 8. Set the desired 'ON' time by combination of the DIP switches and rotary control referring to Figure 2.

9. Fit the front part of the switch to the rear part and insert the 4 screws and tighten. Do not overtighten or you may strip the threads.
10. Restore mains power and wait 20 seconds for the switch circuitry to stabilise then activate the switch and check the 'on' duration.
11. If incorrect turn off the mains power and open the casing and adjust the setting then refit the front panel before restoring the power and re-testing.




Figure 1.

DIP SWITCH SETTING				TIMER FUNCTION
1	2	3	4	
0	0	1	0	2 seconds to 50 seconds
1	0	1	0	50 seconds to 20 minutes
1	1	1	0	20 minutes to 70 minutes
1	1	0	0	70 minutes to 2 hours
-	-	-	1	Timer function disabled

Figure 2.

OPERATION

- Once the button is touched the switched power will be supplied for the time period set on the internal controls. The power will be cut at the end of the timed cycle regardless of any additional touches of the button.
- When the timed cycle has elapsed and the outgoing power is cut, the button can be touched again to begin the timed cycle once more.

CLEANING AND MAINTENANCE

- Clean the product with a soft, dry cloth only. Do not use any solvents or abrasive chemical cleaners.

SPECIFICATIONS

Input voltage:	220-240V~ 50Hz
Rated power handling:	700W - 3700W
Suitable for use with:	Incandescent lighting Fluorescent lighting Low voltage with transformer Ventilation fans and equipment
Timer range:	2 seconds - 2 hours
O/A Dimensions L x W x H:	80 x 111 x 70mm
Switching mode:	One way



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

