HARD AT WORK SINCE 1948.

Telaris Multifunction Electrical Installation Tester



Telaris ProInstall-100-DK

The Telaris ProInstall-100-DK Multifunction Installation Tester verifies the safety of electrical installations in residential, commercial and industrial applications. It has been developed to carry out measurements in accordance with regulation.

- Tests electrical installations for safety in accordance with EN 61557, BS7671 and IEC 60364
- · Lightweight and compact for portability
- Easy to use, intuitive interface allowing you to work immediately and efficiently
- Insulation resistance measurements up to 1000V DC
- Fast loop measurements with high test current
- No trip loop test, does not trip RCDs
- Easy to read, large back lit LCD display with wide viewing angle
- Data logging capabilities downloadable to a PC

TELARIS PROINSTALL-100-DK MEASUREMENT PARAMETERS

Specifications	ProInstall-100-DK
Voltage & frequency display	•
Low Ohm resistance	•
Insulation resistance	•
Loop/line test	
Loop impedance without tripping RCDs	•
PSC (short-circuit current)	
RCD trip time	
RCD trip current (ramp function)	
Test AC and pulsed AC sensitive RCDs (Type AC, type A)	
Phase sequence test	
Illuminated display	
Memory	•

For more detailed specifications see users manual.

HARD AT WORK SINCE 1948.

PROINSTALL-100-DK DETAILED SPECIFICATIONS

AC Voltage Measurement L-N, L-PE , N-PE						
Display range Resolution Intrinsic accuracy 50Hz – 60hz		Measurement range	Operating error	Input impedance	Overload protection	
0 - 500V	0,1V	± (2% + 2D)	50 – 500Vac	± (3% + 3D)	3,3MΩ / 360 kΩ	600 Vrms

Continuity Mea	surements					
Display range (auto-ranging)	Resolution	Intrinsic accuracy	Measurement range	Operating error	Test current	Open circuit voltage
0 - 20 Ω	0,01 Ω				200	
200 Ω	0,1 Ω	± (3% + 3D)	0,30 - 2000	± (10% + 3D)	> 200 mA for Rlo < 2 Ohms	> 4V
2000 Ω	1 Ω				MIO \ Z OIIIIIS	

Insulation Resistance Measurements							
Test voltage	Display range	Resolution	Test current	Intrinsic accuracy	Measurement range	Operating error	Accuracy of test voltage at max. 1mA load
100 V	0 M Ω to 20 M Ω 20 M Ω to 100 M Ω	0,01 MΩ	1 mA @ 100 kΩ	. (50/ . 5 -1-+)	0,1 MΩ to 20 MΩ 20 MΩ to 200 MΩ	. (120/ . 20)	
250 V	0 M Ω to 20 M Ω 20 M Ω to 200 M Ω	0,1 MΩ	1 mA @ 250 kΩ	± (5% + 5 dgt.)	0,25 MΩ to 20 MΩ 20 MΩ to 200 MΩ	± (12% + 3D)	
500 V	0 MΩ to 20 MΩ 20 MΩ to 200 MΩ 200 MΩ to 500 MΩ	0,01 MΩ 0,1 MΩ 1 MΩ	1 mA @ 500 kΩ	± (5% + 5 dgt.), For R > 200 MΩ	0,5 M Ω to 20 M Ω 20 M Ω to 200 M Ω 200 M Ω to 500 M Ω	± (12% + 3D) ± (12% + 3D) ± (15% + 5D)	+20%, -0%
1000 V	0 M Ω to 200 M Ω 200 M Ω to 1000 M Ω	0,1 MΩ 1 MΩ	1 mA @ 1 MΩ	±10%	1 MΩ to 200 MΩ 200 MΩ to 1000 MΩ	± (12% + 3D) ± (15% + 5D)	

Impedance Measurements						
Display range (auto-ranging)	Resolution	Intrinsic accuracy		Measurement range	Operating error	
0 - 20 Ω	0,01 Ω	± (4% + 5 dgt.) no trip* ± (3% + 3 dgt.) high current	No trip mode	0,50 – 2000 Ω	± (15% + 8D) *	
200 Ω	0,1 Ω	± 5%	Hi current mode	0,30 – 200 Ω	± (10% + 5D)	
2000 Ω	1 Ω	± 6%	* Valid for resistance of neutral circuit < 20 Ohms			

PSC Test					
Computation	PSC determined by dividing measured mains voltage by measured loop (L-PE) resistance or line (L-N) resistance.				
Range	0 – 10 kA				
Resolution and Units	I _K < 1000 A; 1 A / I _K > 1000 A; 0,1 A				
Accuracy	Determined by accuracy of Loop Resistance and Mains Voltage measurements.				

RCD Testing		
Types of RCDs tested		
	RCD Type	
AC (Responds to AC)* A (Responds to pulsed signal)	G (General, no delay) S (Time delayed)	ProInstall-100-DK
AC	G	•
AC	S	•
A	G	•
Α	S	•
*1000mA for type AC only		Voltage range: 100 264 VAC



HARD AT WORK SINCE 1948.

PROINSTALL-100-DK DETAILED SPECIFICATIONS

RCD Test, Tripping Speed					
Current settings**	Multiplier	Current accuracy	RCD type*	Test time (max)	
10, 30, 100, 300, 500, 1000 mA	x 1	+10% -0%	G	300 ms.	
10, 30, 100, 300, 500, 1000 mA	x 1	+10% -0%	S	500 ms.	
* G = General S = Delayed-action I	RCD				

** For 1000mA setting type AC RCDs only, trip time measurement only (no ramp test)

RCD Test, Tripping Speed					
Current settings	Multiplier	Current accuracy			
10, 30, 100, 300, 500, 1000 mA*	x ½	+0% -10% of test current			
10, 30, 100, 300, 500, 1000 mA *	x 1	+10% -0%			
10, 30, 100 mA, Auto	x 5	±10%			
*For 1000mA setting type AC RCDs only					

Current multiplier	PCD tumo	Measurer	ment range	Trip time	Trip time energting error
Current multiplier	rrent multiplier RCD type		UK	intrinsic accuracy	Trip time operating error
x ½	G	310 ms.	2000 ms.		
x ½	S	510 ms.	2000 ms.		
x 1	G	310 ms.	310 ms.	. (20/ . 2.5)	. (100/ . 3.5)
x 1	S	510 ms.	510 ms.	+ (2% + 2 D)	± (10% + 2 D)
x 5	G	50 ms.	50 ms.		
x 5	S	160 ms.	160 ms.		

RCD Test, Tripping Current Measurement (Ramp Test) (I $_{\Delta N}$)					
Current range	Step size	Dwell time		Trip current	Trip current operating error
Current range	Step size	Type G	Type S	intrinsic accuracy	inp current operating error
50% to 110% of RCD's rated current	10% of I _{AN}	300 mS / step	500 mS / step	± 5%	± (10% + 2 D)

Phase Sequence Indication					
Display of phase sequence	Indicates "1-2-3" in digital display field for correct sequence. Indicates 3-2-1 for incorrect phase.				
Missing phase indication	Missing phase indicated by dash in place of number on numeric display.				

General Specifications	
Power supply	6 x 1.5 V batteries type IEC LR6 (AA) 6 x 1.2 V NiMH rechargeable batteries
Degree of pollution	2
Overvoltage category	CAT III 500 V / CAT IV 300V
Protection degree	IP40
Protection class	
Electrical safety	EN61010-1/VDE0411
EMC interference resistance	EN61326-1
Dimensions (L x W x H)	Approximately 115 x 255 x 130 mm
Weight	Approximately 1450 g

For complete specifications please download the datasheet and the users manual on www.Amprobe.eu