

<b>Vermason</b>		Product Information	No: PIS 132	
	Page 1 of 1	Issue No 2	Date : 03 June 2003	Approved by:

## **TESTING ANTISTATIC IC TUBES**

and their electrical properties

Code L8....

FEC Part No 459 938

The standard used for testing antistatic tubes is the American National Standard ANSI/EIA-541-1988 Packaging material standards for ESD sensitive items.

### **Measuring static decay time**

The test instrument is an ETS 405 D Static Decay Meter  
Humidity control chamber

- The tubes are conditioned for 48 hours in a control chamber at 12% rH.
- A static decay test is carried out by putting a charge of 5000 volts on the tube. The time taken to decay to less than 500 volts is measured. Maximum decay time allowed is <2 sec.
- The same test is made three times each with a positive and negative charge.
- Decay results of each daily production are recorded and are available on request.

### **Measuring surface resistance**

The test instrument is an ETS 806 surface resistivity meter. Conditioning is as above.

- The specification for surface resistance is  $> 1 \times 10^5$  and  $< 1 \times 10^{12}$  Ohm.

### **Antistatic Solution Control**

- The antistatic solution in which the extruded tubes are dipped is tested once a day for conductivity and alcohol content.

### **Production Control**

- Hourly inspection
- Samples of each batch are kept on the shelf for six months.
- Every 24 hours a production sample is tested for decay time and surface resistance.

*For further information, please contact*

**Vermason Ltd, 1 Avenue One, Letchworth, Hertfordshire SG6 2HB. UK**

Tel: +44(0)1462 672005 Fax: +44(0)1462 670440

e-mail : [sales@vermason.co.uk](mailto:sales@vermason.co.uk)

[www.vermason.co.uk](http://www.vermason.co.uk)