



### Main

Range	Enerlin'X
Device short name	EGX300
Product or component type	Gateway module
Device application	Server Gateway
Range compatibility	Circuit-breaker Circuit-breaker Circuit-breaker

### Complementary

Communication network type	RS232/485, Modbus RTU and ASCII even/odd or none parity, at 38400/57600 bauds on SUB-D 9 RS232/485, PowerLogic (SY/MAX) even/odd or none parity, at 38400/57600 bauds on SUB-D 9 RS232/485, JBUS even/odd or none parity, at 38400/57600 bauds on SUB-D 9 Ethernet, HTTP on RJ45 Ethernet, Modbus TCP/IP on RJ45 Ethernet, FTP on RJ45 Ethernet, SNMP on RJ45 Ethernet, BOOTP (Bootstrap Protocol) on RJ45
Communication gateway	Ethernet/Fieldbus
Web server	Embedded
Mounting mode	By clips
Mounting support	35 mm DIN rail
Control type	By software
[Us] rated supply voltage	24 V DC
Power consumption	4 W
Product certifications	UL 508 CUL FCC Class A
Standards	EN 61000-4-4 EN 61000-4-6 EN 55011 EN 55022

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

EN 61000-6-2  
EN 61000-4-5  
EN 61000-4-8  
EN/IEC 60950  
EN 61000-4-2  
EN 61000-4-3  
UL 60950  
AS/NZS 60950

Height	80.8 mm
Width	72 mm
Depth	65.8 mm
Product weight	0.17 kg
Language	Spanish English German Chinese French Italian

## Environment

IP degree of protection	IP30
Relative humidity	5...95 % at 55 °C without condensation
Ambient air temperature for operation	-25...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0826 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">End of life manual</a>
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------