Product data sheet Characteristics

XB5AD25

black complete selector switch Ø22 2-position stay put 1NO+1NC

Product availability: Stock - Normally stocked in distribution facility

Price*: 68.00 USD



Main

Range of product	Harmony XB5
Product or component type	Complete selector switch
Device short name	XB5
Bezel material	Plastic
Mounting diameter	0.87 in (22 mm)
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Stay put
Operator profile	Black standard handle
Operator position information	2 positions 90°
Contacts type and composition	1 NO + 1 NC
Contact operation	Slow-break
Connections - terminals	Screw clamp terminals: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals: >= 1 x 0.22 mm² without cable end conforming to EN/IEC 60947-1

Complementary

Main		
Range of product	Harmony XB5	
Product or component type	Complete selector switch	
Device short name	XB5	
Bezel material	Plastic	
Mounting diameter	0.87 in (22 mm)	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	Stay put	
Operator profile	Black standard handle	
Operator position information	2 positions 90°	
Contacts type and composition	1 NO + 1 NC	
Contact operation	Slow-break	
Connections - terminals	Screw clamp terminals: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals: >= 1 x 0.22 mm² without cable end conforming to EN/IEC 60947-1	
Complementary		
Height	1.65 in (42 mm)	
Width	1.18 in (30 mm)	
Depth	2.76 in (70 mm)	
'	, ,	
Terminals description ISO n°1	(13-14)NO	
Product weight	0.09 lb(US) (0.043 kg)	
Resistance to high pressure washer	1015.26 psi (7000000 Pa) at 131 °F (55 °C),distance: 0.1 m	
Contacts usage	Standard contacts	
Positive opening	With positive opening conforming to EN/IEC 60947-5-1 appendix K	
Torque value	0.14 N.m NO changing electrical state	
Mechanical durability	1000000 cycles	
Nov. 00, 2047		_

Tightening torque	7.0810.62 lbf.in (0.81.2 N.m) conforming to EN 60947-1		
Shape of screw head	Cross head compatible with Philips no 1 screwdriver Cross head compatible with pozidriv No 1 screwdriver Slotted head compatible with flat Ø 4 mm screwdriver Slotted head compatible with flat Ø 5.5 mm screwdriver		
Contacts material	Silver alloy (Ag/Ni)		
Short-circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1		
[lth] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1		
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN 60947-1		
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-1		
[le] rated operational current	1.2 A 600 V AC-15 A600 EN/IEC 60947-5-1 0.27 A 250 V DC-13 Q600 EN/IEC 60947-5-1 0.1 A 600 V DC-13 Q600 EN/IEC 60947-5-1 3 A 240 V AC-15 A600 EN/IEC 60947-5-1 0.55 A 125 V DC-13 Q600 EN/IEC 60947-5-1 6 A 120 V AC-15 A600 EN/IEC 60947-5-1		
Electrical durability	1000000 cycles, AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C		
Electrical reliability	Λ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4 Λ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4		

Environment

Protective treatment	TH		
Ambient air temperature for storage	-40158 °F (-4070 °C)		
Ambient air temperature for operation	-40158 °F (-4070 °C)		
Electrical shock protection class	Class II conforming to IEC 60536		
IP degree of protection	IP69 IP67 conforming to IEC 60529 IP69K		
NEMA degree of protection	NEMA 13 NEMA 4X		
IK degree of protection	IK06 conforming to IEC 50102		
Standards	UL 508 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 CSA C22.2 No 14 JIS C 4520		
Product certifications	ications LROS (Lloyds register of shipping) CSA DNV RINA BV GL UL		
Vibration resistance	5 gn (f = 2500 Hz) conforming to IEC 60068-2-6		
Shock resistance	resistance 30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27		

Ordering and shipping details

Category	22467 - PUSHBUTTONS,22MM(PLASTIC) NEW		
Discount Schedule	CS2		
GTIN	00785901716150		

Nbr. of units in pkg.	1	
Package weight(Lbs)	0.11	
Returnability	Y	
Country of origin	FR	


Contractual warranty

Warranty period	18 months

Product data sheet Dimensions Drawings

XB5AD25

Dimensions




e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

XB5AD25

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. \varnothing 22.5 mm recommended (\varnothing 22.3 $_0$ ^{+0.4}) / \varnothing 0.89 in. recommended (\varnothing 0.88 in. $_0$ ^{+0.016})
- (2) (3)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- Diameter on finished panel or support
- (2) (3) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. \emptyset 22.5 mm recommended (\emptyset 22.3 $_0$ ^{+0.4}) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0$ ^{+0.016})