

(0.80 mm) .0315"

SESDT-10-32-G-03.0-D-L2

SESDT-15-32-G-03.2-L

SESDT-05-32-G-03.2-L

SESDT SERIES


DISCRETE WIRE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?SESDT

- Insulator Material:** Natural Nylon
- Contact Material:** BeCu
- Plating:** Au over 50 μ" (1.27 μm) Ni
- Wire:** Tinned Copper
- Wire Insulation:** FEP
- Operating Temp Range:** -55 °C to +125 °C
- Current Rating:** 1.9 A per pin (2 pins powered)
- Voltage Rating:** 200 VAC/280 VDC
- RoHS Compliant:** Yes

Mates with:
TEM-L1




RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



TYPE STRIP	POSITIONS PER ROW	32	PLATING OPTION	ASSEMBLED LENGTH	OPTION
SESDT = Double Row *Teflon® Cable (32 AWG)	-05, -10, -15, -20		-G = 10 μ" (0.25 μm) Gold on contact area, 3 μ" (0.08 μm) Gold on tail	- "XX.X" = Assembled Length in Inches (76.2 mm) 03.0" min.	Double Ended Assemblies -L1 = Pin 1 to Pin 1 -L2 = Pin 1 to Pin 2 -L3 = Pin 1 to Pin N-1 -L4 = Pin 1 to Pin N Single Ended Assembly -L = Latching



POSITIONS PER ROW	N	N-1	A	B
-05	10	09	(11.50) .453	(5.70) .224
-10	20	19	(15.50) .610	(9.70) .382
-15	30	29	(19.50) .768	(13.70) .539
-20	40	39	(23.50) .925	(27.70) .697

Notes:
Patent Pending

*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Teflon® cable is intended for crimp only. Contact Samtec for solderable cable applications.

Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications. Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.