


# Technical Data Sheet

## RRC-SCC1130 – Single Cell Charger 1130



### 5 Watt Desktop Battery Charger for RRC1130

#### Features:

- Single bay charger
- For the standard battery RRC1130
- Optimized charging process for RRC battery:
  - Longer cycle life
- Simple operation – Plug and Play
- External wall plug power supply for worldwide use

#### Applications:

- Standard charging station for mobile devices used in medical, industrial and consumer markets

### Specification RRC-SCC1130

Input	
Voltage	5V nom.
Current	1000mA nom.
Power	5W

Output	
Voltage	4.35VDC
Current max.	1A
Voltage tolerance <sup>(1)</sup>	±1% max.
Current tolerance <sup>(1)</sup>	±10% max. @1A
Protection	Short circuit Battery over/under temperature Charger over temperature Charge timer

Environmental	
Cooling	convection cooled
Temperature	Operating: 0°C to 40°C Non-operating -10°C to 70°C
Pressure & Altitude	Operating: 1060hPa to 795hPa -382m to 2000m Non-operating: 1060hPa to 572hPa -382m to 4570m
Humidity	5% to 95% r.H., non-condensing

General	
Indicator	Multi-color LED (green, red, yellow)
Battery types	Standard battery RRC1130
Green procurement	RoHS 2011/65/EU WEEE 2012/19/EU Chinese RoHS

LED Indications	
Yellow light	The inserted battery is of the correct type and is currently being charged.
Green light	The battery is charged and can be removed for use.
Red blinking	Battery detection phase
Red light	No battery inserted, Battery over/under temperature-, charger over temperature-, battery charge timer time-out-error or input voltage too low

Charger Mechanical Details	
Housing dimensions (LxWxH)	67 x 107 x 9mm
Weight	25g (excluding power supply)

#### Notes:

1. Total regulation tolerance includes initial set accuracy, line and load regulation

# Technical Data Sheet

## RRC-SCC1130 – Single Cell Charger 1130



Safety & EMC		
Regulatory approvals	In combination with specified external AC/DC power supply	
Electromagnetic Emissions	Europe	CE
Electromagnetic Immunity	USA	EN55022, level B FCC15 class B
	ESD immunity	EN/IEC61000-4-2
	Electromagnetic field immunity	EN/IEC61000-4-3
	EFT / Burst	EN/IEC61000-4-4
	Surge	EN/IEC61000-4-5
	Conducted Immunity	EN/IEC61000-4-6
	Magnetic Fields	EN/IEC61000-4-8

### Specification external AC/DC power supply

Input	
Voltage range	100 - 240VAC
Current	0.3A max.
Stand by power	No load 0.1W @ 230 VAC

Output	
Voltage range	5VDC
Power	5W max.
Current range	1A
Protection	Over voltage, Short circuit

Environmental	
Temperature	Operating: 0°C to 40°C
	Non-operating -20°C to 60°C

General	
Efficiency	California's Energy Efficiency Level VI
Line regulation	±5%
Ripple & Noise	200mV (p-p)

Power Supply Mechanical Details	
Standard output connector	Micro USB
Housing dimensions (LxWxH)	71 x 60 x 26.5mm for UK 60 x26 x40mm for EU 60 x26 x40mm for KR 60.3 x 41.5 x 66.3mm for AUS 60 x 25.2 x 40mm for USA/CAN/JP 68 x 30 x 35mm for CN
Weight	70g max.

Safety & EMC & Approvals		
Approvals	Europe	CE
	International	CB
	USA/Canada	cULus
	Australia	RCM
	Korea	KC
	China	CCC
	Japan	PSE
	Russia (Customs Union)	EAC
	India	BIS

Germany/Headquarters	USA	Hong Kong	China
RRC power solutions GmbH Technologiepark 1 D-66424 Homburg / Saar	RRC power solutions Inc. 18340 Yorba Linda Blvd., Suite 107-437 Yorba Linda, CA 92886-4104	RRC power solutions Ltd. S-V,6/F, Valiant Industrial Centre 2-12 Au Pui Wan Street Fo Tan, N.T. Hong Kong	RRC power solutions Ltd. Room 520, Yuanlin Building, Aiguo Road No. 3066, Luohu District, Shenzhen 518021
Tel.: +49 6841 98090 Fax: +49 6841 9809280 Email: sales@rrc-ps.de Web: www.rrc-ps.de	Tel.: +1 714 777 3604 Fax: +1 714 777 3658 Email: usa@rrc-ps.com Web: www.rrc-ps.com	Tel.: +852 2376 0106 Fax: +852 2376 0107 Email: hkrrc@rrc-ps.cn Web: www.rrc-ps.com	Tel.: +86 755 8374 1908 Fax: +86 755 8374 1861 Email: hkrrc@rrc-ps.cn Web: www.rrc-ps.com