



## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter : 85 m <sup>3</sup> /h at 50 Hz Free flow rate with standard filter : 98 m <sup>3</sup> /h at 60 Hz
[Us] rated supply voltage	175...253 V
Input voltage	230 V 50/60 Hz

## Complementary

Rated power in W	17 W 50 Hz 15 W 60 Hz
[In] rated current	0.121 A 50 Hz 0.097 A 60 Hz
Noise level	46...49 dB
Bearing type	Ball
Height	External : 170 mm
Width	External : 150 mm
Depth	External : 62 mm
Cut-out dimensions	125 x 125 mm
Product weight	0.78 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	50 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Faston connector
IP degree of protection	IP54

Device composition	<ul style="list-style-type: none"> <li>1 outlet grille front</li> <li>1 axial motor</li> <li>2 protective grille on the front and rear surfaces</li> <li>1 filter front of axial motor</li> <li>1 cut-out template</li> <li>1 power cord</li> </ul>
Condition of use	<ul style="list-style-type: none"> <li>Surrounding environment must be relatively clean</li> <li>Filter must be cleaned and replaced regularly</li> <li>Outside temperature must be 5 °C lower than inside temperature</li> <li>Flow rates depends on the work point, see ProClima software</li> <li>Overfrequent filter replacement should be avoided</li> </ul>

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------