Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



76408TS Multi-Conductor - 300V Shielded, Continuous Flexing Data Applications Up to 6 Million FLex Life Cycles



For more Information please call

1-800-Belden1

General Description:

28 AWG stranded (7x36) tinned copper conductors, PVC insulation, aluminum/polyester foil shield, tinned copper braid shield, 85% coverage, oil-resistant overall PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
8	28	7x36	TC - Tinned Copper	0.381

Total Number of Conductors:

16

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PVC - Polyvinyl Chloride	0.254	0.889

Outer Shield

Outer Shield Material:

Туре	Outer Shield Material	Coverage (%)
Foil Shield	Alum/Mylar	100.000
Braid	Tinned Copper	85.000

Outer Shield Drain Wire AWG:

Component	AWG	Stranding	Drain Wire Conductor Material
Drain Wire	26	7x34	TC - Tinned Copper

Outer Shield Separator Material:

Tissue Tape, 25% Overlap, Min.

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)	
PVC - Polyvinyl Chloride	1.016	

Overall Cable

Overall Nominal Diameter:

8.407 mm

Pair

Pair Color Code Chart:

1 BLACK-RED 2 BLACK-WHITE 3 BLACK-GREEN 4 BLACK-BLUE 5 BLACK-BROWN 6 BLACK-YELLOW 7 BLACK-ORANGE 8 RED-GREEN	Number	Color
3 BLACK-GREEN 4 BLACK-BLUE 5 BLACK-BROWN 6 BLACK-YELLOW 7 BLACK-ORANGE	1	BLACK-RED
4 BLACK-BLUE 5 BLACK-BROWN 6 BLACK-YELLOW 7 BLACK-ORANGE	2	BLACK-WHITE
5 BLACK-BROWN 6 BLACK-YELLOW 7 BLACK-ORANGE	3	BLACK-GREEN
6 BLACK-YELLOW 7 BLACK-ORANGE	4	BLACK-BLUE
7 BLACK-ORANGE	5	BLACK-BROWN
. 52.01.01.010	6	BLACK-YELLOW
8 RED-GREEN	7	BLACK-ORANGE
	8	RED-GREEN

Mechanical Characteristics (Overall)

Bulk Cable Weight:	86.316 Kg/Km
Max. Recommended Pulling Tension:	137.894 N
Min. Bend Radius/Minor Axis:	83.820 mm
Min. Bend/Installation:	83.820 mm
Min. Bend Radius (Continuous Flexing):	127 mm
Flex Cycle Rating:	6 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	СМ
AWM Specification:	UL Style 20006
CSA Specification:	600 V AWM I/II A/B

Page 1 of 2 10-02-2017

Detailed Specifications & Technical Data





76408TS Multi-Conductor - 300V Shielded, Continuous Flexing Data Applications Up to 6 Million FLex Life Cycles

EU Directive 2011/65/EU (ROHS II):	Yes
Other Specification:	AWM/STYLE 10002, AWM/STYLE 2661, CM, AWM I/II A/B, C(UL) TYPE CMG, FT4, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2)
Flame Test	
CSA Flame Test:	FT4
Suitability	
Sunlight Resistance:	Yes

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
Characteristic Impedance	97.000

Nom. Inductance:

Inductance (µH/m) 0.722

Nom. Capacitance Cond. to Other Cond. & Ground:

Description	Freq. (kHz)	Capacitance (pF/m)
Mutual Capacitance	1.000	64.636
Ground Capacitance	1.000	114.835

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 219.827

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km) 9.187

Notes (Overall)

Notes: Temperature Range -10 to 105°C(static), +5 to 105°C (dynamic)

Put Ups and Colors:

tem# Putup Ship Weight Color Notes Ite	Item Desc
--	-----------

Revision Number: 0 Revision Date: 09-27-2017

© 2017 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Page 2 of 2