

27326A Multi-Conductor - 600V Type TC Cable



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG multi-conductor stranded (7x26) bare copper conductors, PVC/Nylon insulation, PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	18	7x26	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.047

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	Blue
4	Orange

Overall Nominal Diameter: 0.313 in.

Mechanical Characteristics (Overall)

Wet Temperature Range: -30°C To +75°C

Dry Temperature Range: -30°C To +90°C

Bulk Cable Weight: 52 lbs/1000 ft.

Max. Recommended Pulling Tension: 88 lbs.

Min. Bend Radius/Minor Axis: 3.200 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: NPLF, TC

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

27326A Multi-Conductor - 600V Type TC Cable

Other Specification:	ICEA S-73-532, S-61-402
----------------------	-------------------------

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Conductor DC Resistance:**

DCR @ 20°C (Ohm/1000 ft)
5.860

Max. Operating Voltage - UL:

Voltage
600 V RMS (NEC Type TC)
150 V RMS (NPLF)

Max. Recommended Current:

Current
4.8 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
27326A 01010000	10,000 FT	600.000 LB	BLACK	C	4 #18 PVC/NYL PVC
27326A 0105000	5,000 FT	290.000 LB	BLACK	C	4 #18 PVC/NYL PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 07-11-2013

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.