



For more Information  
please call

1-800-Belden1



### General Description:

20 and 18 AWG stranded tinned copper conductors, PVC insulation (power), FPE insulation (Data), individually foil shielded (100% coverage) and an overall tinned copper braid (65% coverage), sunlight/oil-resistant PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
4	1	18	19x30	TC - Tinned Copper
	1	20	19x32	TC - Tinned Copper

#### Insulation

Insulation Material:

Insulation Material	AWG
PVC - Polyvinyl Chloride	18
FPE - Foam Polyethylene	20

#### Inner Shield

Inner Shield Material:

Layer #	Type	Inner Shield Material	Coverage (%)
18 AWG Pair	Tape	Aluminum Foil-Polyester Tape	100
20 AWG Pair	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
20

Inner Shield Drain Wire Stranding: 19x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	65

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

#### Overall Cable

Overall Nominal Diameter: 0.378 in.

#### Pair

Pair Color Code Chart:

Number	Color
18 AWG Pair	Red & Black
20 AWG Pair	Blue & White

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C (UL AWM Style 20201)

Bulk Cable Weight: 68 lbs/1000 ft.

Max. Recommended Pulling Tension: 65 lbs.

Min. Bend Radius/Minor Axis: 3.800 in.

### Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

## 7895A Multi-Conductor - DeviceBus® for ODVA DeviceNet™

NEC/(UL) Specification:	CMG, PLTC
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 20201 (600 V 75°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Other Specification:	ODVA Cable III

## Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

## Suitability

Sunlight Resistance:	Yes
Oil Resistance:	Yes

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

## Nom. Characteristic Impedance:

Description	Impedance (Ohm)
20 AWG Pair	120

## Nom. Capacitance Conductor to Conductor:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/ft)
20 AWG Pair	1			12.0

## Nominal Velocity of Propagation:

Description	VP (%)
20 AWG Pair	75

## Maximum Delay:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Delay (ns/ft)
20 AWG Pair				1.36

## Maximum Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/100 m)
18 AWG	6.9
20 AWG	10.9

## Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.2

## Max. Attenuation:

()	Description	Freq. (MHz)
.29	20 AWG Pair Only	.125
.50		.500
.70		1.000

## Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	PLTC, CMG
600 V RMS	UL AWM

## Notes (Overall)

**Notes:** Mid. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Association, Inc. trademark.

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

## 7895A Multi-Conductor - DeviceBus® for ODVA DeviceNet™

7895A T5U1000	1,000 FT	84.000 LB	GRAY T5U	C	2#18 PVC, 2#20 FHDPE SH PVC
7895A T5U500	500 FT	41.000 LB	GRAY T5U		2#18 PVC, 2#20 FHDPE SH PVC
7895A T5U5000	5,000 FT	440.000 LB	GRAY T5U	C Z	2#18 PVC, 2#20 FHDPE SH PVC

**Notes:**

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1    Revision Date: 05-14-2007

© 2017 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).