

SIMATIC S7-1200, CPU 1211C, COMPACT CPU, DC/DC/DC,
ONBOARD I/O: 6 DI 24V DC; 4 DO 24 V DC; 2 AI 0 - 10V DC,
POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA
MEMORY: 50 KB



General information

Product type designation	CPU 1211C DC/DC/DC
Firmware version	V4.2
Engineering with	
• Programming package	STEP 7 V14 or higher

Supply voltage

Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V

Input current

Current consumption (rated value)	300 mA; CPU only
Current consumption, max.	900 mA; CPU with all expansion modules

Inrush current, max.	12 A; at 28.8 V DC
I^2t	0.5 A ² ·s
Output current	
for backplane bus (5 V DC), max.	750 mA; Max. 5 V DC for CM
Encoder supply	
24 V encoder supply	
• 24 V	L+ minus 4 V DC min.
Power loss	
Power loss, typ.	8 W
Memory	
Work memory	
• integrated	50 kbyte
• expandable	No
Load memory	
• integrated	1 Mbyte
• Plug-in (SIMATIC Memory Card), max.	with SIMATIC memory card
Backup	
• present	Yes
• maintenance-free	Yes
• without battery	Yes
CPU processing times	
for bit operations, typ.	0.08 µs; / instruction
for word operations, typ.	1.7 µs; / instruction
for floating point arithmetic, typ.	2.3 µs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
OB	
• Number, max.	Limited only by RAM for code
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	10 kbyte
Flag	
• Number, max.	4 kbyte; Size of bit memory address area
Local data	
• per priority class, max.	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB
Address area	
Process image	

- Inputs, adjustable
- Outputs, adjustable

1 kbyte

1 kbyte

Hardware configuration

Number of modules per system, max.

3 communication modules, 1 signal board

Time of day

Clock

- Hardware clock (real-time) Yes
- Backup time 480 h; Typical
- Deviation per day, max. ± 60 s/month at 25 °C

Digital inputs

Number of digital inputs

6; Integrated

- of which inputs usable for technological functions

3; HSC (High Speed Counting)

Source/sink input

Yes

Number of simultaneously controllable inputs

all mounting positions

— up to 40 °C, max.

6

Input voltage

- Rated value (DC) 24 V
- for signal "0" 5 V DC at 1 mA
- for signal "1" 15 V DC at 2.5 mA

Input current

- for signal "1", typ.

4 mA; nominal

Input delay (for rated value of input voltage)

for standard inputs

— parameterizable

0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 μ s; 0.05 / 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 ms

— at "0" to "1", min.

0.2 ms

— at "0" to "1", max.

12.8 ms

for interrupt inputs

— parameterizable

Yes

for counter/technological functions

— parameterizable

Single phase : 3 @ 100 kHz, differential: 3 @ 80 kHz

Cable length

- shielded, max.
- unshielded, max.

500 m; 50 m for technological functions

300 m; For technological functions: No

Digital outputs

Number of digital outputs

4

- of which high-speed outputs

4; 100 kHz Pulse Train Output

Limitation of inductive shutdown voltage to

L+ (-48 V)

Switching capacity of the outputs

• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Output voltage	
• for signal "0", max.	0.1 V; with 10 kOhm load
• for signal "1", min.	20 V
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", max.	1 μ s
• "1" to "0", max.	5 μ s
Switching frequency	
• of the pulse outputs, with resistive load, max.	100 kHz
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Analog inputs	
Number of analog inputs	2
Input ranges	
• Voltage	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
• Input resistance (0 to 10 V)	≥ 100 k ohms
Cable length	
• shielded, max.	100 m; twisted and shielded
Analog outputs	
Number of analog outputs	0
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	10 bit
• Integration time, parameterizable	Yes
• Conversion time (per channel)	625 μ s
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
1. Interface	
Interface type	PROFINET
Physics	Ethernet
Isolated	Yes

automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Interface types	
• Number of ports	1
• integrated switch	No
Functionality	
• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes
• Web server	Yes
• Media redundancy	No
PROFINET IO Controller	
• Transmission rate, max.	100 Mbit/s
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	No
— MRP	No
— MRPD	No
— PROFINergy	No
— Prioritized startup	Yes
— Number of IO devices with prioritized startup, max.	16
— Number of connectable IO Devices, max.	16
— Number of connectable IO Devices for RT, max.	16
— of which in line, max.	16
— Activation/deactivation of IO Devices	Yes
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— Updating time	The minimum value of the update time also depends on the communication component set for PROFINET IO, on the number of IO devices and the quantity of configured user data.
PROFINET IO Device	
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No

— Open IE communication	Yes
— IRT	No
— MRP	No
— MRPD	No
— PROFinergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2

Protocols

Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 required
AS-Interface	Yes; CM 1243-2 required

Protocols (Ethernet)

• TCP/IP	Yes
• DHCP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes

Open IE communication

• TCP/IP	Yes
— Data length, max.	8 kbyte
— several passive connections per port, supported	Yes
• ISO-on-TCP (RFC1006)	Yes
— Data length, max.	8 kbyte
• UDP	Yes
— Data length, max.	1 472 byte

Web server

• User-defined websites	Yes
-------------------------	-----

Further protocols

• MODBUS	Yes
----------	-----

Communication functions

S7 communication

• supported	Yes
• as server	Yes
• as client	Yes
• User data per job, max.	See online help (S7 communication, user data size)

Web server

• supported	Yes
-------------	-----

Number of connections

• overall	16; dynamically
-----------	-----------------

Test commissioning functions	
Status/control	
• Status/control variable	Yes
• Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
Forcing	
• Forcing	Yes
Diagnostic buffer	
• present	Yes
Traces	
• Number of configurable Traces	2
• Memory size per trace, max.	512 kbyte
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• RUN/STOP LED	Yes
• ERROR LED	Yes
• MAINT LED	Yes
Integrated Functions	
Number of counters	6
Counting frequency (counter) max.	100 kHz
Frequency measurement	Yes
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction interface	4; With integrated outputs
PID controller	Yes
Number of alarm inputs	4
Number of pulse outputs	4
Limit frequency (pulse)	100 kHz
Potential separation	
Potential separation digital inputs	
• Potential separation digital inputs	No
• between the channels, in groups of	1
Potential separation digital outputs	
• Potential separation digital outputs	Yes
• between the channels	No
• between the channels, in groups of	1
EMC	
Interference immunity against discharge of static electricity	
• Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes

— Test voltage at air discharge	8 kV
— Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
• Interference immunity on supply lines acc. to IEC 61000-4-4	Yes
• Interference immunity on signal cables acc. to IEC 61000-4-4	Yes
Interference immunity against voltage surge	
• on the supply lines acc. to IEC 61000-4-5	Yes
Interference immunity against conducted variable disturbance induced by high-frequency fields	
• Interference immunity against high-frequency radiation acc. to IEC 61000-4-6	Yes
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-20 °C
• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa

• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
• Installation altitude, min.	-1 000 m
• Installation altitude, max.	2 000 m

Relative humidity

• Operation, max.	95 %; no condensation
-------------------	-----------------------

Vibrations

• Vibration resistance during operation acc. to IEC 60068-2-6	2 g (m/s ²) wall mounting, 1 g (m/s ²) DIN rail
• Operation, tested according to IEC 60068-2-6	Yes

Shock testing

• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
--------------------------------------	---

Pollutant concentrations

• SO ₂ at RH < 60% without condensation	SO ₂ : < 0.5 ppm; H ₂ S: < 0.1 ppm; RH < 60% condensation-free
--	--

Configuration

Programming

Programming language	
— LAD	Yes
— FBD	Yes
— SCL	Yes

Know-how protection

• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes

Access protection

• Protection level: Write protection	Yes
• Protection level: Read/write protection	Yes
• Protection level: Complete protection	Yes

Cycle time monitoring

• adjustable	Yes
--------------	-----

Dimensions

Width	90 mm
Height	100 mm
Depth	75 mm

Weights

Weight, approx.	370 g
-----------------	-------

last modified: 11/28/2017