


NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 1 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	

1 Objective

This specification defines the performance, test, quality and reliability requirements of the Minitek Pwr3.0 High Current Connectors (HCC).

2 Scope


This specification is applicable to the termination characteristics of the Minitek Pwr3.0 High Current Connectors (HCC) which provides high current rating.

3 Product Name and Part Number

Product Name	Part Serial Number	Material and Finish
Wire Connector Housing	10132445	High Temp. Thermoplastic, UL 94V-0, Black
	10132446	High Temp. Thermoplastic, UL 94V-0, Black
Crimp Terminal	10132447	High Conductivity Copper Alloy, Tin or Gold Flash Plated, over Nickel
	10132448	High Conductivity Copper Alloy, Tin or Gold Flash Plated, over Nickel
Header	10132449	HSG: High Temp. Thermoplastic, UL 94V-0, Black
		Contact: High Conductivity Copper Alloy, Tin or Gold Flash Plated, over Nickel
	10132450	HSG: High Temp. Thermoplastic, UL 94V-0, Black
		Contact: High Conductivity Copper Alloy, Tin or Gold Flash Plated, over Nickel

4 Ratings and Applicable Wires

Item	Specification
Rated Voltage	250V AC/DC
Applicable Wire	AWG #16, AWG #18, AWG #20
Insulation Outer Diameter	2.20 Max.
Operating Temperature Range	-40 ~ +85°C

NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 2 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	

Rated Current

Pin AWG#	2 pins	4 pins	6, 8 pins	10 pins	12 pins	14, 16, 18 pins	20, 22, 24 pins
16 AWG	12 A	11.5 A	9 A	9 A	7.5 A	7 A	6.5 A
18 AWG	11 A	10 A	8 A	8 A	6.5 A	6 A	5.5 A
20 AWG	10 A	9 A	7.5 A	6.5 A	6 A	5.5 A	5 A

5 Requirements

5.1 Qualification

Connectors furnished under this specification shall be capable of meeting the qualification test requirements specified herein.

5.2 Material

The material for each component shall be as specified herein or equivalent.

5.3 Finish


The finish for applicable components shall be as specified herein or equivalent.

5.4 Design and Construction

Connectors shall be of the design, construction, and physical dimensions specified on the applicable product drawing. There shall be no cracks, burrs, or other physical defects that may impair performance.

6 Electrical Performance

Item		Test Condition	Requirement
6-1	Contact Resistance	Measure it with low voltage less than 20mV and 10mA. Test Method : EIA-364-06	10mΩ Max.
6-2	Insulation Resistance	Apply 500V DC between adjacent contacts and measure its resistance within 1 minute. Test Method : EIA-364-21	1000MΩ Min.


NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 3 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	

6-3	Dielectric Withstanding Voltage	Apply AC 1500Vr.m.s between adjacent contacts and measure its resistance within 1 minute. Test Method : EIA-364-20	No breakdown.
6-4	Temperature Rise	Apply specified current to contacts connected in series. Measure change of temperature on contact using thermocouples or 4 hours. Test Method : EIA-364-70 Method 1	Temperature rise value: 30°C Max.

Note: The temperature rise test part is plastic insulation surface which nearby the connecting point.


7 Mechanical Performance

Item		Test Condition	Requirement		
7-1	Mating and Unmating Force	Measure force necessary to mate between the counterpart connectors. Testing speed: 25±3mm / minute. Test Method: EIA-364-13 (Per circuit)	Mating Force: 0.50 Kgf Max. (mating force avg. of 30 times) Unmating Force: 0.20 Kgf Min.		
7-2	Contact Retention	Measure the contact retention with tensile strength tester. Testing speed: 25±3mm / minute. Test Method: EIA-364-05	1.50 kgf (Min.)		
7-3	Crimp Retention	Measurement of tensile strength at conductor crimp of socket contact using tensile tester. (No crimp at covered part) Testing speed: 25±3mm / minute. Test Method: EIA-364-08	16 AWG	18 AWG	20 AWG
			7.0 Kgf Min.	7.0 Kgf Min.	5.0 Kgf Min.
7-4	Pin Retention	Measure the pin retention with tensile strength tester. Testing speed: 25±3mm / minute. Test Method: EIA-364-05	1.5 Kgf Min.		


NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 4 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	


8 Environmental Performance

Item		Test Condition	Requirement
8-1	Durability	Mate and unmate specimens for 50 cycles. Test Method: EIA-364-09	Contact Resistance: 20mΩ Max.
8-2	Vibration	Frequency: 10-55-10 Hz / minute. Amplitude: 1.52mm. Direction: Each of X, Y & Z-axis directions. *Each axis shall be at right angles to others. Period: 2 hours for each direction. Test Method: EIA-364-28	1. No electrical discontinuity more than 1 μs. 2. No damage.
8-3	Shock	Max. G: 50G Duration: 11 msec. 3 strokes in each X, Y, Z axials. Test Method: EIA-364-27	1. No electrical discontinuity more than 1 μs. 2. No damage.
8-4	Heat Resistance	Mated connector shall be placed in a chamber for 96 hours at +85±2 °C. Test Method: EIA-364-17	1. No damage. 2. Insulation Resistance: 1000MΩ (Min.) 3. Voltage proof: 1500Vr.m.s. for 1 minute, no breakdown. 4. Contact Resistance: 20mΩ Max.
8-5	Cold Resistance	Mated connector shall be placed in a chamber for 96 hours at -40±2°C. Test Method : EIA-364-59	
8-6	Humidity	Mated connector shall be placed in a humidity chamber on the following conditions. Temperature: 60±2°C Relative Humidity: 90-95% Period: 240 hours Test Method: EIA-364-31	

NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 5 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	


8-7	Temperature Cycling	Mated connector shall be set to temperature cycling for 10 cycles of which 1 cycle consist of a) -55°C, 30 minute. b) +85°C, 30 minute. Test Method: EIA-364-32	<ol style="list-style-type: none"> 1. No damage. 2. Insulation Resistance: 1000MΩ Min. 3. Voltage proof: 1500Vr.m.s. for 1 minute, no breakdown. 4. Contact Resistance: 20mΩ Max.
8-8	Salt Spray	Mated connector shall be placed on a salt spray chamber on the following conditions. Salt Solution Density: 5±1%. Temperature: 35±2°C. Period: 8 hours for post-plate terminals; 48 hours for pre-plate terminals; Test Method: EIA-364-26	Contact Resistance: 20mΩ Max.
8-9	Solderability	After dipping in the flux for 5 to 10 seconds, dip in Sn-Ag-Cu solder (Sn 96.5%) of 245±2°C for 3±0.5 seconds. Test Method: EIA-364-52	Wet solder coverage: 95% Min.
8-10	Resistance to IR Reflow Heat (SMT)	According to the attached reflow condition. Peak Temp.: 260±5°C for 5±0.5 seconds. Test for 3 cycles	No damage to insulator material

NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 6 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	




Profile Feature	Pb-Free Assembly
Average ramp-up rate (TL to TP)	3°C / second Max.
Preheat - Temperature Min. (TS Min.) - Temperature Max. (TS Max.) - Time (Min. to Max.) (ts)	150°C 200°C 60-180 seconds
TS Max. to TL - Ramp-up rate	3°C / second Max.
Preheat - Temperature Min. (TL) - Time (t1)	217°C 60-150 seconds
Peak Temperature (TP)	260 +0/-5°C
Time within 5°C of actual Peak Temperature	20-40 seconds
Ramp-down Rate	6°C / second Max.
Time 25°C to Peak Temperature	8 minutes Max.

Note : All temperature refer to topside of the package, measured on the package body surface.

NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
TITLE Minitek Prw3.0 High Current Connectors		PAGE 7 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	

9 Qualification Test Sequence

Test or Examination	Test Group												
	A	B	C	D	E	F	G	H	I	J	K	L	M
	Test Sequence												
Examination of product	1, 9	1, 3	1, 7	1, 6	1, 5	1, 5	1, 5	1, 5	1, 3	1, 3	1, 3	1, 3	1, 3
Contact Resistance (Low Level)	2, 6		2, 6	2, 5	2, 4	2, 4	2, 4	2, 4					
Insulation Resistance	3, 7												
Dielectric Withstanding Voltage	4, 8												
Temperature Rise		2											
Mating Force			3										
Un-mating Force			4										
Contact Retention												2	
Crimp Retention											2		
Pin Retention													2
Durability			5										
Vibration				3									
Shock				4									
Heat Resistance					3								
Cold Resistance													
Humidity	5					3							
Temperature cycling							3						
Salt Spray								3					
Solder ability									2				
Resistance to Solder heat										2			
Sample Q'ty	5	5	5	5	5	5	5	5	5	5	5	5	5

NUMBER GS-12-1291	TYPE PRODUCT SPECIFICATION		
Minitek Prw3.0 High Current Connectors		PAGE 8 of 8	REVISION C
		AUTHORIZED BY Kenny Tai	DATE 2016-01-04
		CLASSIFICATION UNRESTRICTED	

REVISION RECORD

<u>Rev</u>	<u>Page</u>	<u>Description</u>	<u>EC#</u>	<u>Date</u>
A	All	New Release		2015-02-16
B	All	1. Change operating temp. from -25~+85°C to -40~+85°C 2. Add "Test for 3 cycles" for "Resistance to IR Reflow Heat" 3. Correct typo for test method of "Cold Resistance" from EIA-364-17 to EIA-364-59	ELX-T-20747	2015-04-23
C	All	Change mating/unmating force to 0.50Kgf/0.20Kgf Change current rating spec.	ELX-T-22932	2016-01-04