



MAX750H400S

OVERVIEW

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Thick body material
- Fully length hinges
- Nylon pins, corrosion free
- Cubed foams in the bottom and convoluted foams in the lid

Body and handle: polypropylene copolymer

Latches: nylon

Pins (for locks) : nylon + 30% fiberglass Pins (for wheels): stainless steel

COLOURS:



EXTERNAL DIMENSIONS: 816 x 540 x H426 mm (32.12 x 21.26 x H 16.77inch)

INTERNAL DIMENSIONS: 750 x 480 x H400 mm (29.52 x 18.90 x H 15.75inch)

LID-BOTTOM DEPTH: 60 + 340 mm (2.36 + 13.38 inch)

WEIGHT W/O FOAM: 12.10 kg – 26.67 Lbs

WEIGHT WITH FOAM: 13.70 kg – 30.20 Lbs

INTERNAL CUBIC VOLUME: 144000000 cubic mm - 5.08 cubic feet

VOLUME CAPACITY: 144 Lt

HANDLE CAPACITY: 50 Kg

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON W/O FOAMS: 14.40 Kg – 31.74 Lbs

WEIGHT OF THE FULL CARTON WITH FOAMS : 15.75 Kg – 34.72 Lbs

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: wheels, IP67, large fold down handle, DEF STAN 81-41, STANAG 4280

