

Safety Data Sheet

Copyright, 2015, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

This Safety Data Sheet (SDS) is provided as a courtesy in response to a customer request. This product is not regulated under, and a SDS is not required for this product by the OSHA Hazard Communication Standard (29 CFR 1910.1200) because, when used as recommended or under ordinary conditions, it should not present a health and safety hazard. However, use or processing of the product not in accordance with the product's recommendations or not under ordinary conditions may affect the performance of the product and may present potential health and safety hazards.

Document Group: 09-3272-3 **Version Number:** 9.00 05/19/15 04/19/12 **Issue Date: Supercedes Date:**

SECTION 1: Identification

1.1. Product identifier

Connectors with Hot Melt Adhesive: 6100, 6200, 6300, 8100, 8300

Product Identification Numbers

80-6111-2753-3, 80-6111-2754-1, 80-6111-2755-8, 80-6111-2757-4, 80-6111-2758-2, 80-6111-2762-4, 80-6111-2764-0, 80-6111-2758-2, 80-6111-2758-2, 80-6111-2762-4, 80-6111-2764-0, 80-6111-2758-2, 6111-2765-7, 80-6111-2766-5, 80-6111-2767-3, 80-6111-2768-1, 80-6111-4965-1, 80-6111-4966-9, 80-6111-4982-6, 80-6111-4965-1, 80-6111-496-1, 80-6111-496-1, 80-6111-496-1, 80-6111-496-1, 80-6111-496-1, 80-6111-496-1, 80-6111-496-1, 806111-4983-4, 80-6111-5381-0, 80-6111-5382-8, 80-6111-6953-5, 80-6111-7612-6, 80-6113-1349-7, 80-6113-1350-5, 80-6111-6953-5, 80-6113-1349-7, 80-6113-1350-5, 80-6113-1350-5, 80-6113-1349-7, 80-6113-1350-5, 80-6111-5, 80-61110-5, 80-61110-5, 80-61110-5, 80-61110-5, 6113-1351-3, 80-6113-1352-1, 80-6113-1429-7, 80-6113-1430-5, 80-6113-1431-3, 80-6113-1432-1, 80-6113-1433-9, 80-6113-1431-3, 80-6113-1431-6113-1434-7, 80-6113-1435-4, 80-6113-1436-2, 80-6113-1437-0, 80-6113-1438-8, 80-6113-1439-6, KQ-6106-2549-4, KQ-6111-4965-0, KQ-6111-4982-5

1.2. Recommended use and restrictions on use

Recommended use

Terminate connectors onto fiber optic cable., Secure optical fiber in fiber optic connector.

1.3. Supplier's details

MANUFACTURER: 3M

DIVISION: Communication Markets Division

ADDRESS: 3M Center, St. Paul, MN 55144-1000, USA 1-888-3M HELPS (1-888-364-3577) **Telephone:**

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

This product is exempt from hazard classification according to OSHA Hazard Communication Standard, 29 CFR 1910.1200. Combustible Dust.

2.2. Label elements

Signal word

Warning Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

Hazard Statements

May form combustible dust concentrations in air.

2.3. Hazards not otherwise classified

May cause thermal burns.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
FATTY ACID DIMER-BASED POLYAMIDE RESIN	Trade Secret*	98 - 100

^{*}The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

No need for first aid is anticipated.

Skin Contact:

Immediately flush skin with large amounts of cold water for at least 15 minutes. DO NOT ATTEMPT TO REMOVE MOLTEN MATERIAL. Cover affected area with a clean dressing. Get immediate medical attention.

Immediately flush eyes with large amounts of water for at least 15 minutes. DO NOT ATTEMPT TO REMOVE MOLTEN MATERIAL. Get immediate medical attention.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable.

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product. Powdered material may form explosive dust-air mixture. Avoid fire fighting methods that

would cause powders to become airborne.

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Eliminate all ignition sources if safe to do so. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Avoid dispersal of dust in the air (i.e., clearing dust surfaces with compressed air). Vacuum to avoid dusting. WARNING! A motor could be an ignition source and cause combustible dust in the spill area to burn or explode. Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin contact with hot material. This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Dust clouds of this material in sufficient concentration in combination with an ignition source may be explosive. Dust deposits should not be allowed to accumulate on surfaces because of the potential for secondary explosions. Routine housekeeping should be instituted to ensure that combustible dusts do not accumulate on surfaces. Solids can generate static electricity charges when transferred and in mixing operations sufficient to be an ignition source. Evaluate the need for precautions, such as grounding and bonding, low energy transfer of material (e.g. low speed, short distance), or inert atmospheres.

7.2. Conditions for safe storage including any incompatibilities

Store away from heat.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this SDS.

8.2. Exposure controls

8.2.1. Engineering controls

Provide appropriate local exhaust when product is heated. Provide local exhaust at process emission sources to control exposure near the source and to prevent the escape of dust into the work area. It is recommended that all dust control equipment (such as local exhaust ventilation), process equipment, and material transport systems involved in handling of this product be evaluated for the need for explosion-protection safeguards. Recognized safeguards include explosion relief vents, explosion suppression systems, and oxygen deficient process environments. Ensure that dust-handling systems (such as exhaust ducts, dust collectors, vessels, and processing equipment) are designed in a manner to prevent the escape of dust into the work area (i.e., there is no leakage from the equipment). Evaluate the need for electrically classified equipment.

8.2.2. Personal protective equipment (PPE)

Page 3 of 8

Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

Indirect Vented Goggles

Skin/hand protection

No chemical protective gloves are required.

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

Thermal hazards

Wear heat insulating gloves when handling hot material to prevent thermal burns.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form: Solid

Specific Physical Form:Connector with Sealant **Odor, Color, Grade:**Blue solid mild resinous odor.

Odor threshold Not Applicable pН No Data Available No Data Available **Melting point Boiling Point** Not Applicable No flash point **Flash Point** Not Applicable **Evaporation rate** Not Classified Flammability (solid, gas) Flammable Limits(LEL) Not Applicable Flammable Limits(UEL) Not Applicable **Vapor Pressure** Not Applicable Not Applicable Vapor Pressure **Vapor Density** Not Applicable **Density** Not Applicable

Specific Gravity 0.960 [Ref Std: WATER=1]

Solubility in Water Nil

Solubility- non-water Not Applicable Partition coefficient: n-octanol/ water No Data Available **Autoignition temperature** No Data Available **Decomposition temperature** Not Applicable No Data Available Viscosity No Data Available Average particle size **Bulk density** No Data Available **Hazardous Air Pollutants** No Data Available Molecular weight No Data Available **Volatile Organic Compounds** Not Applicable No Data Available Percent volatile

Softening point VOC Less H2O & Exempt SolventsNo Data Available

Not Applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Not determined

10.5. Incompatible materials

Not determined

10.6. Hazardous decomposition products

Substance

Carbon monoxide At Elevated Temperatures
Carbon dioxide At Elevated Temperatures
Oxides of Nitrogen At Elevated Temperatures
Toxic Vapor, Gas, Particulate At Elevated Temperatures

Under recommended usage conditions, hazardous decomposition products are not expected. Hazardous decomposition products may occur as a result of oxidation, heating, or reaction with another material.

Condition

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

No health effects are expected.

Skin Contact:

During heating:

Thermal Burns: Signs/symptoms may include intense pain, redness and swelling, and tissue destruction.

Page 5 of 8

Eye Contact:

During heating:

Thermal Burns: Signs/symptoms may include severe pain, redness and swelling, and tissue destruction.

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

For the component/components, either no data are currently available or the data are not sufficient for classification.

Serious Eye Damage/Irritation

For the component/components, either no data are currently available or the data are not sufficient for classification.

Skin Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

For the component/components, either no data are currently available or the data are not sufficient for classification.

Carcinogenicity

For the component/components, either no data are currently available or the data are not sufficient for classification.

Reproductive Toxicity

Reproductive and/or Developmental Effects

For the component/components, either no data are currently available or the data are not sufficient for classification.

Target Organ(s)

Specific Target Organ Toxicity - single exposure

For the component/components, either no data are currently available or the data are not sufficient for classification.

Specific Target Organ Toxicity - repeated exposure

For the component/components, either no data are currently available or the data are not sufficient for classification.

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. If no other disposal options are available, waste product may be placed in a landfill properly designed for industrial waste.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit http://3M.com/Transportinfo or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 Flammability: 1 Instability: 0 Special Hazards: None

Page 7 of 8

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 0 Flammability: 1 Physical Hazard: 0 Personal Protection: X - See PPE section.

Hazardous Material Identification System (HMIS® III) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® III ratings are to be used with a fully implemented HMIS® III program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group: 09-3272-3 **Version Number:** 9.00 **Issue Date:** 05/19/15 **Supercedes Date:** 04/19/12

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com