



TECHNICAL DATA SHEET

Releasable Cable Ties

**RoHS
Compliant**

Materials Used:	
Main component	Nylon 66, 94V-2 certificated by UL
Main Features	
Heat, acid and erosion resistant. Good insulation Releasable	

ITEM No	Length (mm)	Width (mm)	Max Bundle Dia (mm)	Tensile Strength		Colour
				Lbs	Kgs	
CB14723	300	7.5	75	50	22	Natural
CBBR7722	150	7.2	35	50	22	Black
CBBR7723	150	7.2	35	50	22	Black
CBBR7724	200	7.2	50	50	22	Black
CBBR7725	250	7.5	60	50	22	Black
CBBR7726	300	7.2	80	50	22	Black
CBBR7727	150	7.2	35	50	22	Natural
CBBR7728	150	7.2	35	50	22	Natural
CBBR7729	200	7.2	50	50	22	Natural
CBBR7731	300	7.2	80	50	22	Natural



Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.