Product data sheet Characteristics

XB4BP31EX

green pushbutton Ø 22 - spring return - 1 NO - ATEX



Main

| Range of product | Harmony XB4 | : |
|---------------------------------|------------------------|---|
| Product or component type | Complete push-button | |
| Device short name | XB4 | |
| Bezel material | Chromium plated metal | |
| Fixing collar material | Zamak | |
| Mounting diameter | 22 mm | |
| Sale per indivisible quantity | 1 | |
| Dust zone | Zone 21 - 22 | |
| Type of operator | Spring return | |
| Operator profile | Green projecting | : |
| Operator additional information | Booted (clear silicon) | |
| Contacts type and composition | 1 NO | |

Complementary

| Desistance to bish successor weeken | 7000000 D+ FF %C -+ 0.4 | |
|-------------------------------------|---|--|
| Resistance to high pressure washer | 7000000 Pa at 55 °C at 0.1 m | |
| Device mounting | Fixing hole Ø 22.5 mm (22.3 +0.4/0) conforming to EN/IEC 60947-1 | |
| Fixing center | >= 30 x 40 mm on support panel | |
| Embedding depth | 43 mm | |
| Marking | Ex tb IIIC | |
| Shape of signaling unit head | Round | |
| Contact operation | Slow-break | |
| Positive opening | Without | |
| Operating travel | 2.6 mm (NO changing electrical state) | |
| | 4.3 mm (total travel) | |
| Operating force | 3.8 N (NO changing electrical state) | |
| Mechanical durability | 5000000 cycles | |
| Connections - terminals | Screw clamp terminals, clamping capacity: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 | |
| | Screw clamp terminals, clamping capacity: $1 \times 0.222 \times 2.5 \text{ mm}^2$ without cable end conforming to EN/IEC 60947-1 | |
| Tightening torque | 0.81.2 N.m conforming to EN 60947-1 | |
| Shape of screw head | Cross head compatible with Philips no 1 screwdriver | |
| | Cross head compatible with pozidriv No 1 screwdriver | |

| | Slotted head compatible with flat Ø 4 mm screwdriver Slotted head compatible with flat Ø 5.5 mm screwdriver | |
|---|---|--|
| Contacts material | Silver alloy (Ag/Ni) | |
| Short-circuit protection | 10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1 | |
| [lth] conventional free air thermal current | 10 A conforming to EN/IEC 60947-5-1 | |
| [Ui] rated insulation voltage | 600 V (degree of pollution: 3) conforming to EN/IEC 60947-1 | |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-1 | |
| [le] rated operational current | 3 A at 240 V AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V AC-15, A600 conforming to EN/IEC 60947-5-1 | |
| Electrical durability | 1000000 cycles AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1: appendix C 1000000 cycles AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1: appendix C 1000000 cycles AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1: appendix C 1000000 cycles DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1: appendix C 1000000 cycles DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1: appendix C | |
| Electrical reliability | Λ < 10exp(-6) at 5 V and 1 mA in clean environment conforming to EN/IEC 60947-5-4 Λ < 10exp(-8) at 17 V and 5 mA in clean environment conforming to EN/IEC 60947-5-4 | |

| Protective treatment | TH |
|---------------------------------------|---|
| Ambient air temperature for storage | -4070 °C |
| Ambient air temperature for operation | -4070 °C |
| Overvoltage category | I conforming to IEC 60536 |
| IP degree of protection | IP67 IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 13 NEMA 4X |
| IK degree of protection | IK03 conforming to IEC 50102 |
| Standards | EN 50014 EN 50281-1-1 IEC 61241-0 IEC 61241-1 |
| Directives | 94/9/EC - ATEX directive |
| Product certifications | DNV GL INERIS 04ATEX9004U |
| Vibration resistance | 5 gn (f = 2500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |


Contractual warranty

| Warranty period 18 months |
|---------------------------|
|---------------------------|

Product data sheet Dimensions Drawings

XB4BP31EX

Pushbutton



e: support thickness: 1 to 6 mm / 0.04 to 0.24 in.

XB4BP31EX

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

| Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board | Connection by Faston Connectors |
|---|---------------------------------|
| (2) | (5) |

- Diameter on finished panel or support
- 40 mm min. / 1.57 in. min.
- 30 mm min. / 1.18 in. min.
- (1) (2) (3) (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0$ $^{+0.4}$ / 0.88 in. $_0$ $^{+0.016})$
- (5) (6) 45 mm min. / 1.78 in. min.
- 32 mm min. / 1.26 in. min.