Keysight Technologies U1610A/U1620A Handheld Digital Oscilloscope

Data Sheet







Introduction

Retool your expectations in the world's first VGA display handheld oscilloscope with two isolated channels

The Keysight Technologies, Inc. U1610A/U1620A is the world's first handheld oscilloscope with a VGA display. This 100/200 MHz handheld oscilloscope offers a floating measurement capability with two CAT III 600 V isolated channels. With up to 2 GSa/s sam- pling rate and 2 Mpts memory depth, it captures more waveforms from signals such as pulse width modulated circuit, in rush, transient, and motor start up sequences. The benchtop-like display and dual window zoom allow you to easily identify problem areas and zoom in for more detailed analysis. Now, you can view signals in detail and detect glitches easily.

Features

- 100/200 MHz bandwidth with two isolated channels
- 5.7-inch VGA TFT LCD display with 3 selectable viewing modes (indoor, outdoor and night vision)
- 2 Mpts memory depth and 2 GSa/s sampling rate allows detailed analysis of captured glitches
- 10,000-count resolution on DMM display
- Channel-to-channel isolation with CAT III 600 V safety ratings
- Data logging capability to PC
- 10 selectable languages on the User Interface (UI) system

5.7-inch VGA display with 3 selectable viewing modes

Visualizing electrical waveforms has never been in such clarity. Our U1610A/U1620A oscilloscope comes with a 5.7-inch VGA TFT LCD display that enables clear viewing of measurements on-site and on the field. With the option of up to three viewing modes, users can now view waveforms under all lighting conditions, including in indoor, outdoor or dark environ- ments. All three viewing modes have predefined contrast levels for customized lighting conditions and optimized battery life.

Indoor mode

The indoor mode has high contrast and brightness levels to clearly distinguish waveforms under an indoor light environment. Engineered with a VGA TFT LCD screen, users can now view the display across wide viewing angles for more efficient troubleshooting task.

Outdoor mode

When performing field work in an outdoor environment, users can easily switch to this viewing mode via a set of accessible soft keys. This mode works in an anti-glare mechanism; it filters out excessive sunlight, hence reducing the risk of misreading or misinterpreting measurements.

Night vision mode

The night vision mode is tailored to be viewable under subdued lighting by enabling high contrast levels between the screen background and waveforms. With a single press of button, this mode is activated and the screen automatically adjusts with proper colour correction-creating clear contrasts between the waveforms against the dark environment. This mode is useful when measuring high speed signals, particularly in nonrepetitive signals.



Figure 1. Indoor mode for clear distinct readings



Figure 2. Outdoor mode that is sunlight viewable



Figure 3. Night vision mode for performing tasks in a poorly lit environment

2 Mpts memory depth and 2 GSa/s sampling rate allows detailed analysis of captured glitches

A good oscilloscope must be accompanied with even better specifications for an in-depth analysis of captured glitches. With deep memory of 2 Mpts and sampling rate of 2 GSa/s, non-repeating signals can be captured over a wider time base. What's more, its dual window zoom feature allows you to work more productively by simultaneously viewing signals captured over a period of time and zooming into the most subtle details.


Channel-to-channel isolation with CAT III 600 V safety ratings

The U1610/U1620A extends the maximum input rating to cater for high voltage measurement and transient voltages which are recordable via a handheld oscilloscope. Equipped with the most robust isolation topology, technicians can now mea- sure signals in the field and perform floating measurements. This type of isolation enables each channel to be individually isolated from one another and from other non-isolated system components.

Up to 10 selectable languages programmed in the scope

The U1610A/U1620A is programmed with up to 10 selectable languages (English, French, German, Italian, Spanish, Portuguese, Traditional and Simplified Chinese, Japanese and Korean) on the User Interface (UI) system and help menu. The diverse range of languages offered here gives users the choice to operate the unit in the language that they are most comfortable in.

Front panel description



Outdoor viewing mode as illustrated

Figure 4. The U1620A as shown

Specifications

	U1610A	U1620A		
Specification				
Vertical system				
Bandwidth (-3 dB) ¹	100 MHz	200 MHz		
DC vertical gain accuracy ¹	± 4% of	full scale		
	Full scale is eq	uivalent to 8 div		
Dual cursor accuracy ¹	± {DC vertical gain accuracy + 0.4% f	ull scale (~1 least significant bit (LSB)}		
	± {4% full scale ± 0.4	% full scale (~1 LSB)}		
Characteristic				
Acquisition				
Maximum Sampling Rate				
Single Chanel Operation	1 GSa/s interleave	2 GSa/s interleave		
Dual Channel Operation	500 MS/s each channel	1 GS/s each channel		
Maximum Recording Length				
Single Chanel Operation	120 Kpts interleave	2 Mpts interleave		
Dual Channel Operation	60 Kpts each channel	1 Mpts each channel		
Vertical resolution		oits		
Peak detection	> 10 ns	> 5 ns		
Average	Selectable from 2 to 8192 in powers-of-2 increments			
Filter	10 kHz and 20 MH	z bandwidth limiters		
Interpolation	(Sin x)/x			
Vertical system				
Analog channels	Channel 1 and Channel 2 simultaneous acquisition			
Calculated rise time	3.50 ns typical 1.75 ns typical			
Vertical scale	2 mV/div to 50 V/div			
Maximum input	CAT III 600 V (with 10:1 probe)			
<u> </u>	CAT III 30	0 V (direct)		
Offset (position) range	± 4	div		
Dynamic range		3 div		
Input impedance		≈ 22 pF ± 3 Pf		
Coupling		, AC		
Bandwidth limit	10 kHz and 20	MHz (selectable)		
Channel-to-channel isolation (with channels at the same V/div)	CAT II	I 600 V		
Probes	U1560-60002 1:1 passive probe			
	U1561-60002 1	0:1 passive probe		
	U1562-60002 10	0:1 passive probe		
Probe attenuation factors	1x, 10x, 100x			
Probe compensation output	5 V _{pp} ;	1 kHz		
Noise peak-to-peak (typical)	3% of full scale or 5 n	nV _{pp} , whichever greater		
DC vertical offset (position) accuracy	$\pm 0.1 \text{ div } \pm 2 \text{ mV}$	±1.6% offset value		
0: 1	± {DC vertical gain accuracy + DC vertic	al offset accuracy + 0.2% full scale (~1/2		
Single cursor accuracy		ant bit (LSB)}		

Specifications (continued)

	U1610A	U1620A		
Characteristic (continued)				
Horizontal system				
Range	5 ns/div to 50 s/div	2 ns/div to 50 s/div		
Resolution	100 ps for 5 ns/div	40 ps for 2 ns/div		
Timebase accuracy	25 р	pm		
Reference position	Left, cent	er, right		
Delay range (pre-trigger)	1 screen width or 120 μs (whichever less)	1 screen width or 1 ms (whichever less)		
Delay range (post-trigger)	50 ms to 500 s	20 ms to 500 s		
Delay resolution	100 ps for 5 ns/div	40 ps for 2 ns/div		
Delay time measurement accuracy	Same channel: ± 0.0025% readin	g ± 0.17% screen width ± 60 ps		
	Channel-to-channel: ± 0.0025% read	ding ± 0.17% screen width ± 120 ps		
Modes	Main, zoor	n, XY, roll		
Horizontal pan and zoom	Dual wind	ow zoom		
Trigger system				
Sources	Channel 1, Char	nnel 2, External		
Modes	Normal, Sir	ngle, Auto		
Types	Edge, Glitch, TV, N	th Edge, CAN, LIN		
Autoscale	Finds or displays active channels, sets the edge trigger type on the highest numbered channel, and sets the vertical sensitivity on the scope channel timebase to display ~2 periods			
	Requires > 10 mV _{pp} minimum voltage, 0.5% duty cycle, and > 50 Hz minimum frequency			
Holdoff time	60 ns to 10 s			
Range	± 6 div from center of screen			
Sensitivity	≥ 10 mV/div: 0.5 div			
	< 10 mV/div: greate	er of 1 div or 5 mV		
Trigger level accuracy	± 0.6	div		
Coupling modes	AC (~10 Hz), DC, LF-Reject (~35 kHz), HF-Reject (~35 kHz)			
External trigger				
- Input impedance	1 MΩ ≈ 10 pF			
- Maximum input	CAT III	300 V		
- Range	DC coupling: trig	gger level ± 5 V		
- Bandwidth	100	kHz		
Measurement				
Automatic measurements	Delay, duty cycle (+/-), fall/rise time, f T-min, width (+/-), amplitude, average minimum, overshoot, peak-to-peak, pr (AC/DC), active/apparent/reactive po U1583B/1146A), DC (e, base, crest, cycle mean, maximum, eshoot, standard deviation, top, Vrms ower, power factor AC current (with		
Waveform math functions	CH1 + CH2, CH1 - CH2, CH2 - CH1, C (CH1), d/dt (CH2), ∫(C			
Cursors	Delta V: Voltage difference between cursors			
	Delta T: Time differen			
EET ' ·	102	2/4		
FFT points	102	<u> </u>		

Specifications (continued)

	U1610A	U1620A
Characteristic (continued)		
Display system		
Display	5.7" TFT LCD VGA Color	(outdoor readable)
Resolution	VGA (screen area): 640 ver	tical by 480 horizontal
Control	Vectors on/off, sin x/x interpolation on/off intensity, color scher	
Real-time clock	Date and time (adjustable)
Language	10 languages (selectable)
Built-in help system	Functional quick help displayed b	by pressing the [Help] button
Storage system		
Save/recall (non-volatile)	10 setups and waveforms can be	saved and recalled internally
Storage mode	USB 2.0 full speed host port (Su	pport up to 4GB USB drive)
	Image formats: .bmp (8-bit, 2	24-bit) and .png (24-bit)
	Data forma	at: .csv
1/0	USB 2.0 full-speed host, US	SB 2.0 full-speed client
Printer compatibility	PCL Inkjet, P	CL Laser

^{1.} Denotes warranted specifications, all others are typical. Specifications are valid after a 30-minute warm-up period and within 23 \pm 10 °C of last calibration temperature.

Maximum input voltages and channel isolation

U1610A and U1620A
300 V CAT III
600 V1 CAT III, 1000 V1 CAT II
600 V1 CAT II, 1000 V1 CAT II, 3540 V1 CAT I
600 V CAT III, 1000 V CAT II
300 V CAT III
Vrms 50-60 Hz (AC sine wave), VDC (DC applications)
600 Vrms CAT III

1. Refer to the respective probe's manual for more information on the specification




Figure 5. Maximum safety voltage for scope reference to earth




Figure 6. Maximum input voltage

Digital multimeter specifications

- Accuracy is given as ± (% of reading + counts of least significant digit) at 23 ± 5 °C, with relative humidity < 80 RH.
- AC V specifications are AC coupled, true RMS and are valid from 5% to 100% of range.
- Temperature coefficient is given as 0.1 × (specified accuracy) / °C (from 0 to 18 °C or 28 to 50 °C).
- Common mode rejection ratio (CMRR) is > 90 dB at DC, 50/60 Hz \pm 0.1% (1 k Ω unbalanced).
- Normal mode rejection ratio (NMRR) is > 60 dB at 50/60 Hz ± 0.1%.

Maximum reading Voltage ¹		10,000	counts with automatic polarity in	dication	
voitage	Input impedance				
Function	Range	Resolution	Accuracy	(nominal)	Test current
DCV	100.00 mV ²	0.01 mV	0.1% + 5	> 1 G Ω	
	1000.0 mV	0.1 mV	0.09% + 5	11.11 MΩ	-
	10.000 V	0.001 V	0.000/	10.10 ΜΩ	-
	100.00 V	0.01 V	- 0.09% + 2	10.01.140	-
	1000.0 V ³	0.1 V	0.15% + 5	10.01 M Ω	
ACV	100.0 mV	0.01 mV	1% + 5 (40 Hz to 2 kHz)	> 1 G Ω	
	1000 0>/	0.1	1% + 5 (40 to 500 Hz)		-
	1000.0 mV	0.1 mV	2% + 5 (500 Hz to 1 kHz)		
	10.000 V 100.00 V	0.001 V 0.01V	1% + 5 (40 to 500 Hz)		
			1% + 5 (500 Hz to 1 kHz)	10.00 ΜΩ	
	100.00 V	0.01	2% + 5 (1 to 2 kHz)		
	1000.0 V ³ 0.1 V	0.1 \/	1% + 5 (40 to 500 Hz)		
	1000.0 V	0.1 V	1% + 5 (500 Hz to 1 kHz)		
ACV + DC V	100.0 mV ²	0.01 mV	1.1% + 5 (40 Hz to 2 kHz)	> 1 GΩ -	
			1.1% + 10 (40 to 500 Hz)		
	1000.0 mV	0.1 mV	2.1% + 10 (500 Hz to 1 kHz)		
	10.0001/	0.001.1	1.1% + 7 (40 to 500 Hz)		
	10.000 V 0.001 V 100.00 V 0.01 V	0.001 V 0.01 V	1.1% + 7 (500 Hz to 1 kHz)	10.00 ΜΩ	
	100.00 V	100.00 V 0.01 V	2% + 5 (1 to 2 kHz)		
			1.2% + 10 (40 to 500 Hz)		
	1000.00 V ³	0.1 V	1.2% + 10 (500 Hz to 1 kHz)		
Diode ⁴	1 V	0.001 V	0.3% + 2		~0.5 mA

Beeper < ~50 mV, single tone for normal forward-biased diode or semiconductor junction of 0.3 V \le reading \le 0.8 V 5 Overload protection: 1000 Vrms for short circuit with < 0.3 A

Open voltage: < +2.8 VDC

- 1. Only allowed to measure up to CAT III 600 V if referring to GND.
- 2. In an open connection, the reading shown on the display is noise pickup due to the high input impedance at the input terminal.
- 3. Only allowed for floating voltage
- 4. Denotes typical specifications, all others are warranted.
- 5. Denotes characteristics.
- 6. The accuracy is specified after the Null function is used to subtract the test lead resistance and thermal effect.
- 7. RH is specified for < 60%. The temperature coefficient is 0.15 \times specified accuracy as > 50 M Ω .
- 8. The accuracy is based on film capacitors or better and uses the Relative mode for residual values.

NOTE: Keysight recommends using the U1586B temperature adapter for temperature measurement. Refer to http://literature.cdn.keysight.com/litweb/pdf/5990-9523EN for more information on the U1586B specifications.

Digital multimeter specifications (continued)

Maximum reading		,	10,000 counts with automatic polarity indicatio	n	
Voltage ¹			CAT II 1000 V or CAT III 600 V		
Function	Range	Resolution	Accuracy	Input impedance (nominal)	Test current
Instant continuity ⁴			Continuous beep when resistance < 10 Ω^{5}		
Resistance	1000.00 Ω ⁶	0.1 Ω			0.5 mA
	10.000 kΩ ⁶ 0.001 kΩ	0.20/ . 2		50 μΑ	
	100.00 k Ω	0.01 k Ω	- 0.3% + 3 -		4.91 μΑ
	1000.0 k Ω	0.1 k Ω			447 nA
	10.000 M Ω	0.001 M Ω	0.8% + 3		112 nA
	100.00 M Ω ⁷	0.01 M Ω	1.5% + 3		112 nA
Capacitance	1000.0 nF	0.1 nF			
	10.000 μF	0.001 μF	1.2% + 48		
	100.00 μF	0.01 μF		_	
-	1000.0 μF	0.1 μF	- 2% + 4 ⁸		
	10.000 mF	0.001 mF			
Frequency ⁴	equency ⁴ 100.00 Hz 0.01 Hz	_			
	1000.0 Hz	0.1 Hz	_		
	10.000 kHz	0.001 kHz	0.03% + 3		
	100.00 kHz	0.01 kHz	_		
	1000.0 kHz	0.1 kHz			

- 1. Only allowed to measure up to CAT III 600 V if referring to GND.
- 2. In an open connection, the reading shown on the display is noise pickup due to the high input impedance at the input terminal.
- 3. Only allowed for floating voltage.
- 4. Denotes typical specifications, all others are warranted.
- 5. Denotes characteristics.
- 6. The accuracy is specified after the Null function is used to subtract the test lead resistance and thermal effect.
- 7. RH is specified for < 60%. The temperature coefficient is $0.15 \times \text{specified}$ accuracy as > $50 \text{ M}\Omega$.
- 8. The accuracy is based on film capacitors or better and uses the Relative mode for residual values.

NOTE: Keysight recommends using the U1586B temperature adapter for temperature measurement. Refer to http://literature.cdn.keysight.com/litweb/pdf/5990-9523EN for more information on the U1586B specifications.

Data logger specifications

	Scope and meter logger	
Range	1 s/div - 86400 s/div (1 day/div)	
Recording time span	8 days	
Memory depth	691200 points	
Recording mode	Continuous (Range will change according to the time elapsed)	
Sampling rate	1 sample/s	

General specifications

Power supply	
Power adapter	Line voltage range: 50/60 Hz, 100 to 240 VAC, 1.6 A
	Output voltage: 15 VDC, 4 A
	Installation Category II
Battery	Li-Ion rechargeable battery pack, 10.8 V
	Operating time: Up to 3 hours
Operating environment	
Temperature	0 to 50 °C (with battery only)
	0 to 40 °C (with power adapter)
Humidity	0 to 80% RH (0 to 35 °C)
	0 to 50% RH (35 to 40/50 °C)
	Altitude up to 2000 m
	Pollution degree 2
Storage compliance	
Temperature	-20 to 70 °C
Humidity	0 to 80% RH
	Altitude up to 15000 m
Shock	Tested to IEC 60068-2-27
Vibration	Tested to IEC 60068-2-6, IEC 60068-2-64
Safety compliance	IEC 61010-1:2001/EN 61010-1:2001
	Canada: CAN/CSA-C22.2 No. 61010-1-04
	USA: ANSI/UL 61010-1:2004
EMC compliance	IEC 61326-1:2005/EN 61326-1:2006
	Australia/New Zealand: AS/NZS CISPR 11:2004
	Canada: ICES/NMB-001:ISSUE 4, June 2006
IP rating	IP 41 ingress protection according to IEC 60529
Dimensions (W × H × D)	183 x 270 x 65 mm
Weight	< 2.5 kg
Warranty	3 years for main unit
	3 months for standard shipped accessories unless otherwise stated

Ordering information

Standard shipped items

 Quick start guide, power adapter, Li-Ion battery pack, USB cable, test lead, 10:1 probe (2 sets), Certificate of Calibration (CoC).

Recommended accessories

Item

1146B

Probe - 100 kHz, 100A AC/DC current probe

U1161A

Test lead kit, extended



U1162A

Alligator clip



U1163A

Grabbers, SMT



U1164A

Test probes, fine tip



U1168B

Test lead kit



U1169A

Test probe leads (with 19-mm tips and 4-mm tips)

U1176A

LED flash light

U1554B

Probe tip, CAT III 1000V, CAT IV 600V



U1560B

Scope probe - X1, CAT III 600V



U1561B

Scope probe - X10, CAT III 1000V



Item

U1562B

Scope probe - X100, CAT III 1000V



U1572A

Li Polymer battery pack



U1573A

Desktop charger and Li Polymer battery pack





U1574A

AC/DC adapter

U1575A

Desktop charger



U1577A

USB cable

U1580A

DMM terminal test lead set



U1583B

AC current clamp

U1586B

Temperature module

U1591A


Soft carrying case



Evolving

Our unique combination of hardware, software, support, and people can help you reach your next breakthrough. We are unlocking the future of technology.







From Hewlett-Packard to Agilent to Keysight

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

Keysight Infoline

Keysight Infoline

www.keysight.com/find/Infoline

Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

KEYSIGHT SERVICES **Keysight Services**

www.keysight.com/find/service

Our deep offering in design, test, and measurement services deploys an industry-leading array of people, processes, and tools. The result? We help you implement new technologies and engineer improved processes that lower costs.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/handheldscope

www.keysight.com/find/U1600

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada (877) 894 4414 Brazil 55 11 3351 7010 Mexico 001 800 254 2440 United States (800) 829 4444

Asia Pacific

Australia 1 800 629 485 China 800 810 0189 800 938 693 Hong Kong 1 800 11 2626 India Japan 0120 (421) 345 080 769 0800 Korea Malaysia 1 800 888 848 Singapore 1 800 375 8100 Taiwan 0800 047 866 Other AP Countries (65) 6375 8100

Europe & Middle East

For other unlisted countries: www.keysight.com/find/contactus (BP-06-08-16)

Opt. 3 (IT)

0800 0260637



United Kingdom

www.keysight.com/go/quality

Keysight Technologies, Inc. DEKRA Certified ISO 9001:2015 Quality Management System



This information is subject to change without notice. © Keysight Technologies, 2013 - 2016 Published in USA, September 12, 2016 5990-9523EN

www.keysight.com