

<u>Spec No.JELF243C-0009J-01</u> P.1/9

# CHIP COIL (CHIP INDUCTORS) LQP18MN□□□□02D Reference Specification

#### 1.Scope

This reference specification applies to LQP18MN\_02 series, Chip coil (Chip Inductors).

2.Part Numbering (ex) LQ

LQ P 18 M N 1N3 C 0 2 D

Product ID Structure Dimension Applications (L×W) and Characteristics Category Characteristics Category Inductance Tolerance Features Electrode Packaging D:Taping \*B:Bulk

Bulk packing also available. (A product is put in the plastic bag under the taping conditions.)

#### 3.Rating

Operating Temperature Range. –40

-40°C to +85°C

(Ambient temperature : Rated current can be handled in this temperature range.)

•Storage Temperature Range. -40°C to +85°C

Customer	MURATA	Inductance		Q	DC Resistance	Self Resonant Frequency	Rated Current
Part Number	Part Number	(nH)	Tolerance	(min.)	(Ω max.)	(MHz min.)	(mA)
	LQP18MN1N3C02D	1.3			0.3		300
	LQP18MN1N5C02D	1.5			0.3		300
	LQP18MN1N8C02D	1.8				6000	
	LQP18MN2N2C02D	2.2			0.4	6000	050
	LQP18MN2N7C02D	2.7					250
	LQP18MN3N3C02D	3.3	±0.2nH				
	LQP18MN3N9C02D	3.9			٥٢	5900	
	LQP18MN4N7C02D	4.7			0.5	5200	200
	LQP18MN5N6C02D	5.6		-	0.6	4700	200
	LQP18MN6N8C02D	6.8			0.7	4300	
	LQP18MN8N2C02D	8.2			0.8	3600	
	LQP18MN10NG02D	10		17	4.0	3400	450
	LQP18MN12NG02D	12			1.0 3000	150	
	LQP18MN15NG02D	15			1.3	2700	
	LQP18MN18NG02D	18			1.5	2300	
	LQP18MN22NG02D	22			1.9	2100	
	LQP18MN27NG02D	27			2.4	1900	400
	LQP18MN33NG02D	33	±2%	±2%	0.0	1700	100
	LQP18MN39NG02D	39			2.8	1400	
	LQP18MN47NG02D	47			2.2	1200	
	LQP18MN56NG02D	56	]		3.4	1000	
	LQP18MN68NG02D	68	]		3.5	900	50
	LQP18MN82NG02D	82	]		4.6	800	50
	LQP18MNR10G02D	100	]		6.1	700	

#### 4. Testing Conditions

《Unless otherwise specified》 《In case of doubt》


Temperature : Ordinary Temperature / 15°C to 35°C Temperature : 20°C ± 2°C

Humidity : Ordinary Humidity / 25%(RH) to 85 %(RH) Humidity : 60%(RH) to 70 %(RH)

Atmospheric Pressure: 86kPa to 106 kPa

P.2/9

# 5. Appearance and Dimensions



# **6.Electrical Performance**

No.	Item	Specification	Test Method
6.1	Inductance	Inductance shall meet item 3.	Measuring Equipment:     Agilent4291A or equivalent Measuring Frequency:     500MHz / 1.3nH to 39nH     300MHz / 47nH to 100nH Measuring Condition:     Test signal level / about 7dBm     Electrical length / 0.94cm     Weight / about 1N to 5N Measuring Fixture: Agilent 16193A
6.2	Q	Q shall meet item 3.	Position coil under test as shown in below and contact coil with each terminal by adding weight. Coil pattern should be a topside, and inner end of the coil should be in the direction of the fixture for
			position of chip coil.  o Inner end of the coil.  6.97mm Measuring Method: See P.9
			<electrical measuring<br="" performance:="">Method of Inductance/Q&gt;</electrical>
6.3	DC Resistance	DC Resistance shall meet item 3.	Measuring Equipment: Digital multi meter
6.4	Self Resonant Frequency(S.R.F)	S.R.F shall meet item 3.	Measuring Equipment: Agilent 8753C or equivalent
6.5	Rated Current	Self temperature rise shall be limited to 25°C max.	The rated current is applied.

# 7.Mechanical Performance

No.	Item	Specification	Test Method
7.1	Shear Test	Chip coil shall not be damaged	Substrate: Glass-epoxy substrate
		after tested as test method.	Land
			1.0 0.6 1.0 (in mm)
			Force:10N
			Hold Duration:5s±1s
			Applied Direction: Parallel to PCB.
			Chip Coil
			F F
			Substrate
	D # = :		
7.2	Bending Test	Chip coil shall not be damaged after tested as test method.	Substrate: Glass-epoxy substrate (100mm × 40mm × 1.6mm)
		and tested as test method.	(100111111 ^ 40111111 ^ 1.0111111)
			<u> </u>
			0.6
			2.6
			100 Solder resist
			(in mm)
			Speed of Applying Force:1mm / s
			Deflection:2mm Hold Duration:30s
			Pressure jig
			R340 F
			Deflection
			Deniesion
			45 45 Draduct
			k → → → Product
			(in mm)
7.3	Vibration	Appearance: No damage	Oscillation Frequency:
		Inductance Change:±10% within	10Hz to 55Hz to 10Hz for 1 min
			Total Amplitude:1.5mm
			Testing Time: A period of 2 hours in each of
7.4	Caldanah 225	The matting area of the electrical	3 mutually perpendicular directions.
7.4	Solderability	The wetting area of the electrode	Flux: Ethanol solution of rosin 25(wt)%
		shall be at least 95% covered with	(Immersed for 5s to 10s) Solder:Sn-3.0Ag-0.5Cu
		new solder coating.	Pre-Heating:150°C±10°C / 60s to 90s
		Pattern side Chip coil	Solder Temperature:240°C±5°C
			Immersion Time:3s±1s
		<del>\</del>	
		The wetting area of the electrode	
		•	

<u>Spec No.JELF243C-0009J-01</u> P.4/9

No.	Item	Specification	Test Method
7.5	Resistance to	Appearance: No damage	Flux: Ethanol solution of rosin 25(wt)%
	Soldering Heat	Inductance Change:±10% within	(Immersed for 5s to 10s)
			Solder:Sn-3.0Ag-0.5Cu
			Pre-Heating:150°C±10°C / 60s to 90s
			Solder Temperature:270°C±5°C
			Immersion Time:10s±1s
			Then measured after exposure in the room
			condition for 24h±2h.


#### **8.Environmental Performance**

It shall be soldered on the substrate

No.	Item	Specification	Test Method
8.1	Heat Resistance	Appearance: No damage Inductance Change:±10% within	Temperature:85°C±2°C Time:1000h (+48h0h)
		inductance change.±10% within	Then measured after exposure in the room condition for 24h±2h.
8.2	Cold Resistance		Temperature:-40°C±2°C Time:1000h (+48h0h) Then measured after exposure in the room condition for 24h±2h.
8.3	Humidity		Temperature:40°C±2°C Humidity:90%(RH) to 95%(RH) Time:1000h (+48h0h) Then measured after exposure in the room condition for 24h±2h.
8.4	Temperature Cycle		1 cycle: 1 step:-40°C±2°C / 30min±3 min 2 step: Ordinary temp. / 10 min to 15 min 3 step:+85°C±2°C / 30min±3 min 4 step: Ordinary temp. / 10min to 15 min Total of 10 cycles Then measured after exposure in the room condition for 24h±2h.

## 9. Specification of Packaging

9.1 Appearance and Dimensions of paper tape (8mm-wide)



### 9.2 Specification of Taping

- (1) Packing quantity (standard quantity) 4,000 pcs / reel
- (2) Packing Method

Products shall be packed in the cavity of the base tape and sealed by top tape and bottom tape.

(3) Sprocket hole

The sprocket holes are to the right as the tape is pulled toward the user.

(4) Spliced point

Base tape and Top tape has no spliced point.

#### P.5/9

# Reference Only

#### (5) Missing components number


Missing components number within 0.1 % of the number per reel or 1 pc., whichever is greater, and are not continuous. The Specified quantity per reel is kept.

#### 9.3 Pull Strength

Top tape	5N min.
Bottom tape	314 111111.


#### 9.4 Peeling off force of cover tape

Speed of Peeling off	300mm/min	
Dealing off force	0.1N to 0.6N	
Peeling off force	(minimum value is typical)	



#### 9.5 Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape (top tape and empty tape) and trailer-tape (empty tape) as follows.



## 9.6 Marking for reel

Customer part number, MURATA part number, Inspection number(\*1) , RoHS Marking (\*2), Quantity etc  $\cdots$ 

- \*1) < Expression of Inspection No.>
- $\begin{array}{c|c} \square \square & OOOO \\ \hline (1) & (2) & \hline (3) \end{array}$

- (1) Factory Code
- (2) Date First digit : Year / Last digit of year

Second digit : Month / Jan. to Sep.  $\rightarrow$  1 to 9, Oct. to Dec.  $\rightarrow$  O,N,D

Third, Fourth digit: Day

(3) Serial No.

\*2) <Expression of RoHS Marking >


ROHS 
$$-\underline{Y}(\underline{\Delta})$$

- (1) RoHS regulation conformity parts.
- (2) MURATA classification number

#### 9.7 Marking for Outside package (corrugated paper box)

Customer name, Purchasing order number, Customer part number, MURATA part number, RoHS Marking (\*2) ,Quantity, etc  $\cdots$ 

#### 9.8. Specification of Outer Case



l	Outer Case Dimensions (mm)			Standard Reel Quantity in Outer Case (Reel)
	W	D	Н	,
	186	186	93	5

\* Above Outer Case size is typical. It depends on a quantity of an order.

Spec No.JELF243C-0009J-01 P.6/9

# 10. 🛕 Caution

#### **Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment(2) Aerospace equipment
- (3) Undersea equipment
- Power plant control equipment
- (5) Medical equipment
- (6) Transportation equipment (vehicles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment (8)
- (9) Data-processing equipment
- (10) Applications of similar complexity and /or reliability requirements to the applications listed in the above


#### 11. Notice

Products can only be soldered with reflow.

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

#### 11.1 Land pattern designing



#### 11.2 Flux, Solder

·Use rosin-based flux.

Don't use highly acidic flux with halide content exceeding 0.2(wt)% (chlorine conversion value).

Don't use water-soluble flux.

- ·Use Sn-3.0Ag-0.5Cu solder.
- ·Standard thickness of solder paste :  $100 \mu$  m to  $150 \mu$  m.

#### 11.3 Reflow soldering conditions


·Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 150°C max. Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max.

Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of products quality.

·Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.

·Reflow soldering profile



	Standard Profile	Limit Profile
Pre-heating	150°C~180°C	C ,90s±30s
Heating	above 220°C, 30s∼60s	above 230°C, 60s max.
Peak temperature	245°C±3°C	260°C,10s
Cycle of reflow	2 times	2 times

# Reference Only

#### 11.4 Reworking with soldering iron.


The following conditions must be strictly followed when using a soldering iron.

Pre-heating	150°C,1 min
Tip temperature	350°C max.
Soldering iron output	80W max.
Tip diameter	Ф3mm max.
Soldering time	3(+1,-0)s
Times	2 times

Note: Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the products due to the thermal shock.

#### 11.5 Solder Volume

· Solder shall be used not to be exceeded the upper limits as shown below.




Accordingly increasing the solder volume, the mechanical stress to Chip is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.

#### 11.6 Attention regarding P.C.B. bending

The following shall be considered when designing and laying out P.C.B.'s.


(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board.

[Products direction]



Products shall be located in the sideways direction (Length: a < b) to the mechanical stress.

(2) Products location on P.C.B. separation



Products (A,B,C,D) shall be located carefully so that products are not subject to the mechanical stress due to warping the board. Because they may be subjected the mechanical stress in order of  $A>C>B\cong D$ .

#### 11.7 Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60°C max.(40°C max for IPA)
- (2) Ultrasonic cleaning shall comply with the following conditions with avoiding the resonance phenomenon at the mounted products and P.C.B.

Power: 20 W / I max. Frequency: 28kHz to 40kHz Time: 5 min max.

- (3) Cleaner
  - 1. Alcohol type cleaner Isopropyl alcohol (IPA)
  - 2. Aqueous agent PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning. In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.
- (5) Other cleaning Please contact us.

<u>Spec No.JELF243C-0009J-01</u> P.8/9

#### 11.8 Resin coating

Inductance value may be changed due to the large cure-stress of the resin when products are coated with resin. In this case, take care when you select resin to prevent the deterioration of the product quality.

#### 11.9 Caution for use


The pattern of the chip coil is covered with the protection film. But the handing the chip coil shall be taken care so that the chip coil would not be damaged with the pick-up nozzle, the sharp substance and so on.


#### 11.10 Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.

Bending Twisting





#### 11.11 Storage and Handing Requirements

(1) Storage period

Use the products within 12 months after delivered. Solderability should be checked if this period is exceeded.

#### (2) Storage conditions

• Products should be stored in the warehouse on the following conditions.

Temperature : -10°C ~ 40°C

Humidity : 15% to 85% relative humidity No rapid change on temperature and humidity.

- Products should not be stored on bulk packaging condition to prevent the chipping of the core and the breaking of winding wire caused by the collision between the products.
- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- (3) Handling Condition

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

## 12./\text{\lambda} Note


- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.

# Reference Only

Spec No.JELF243C-0009J-01 P.9/9

## -<Electrical Performance:Measuring Method of Inductance/Q>-

(1) Residual elements and stray elements of test fixture can be described by F-parameter shown in following.



(2) The impedance of chip coil Zx and measured value Zm can be described by input/output current/voltage.

$$Zm = \frac{V_1}{I_1}$$
 ,  $Zx = \frac{V_2}{I_2}$ 

(3) Thus, the relation between Zx and Zm is following;

$$Zx = \alpha \frac{Zm - \beta}{1 - Zm \Gamma} \qquad \text{where,} \quad \alpha = D / A = 1$$

$$\beta = B / D = Zsm - (1 - Yom Zsm)Zss$$

$$\Gamma = C / A = Yom$$

Zsm:measured impedance of short chip Zss:residual impedance of short chip (0.771nH) Yom:measured admittance when opening the fixture

(4) Lx and Qx shall be calculated with the following equation.

$$Lx = \frac{Im(Zx)}{2\pi f}, Qx = \frac{Im(Zx)}{Re(Zx)}$$

$$Lx : Inductance of chip coil Qx:Q of chip coil f:Measuring frequency$$