


SOLDER TERMINALS - SLOTTED

Dimensions in inches (mm)
See page 92/93 for recommended
Anvil and Punch



How to order code
1XX - XXXX - XX - XX - 00

Basic Part No. | Finish

Material Code Table		
Component	Material	RoHS
Terminal	Brass	✓
	Leaded Red Brass*	✓

Finish Code Table		
Dash No.	Finish	RoHS
-01	Silver	✓
-04	Electro-Tin	✓
-05	Electro-Solder	X

Fig.	Basic Part No.	L	Board Thickness	L1	A	B	C	D	D1	D2	D3	F	Mtg. Hole Diameter
1	140-2089 -11	.035 (0.89)	.016 (0.40)	-	.156 (3.96)	.068 (1.73)	.031 (0.79)	.062 (1.57)	.047 (1.19)	.026 (0.66)	.047 (1.19)	.025 (0.64)	.052 (1.32)
	-01	.051 (1.30)	.031 (0.79)										
	-02	.082 (2.08)	.062 (1.57)										
	-03	.113 (2.87)	.094 (2.39)										
	-04	.145 (3.68)	.125 (3.18)										
	140-1019 -11	.035 (0.89)	.016 (0.40)	-	.156 (3.96)	.068 (1.73)	.031 (0.79)	.072 (1.83)	.047 (1.19)	.026 (0.66)	.057 (1.45)	.028 (0.71)	.052 (1.32)
	-01	.051 (1.30)	.031 (0.79)										
	-02	.082 (2.08)	.062 (1.57)										
2	140-1018 -11	.035 (0.89)	.016 (0.40)	-	.094 (2.39)	.068 (1.73)	-	.072 (1.83)	.047 (1.19)	.026 (0.66)	-	.028 (0.71)	.052 (1.32)
	-01	.051 (1.30)	.031 (0.79)										
	-02	.082 (2.08)	.062 (1.57)										
	-03	.113 (2.87)	.094 (2.39)										
	-04	.145 (3.68)	.125 (3.18)										
	140-1785 -11	.025 (0.64)	.016 (0.40)	-	.156 (3.96)	.093 (2.36)	-	.094 (2.39)	.062 (1.57)	.043 (1.09)	-	.026 (0.66)	.067 (1.70)
	-01	.045 (1.14)	.031 (0.79)										
	-02	.094 (2.39)	.062 (1.57)										
3	140-1941 -11	.025 (0.64)	.016 (0.40)	-	.156 (3.96)	.094 (2.39)	-	.094 (2.39)	.071 (1.80)	.046 (1.17)	-	.029 (0.74)	.076 (1.93)
	-01	.045 (1.14)	.031 (0.79)										
	-02	.094 (2.39)	.062 (1.57)										
	-03	.125 (3.18)	.094 (2.39)										
	-04	.156 (3.96)	.125 (3.18)										
	140-1385 -11	.025 (0.64)	.016 (0.40)	.040 (1.02)	.156 (3.96)	.093 (2.36)	-	.094 (2.39)	.062 (1.57)	.043 (1.09)	-	.025 (0.64)	.067 (1.70)
	-01	.045 (1.14)	.031 (0.79)										
	-02	.094 (2.39)	.062 (1.57)	.062 (1.57)									
4	180-2752 -01	.062 (1.57)	.031 (0.79)	-	.188 (4.78)	.093 (2.36)	-	.125 (3.18)	.060 (1.52)	.042 (1.07)	-	.029 (0.74)	.064 (1.63)
	-02	.094 (2.39)	.062 (1.57)										
	-03	.125 (3.18)	.094 (2.39)										
	-04	.156 (3.96)	.125 (3.18)										
	180-7338 -01*	.062 (1.57)	.031 (0.79)	-	.173 (4.39)	.093 (2.36)	-	.094 (2.39)	.060 (1.52)	.042 (1.07)	-	.029 (0.74)	.064 (1.63)
	-02*	.094 (2.39)	.062 (1.57)										
	-03*	.125 (3.18)	.094 (2.39)										
	-04*	.156 (3.96)	.125 (3.18)										
5	180-2926 -01	.062 (1.57)	.031 (0.79)	.062 (1.57)	.188 (4.78)	.093 (2.36)	-	.125 (3.18)	.060 (1.52)	.042 (1.07)	-	.026 (0.66)	.064 (1.63)
	-02	.094 (2.39)	.062 (1.57)										
	-03	.125 (3.18)	.094 (2.39)										
	-04	.156 (3.96)	.125 (3.18)										
6	140-1028 -01	.063 (1.60)	.031 (0.79)	-	.188 (4.78)	.100 (2.54)	.035 (0.89)	.125 (3.18)	.071 (1.80)	.040 (1.02)	.071 (1.80)	.036 (0.91)	.076 (1.93)
	-02	.094 (2.39)	.062 (1.57)										
	-03	.125 (3.18)	.094 (2.39)										
	-04	.156 (3.96)	.125 (3.18)										
7	140-2187 -11	.030 (0.76)	.016 (0.40)	-	.080 (2.03)	.032 (0.81)	.021 (0.53)	.045 (1.14)	.032 (0.81)	-	-	.015 (0.38)	.036 (0.91)
	-01	.045 (1.14)	.031 (0.79)										
	-02	.077 (1.96)	.062 (1.57)										
	-03	.108 (2.74)	.094 (2.39)										
-04	.139 (3.53)	.125 (3.18)											