




Similar to picture



- Lead-acid Absorbed Glass Mat (AGM) battery module for uninterruptible power supply (UPS)
- Can be connected to both 787-870 UPS Charger and Controller and 787-1675 Power Supply with integrated UPS charger and controller
- Parallel operation provides higher buffer time *
- With built-in NTC K164 (4.7 kOhm) temperature sensor
- DIN 35 carrier rail mounting
- Battery control (from manufacturing no. 216570) detects both battery life and battery type

Technical Data

Input:	
Nominal input voltage V_i nom	24 V DC
Output:	
Nominal output voltage V_o nom	24 V DC
Output current I_o	max. 7.5 A
Final load voltage	max. 27 V DC (at 25 °C)
Charging current	max. 0.3 A
Capacity	1.2 Ah
Fuse protection:	
Internal fuse	15 AT (Type FK 2)

* for parallel connection, please switch battery capacity setting to "OFF" in the UPS charger and controller.

Description

Description	Item No.	Pack. Unit
Lead-acid Absorbed Glass Mat (AGM) battery module	787-876	1

Technical Data

Environmental requirements:	
Ambient operating temperature	-10 °C ... +40 °C
Storage temperature	-20 °C ... +40 °C
Service life	typ. 5/ 4/ 2 years at 20 °C/ 30 °C/ 40 °C
Safety and protection:	
Temperature sensor	NTC K164 (4.7 kΩ)
Protection class	III
Degree of protection	IP20 (acc. to EN 60529)
Connection and type of mounting:	
Wire connection	Input/Output: WAGO 231 Series Battery Control: WAGO 231 Series
Cross sections	Input/Output: 0.08 mm ² ... 2.5 mm ² / AWG 28 ... 12 Battery Control: 0.08 mm ² ... 2.5 mm ² / AWG 28 ... 12
Strip lengths	Input/Output: 8 ... 9 mm / 0.33 in Battery Control: 8 ... 9 mm / 0.33 in
Line length	≤ 3 m (Input, Output, Battery Control)
Type of mounting	DIN-rail mount (EN 60715)
Dimensions and weight:	
Dimensions (mm) W x H x L	55 x 153 x 136.5 Height, incl. female connector, Length from upper-edge of DIN 35 rail
Weight	1800 g
Standards and approvals:	
Standards/Specifications	Battery is tested to VdS, UL 508