

Model No.: OC16SC04-04

Rev: 1

Product Line: Tymphany


Last Update: 2017-04-25 14:32:09

Product Description

This OC family tweeter features a 16 mm 4 ohm voice coil, a damped fabric dome for smooth frequency response performance, and ferrofluid in the gap of the neodymium magnet motor, providing enhanced cooling of the voice coil. The tweeters butterfly comes with 2 mounting holes and with 2 pin terminals. The product is designed to fit snugly into small applications, while providing excellent dynamic sound quality.




Mechanical Drawing



Specifications

DC Resistance	Revc	Ohms	3.93	5.0%	Energy Bandwidth Product	EBP	(1/Qes)*fs
Minimum Impedance	Zmin	Ohms	4.18	7.5%	Moving Mass	Mms	g
Voice Coil Inductance	Le	mH	0.02		Suspension Compliance	Cms	um/N
Resonant Frequency	Fs	Hz	2152.63	15%	Effective Cone diameter	D	cm
Mechanical Q Factor	Qms		2.94		Effective Piston Area	Sd	cm^2
Electrical Q Factor	Qes		4.19		Effective Volume	Vas	L
Total Q Factor	Qts		1.73		Motor Force Factor	BL	Tm
Ratio Fs/Qts	F	Fs/Qts	1245.73		Motor Efficiency Factor	β	(T*M^2)/Ohms
Half Space Sensitivity @2.83V	db@2.83V/1M	dB	86.53	+/- 1.0db	Voice coil former Material	VCfm	
Half Space Sensitivity @1W/1M	db@1W/1M	dB	83.7	+/- 1.0db	Voice coil inner diameter	VCd	mm
Gap Height	Gh	mm	2		Rated Noise Power	P	W
Maximum Linear Excursion	Xmax	mm	0		Test Spectrum Bandwidth		2.5K-20K Hz
Ferrofluid Type	FF		APG Q27N		Driver Size		Inch
Driver Mass	Kg		0.02				16 mm

Frequency and Impedance Response



Highcharts.com