



ESD SAFE

DIMMABLE & BRIGHT LEDs

LARGE LENS WITH
SWING ARM INCLUDED

MODERN & ERGONOMIC DESIGN

Omega 7 ESD

MAGNIFYING LAMP

Our Omega 7 ESD Magnifier uses carbon-fibre and special conductive coatings to guarantee 100% ESD compliance for the lifetime of the magnifier. Large 17.5cm (7") diameter, 3 diopter (1.75X) optical quality glass lens provides the largest field of view to allow precise inspection. Supplied with 12 diopter (4.0X) swing arm lens for inspecting fine detail. An optional 12.7cm (5") diameter, 5 diopter (2.25X) lens is available separately.

5
great
reasons to use
Daylight
magnifiers



CONTRAST



BRIGHTER



SPREAD
OF LIGHT



ERGONOMICS



HEALTHY
VISION



MAGNIFICATION

+44 (0)20 8964 1200
www.daylightcompany.com




daylight
when light matters

D/E25171

Omega 7 ESD Magnifier

- ★ Ergonomic and professional ESD safe magnifying lamp
- ★ Swing Arm ESD Safe 12D (4.0X) lens included
- ★ 60 daylight premium LEDs with 2 brightness levels
- ★ Large 17.5cm (7") 3D (1.75X) optical quality glass lens with anti-static coating included
- ★ Suitable for use in EPA, (Electrostatic Protected Areas) To IEC 61340-5-1 and ANSI/ESD 20:20
- ★ Unique quick change lens mechanism - no tools required
- ★ Heavy duty arm with reinforced joints



Available Accessories



Product Information

Width	23cm (9.1")
Height	60cm (23.6")
Depth	90cm (35.4")
Weight	3.7kg (8.2lb)
Colour	Black
Reach	118.1cm (46.5")
Cable Length	2.6m (102.4")
Lens Size	17.5cm (7")
Magnification	3D (1.75X) & 12D (4.0X)
Extra Magnification available separately	5D (2.25X) (D65171A)
Lens Material	Optical Quality Glass

Light Output

Light Source	LED
Lumens	814lm
Lux	6,300 Lux at 15cm (6")
Colour Temperature	6,000°K
Power Consumption	12W

Packaging Information

Width	52cm (20.5")
Height	60cm (23.6")
Depth	10cm (3.9")
Packed Weight per unit	5kg (11lb)
Products per Master Carton	2

+44 (0)20 8964 1200
www.daylightcompany.com

