

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

1.9kW Single-Phase Switched PDU, 120V Outlets (16 5-15/20R), L5-20P/5-20P input, 12ft Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20NET





Description

Tripp Lite single phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface.

Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is continuously displayed locally via visual meter and remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

Features

- 20A 120V Switched Power Distribution Unit / PDU with built-in web/network interface (Agency derated to 16A continuous)
- Attached NEMA L5-20P input with NEMA 5-20P plug adapter, 12 ft. / 3.6m input cable
- 1U horizontal rackmount form factor
- 16 switched NEMA 5-15/20R outlets (8 front / 8 rear)
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and total output load level in amps
- Digital display continuously reports total output load level in amps
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing

1/4

Highlights

- Switched 20A 120V PDU, 1U horizontal rackmount format
- Reports voltage, frequency & load level via ethernet interface
- Visual current meter, Reversible housing
- NEMA L5-20P input with 5-20P plug adapter, 12 ft. / 3.6m line cord
- 16 NEMA 5-15/20R switched outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options
- TAA Compliant

Package Includes

- PDU with attached L5-20P input power cord
- 5-20P plug adapter
- Installable 1U mounting brackets
- PowerAlert software
- User manual



- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

Specifications

OVERVIEW		
PDU Type	Switched	
OUTPUT		
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 20A total capacity (Agency de-rated to 16A); 16A max per outlet	
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(16) 5-15/20R	
Output Nominal Voltage	100; 120; 127	
Overload Protection	n/a	
Customized Load Management Receptacles	16 individually switched output receptacles	
INPUT		
PDU Input Voltage	100; 120; 127	
Recommended Electrical Service	20A 120V	
Maximum Input Amps	20	
Maximum Input Amps Details	Agency de-rated to 16A continuous	
PDU Plug Type	NEMA 5-20P; NEMA L5-20P	
Input Cord Length (ft.)	12	
Input Cord Length (m)	3.66	
Input Phase	Single-Phase	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Digital display reports total PDU output current in amps	
Front Panel LEDs	16 LEDs display power on-off status for each output receptacle	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Switches	n/a
PHYSICAL	
Minimum Required Rack Depth (inches)	20.5
Minimum Required Rack Depth (cm)	52.1
Shipping Dimensions (hwd / in.)	5.4 x 20.6 x 23.3
Shipping Dimensions (hwd / cm)	13.7 x 52.3 x 59.2
Shipping Weight (lbs.)	16.7
Shipping Weight (kg)	7.6
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 15.5
Unit Dimensions (hwd / cm)	4.44 x 44.4 x 39.4
Unit Weight (Ibs.)	12.5
Unit Weight (kg)	5.7
Material of Construction	Metal
Form Factors Supported	1U rackmount
PDU Form Factor	1U; Horizontal
ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
COMMUNICATIONS	
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via web, telnet, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
SPECIAL FEATURES	
TVSS Grounding	Grounding lug
CERTIFICATIONS	
Certifications	Tested to UL 60950-1 (USA), CSA (Canada), Class A (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant
WARRANTY	



Product Warranty Period (Worldwide) 2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies