



OPTIONS



VERSIONS

Type	Force N	Feed mm/s	Pitch of screw mm	Resolution $\mu\text{m}/\text{step}$	Current per Winding A	Resistance per Winding Ohm	Inductance per Winding mH	Weight kg	Bushing Length „L“ mm	Length „A“ mm
L2818S0604-T5X5	30	100	5	25	0.67	5.6	4	0.11	20	31.5
L2818L0604-T5X2	115	20	2	10	0.67	9.2	7.2	0.19	20	50.5
L2818L0604-T5X5	60	140	5	25	0.67	9.2	7.2	0.19	20	50.5

ORDER IDENTIFIER



L2818S0604-T5X5

ACCESSORIES




- ZST5-2-200-1** Threaded Screw
- ZST5-2-300-1** Threaded Screw
- ZST5-2-1000** Threaded Screw
- ZST5-5-200-1** Threaded Screw
- ZST5-5-300-1** Threaded Screw
- ZST5-5-1050** Threaded Screw
- Nanolube** Lubricant

CAUTION



The force and power ratings specified in the data sheets are based on a duty cycle of 10% to 20% and must be reduced for higher values. Moving against fixed end stops should be avoided.

DIMENSIONS (IN MM)



TORQUE CURVES

