

RF Attenuator 6620_SMA-50-1/199_N

Description

Standard Attenuator, Low Power



Product Configuration

Connector (side 1 / side 2) SMA plug (male) / SMA jack (female)
 Interface Standards IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Nominal impedance	50 Ω			
Nominal attenuation	20 dB			
Frequency range	DC to 18 GHz			
Frequency sub range (GHz)	DC to 4	4 to 8	8 to 12.4	12.4 to 18
Attenuation deviation (±dB)	0.5	0.5	0.5	0.5
VSWR max.	1.15	1.2	1.25	1.35
Power rating	2 Watt average power up to 25 °C ambient temperature, linearly derated to 0.5 Watt at 125 °C ambient temperature. 250 Watt peak power, 5 μs pulse, 0.05 % duty cycle			

Mechanical Data

Weight 0.004 kg

Environmental Data

Operating temperature -65 °C to 125 °C
 2011/65/EU (RoHS) compliant

Material Data

Piece Part (side 1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	Passivated (Plating)
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing DOU-00089026

Ordering Information

Single packaging 6620_SMA-50-1/199_NE