



PRODUCT SPECIFICATION

TITLE

2.4/5GHz BALANCE FLEX ANTENNA

TABLE OF CONTENTS

- 1.0 SCOPE
- 2.0 PRODUCT DESCRIPTION
- 3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS
- 4.0 RATINGS
- 5.0 PERFORMANCE
- 6.0 TEST GROUPINGS
- 7.0 PACKING

REVISION: D1	ECR/ECN INFORMATION: EC No: 169066 DATE: 2017/12/07	TITLE: 2.4/5GHz BALANCE FLEX ANTENNA	SHEET No. 1 of 8
DOCUMENT NUMBER: PS-146153-100	CREATED / REVISED BY: Kang Cheng 2017/12/07	CHECKED BY: Colin Xu 2017/12/07	APPROVED BY: Stary Song 2017/12/07



PRODUCT SPECIFICATION

2.4/5GHz Balance Flex Antenna

1.0 SCOPE

This Product Specification covers the mechanical, electrical and environmental performances requirements and test methods for 2.4/5GHz Balance Flex Antenna with solder cable.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBER (S)

Product name: 2.4/5 GHz Balance Flex Antenna 146153

2.2 Design and Construction

Antenna construction and physical dimensions specified on the applicable sales drawing.

2.3 Materials

- a) Flex: Refer to sales drawings SD of 1461530100 and 1461531100.
- b) Cable Line: Refer to sales drawings SD of 1461530100 and 1461531100.
- c) Connector: Refer to sales drawings SD of 1461530100 and 1461531100.

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

See drawings and other sections of this specification for the relevant reference documents. In cases where the specification differs from the drawings, the drawings take precedence.

4.0 RATINGS

4.1 RF POWER

2 WATTS MAX

4.2 TEMPERATURE

Operating: - 30°C to 85°C
 Storage : - 40°C to 95°C

4.3 HUMIDITY

Operating : -30°C to 85°C
 -30°C to 50°C, 85%RH or less
 50°C to 85°C, 60%RH or less

Storage : -40°C to 95°C
 -40°C to 50°C, 85%RH or less
 50°C to 95°C, 60%RH or less

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	2 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Stary Song 2017/12/07



PRODUCT SPECIFICATION

5.0 PERFORMANCE

5.1 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 50mm (1461530050 and 1461531050)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENTS	
5.1.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.1.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.1.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	3.2 dBi	4.25 dBi
5.1.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>78%	>79%
5.1.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.1.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

5.2 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 100mm (1461530100 and 1461531100)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT	
5.2.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.2.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.2.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	3.0 dBi	4.0 dBi
5.2.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>75%	>75%
5.2.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.2.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	3 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Stary Song 2017/12/07



PRODUCT SPECIFICATION

5.3 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 150mm (1461530150 and 1461531150)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT	
5.3.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.3.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.3.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	2.8 dBi	3.7 dBi
5.3.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>72%	>70%
5.3.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.3.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

5.4 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 200mm (1461530200 and 1461531200)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT	
5.4.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.4.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.4.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	2.6 dBi	3.5 dBi
5.4.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>69%	>66%
5.4.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.4.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	4 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Sary Song 2017/12/07



PRODUCT SPECIFICATION

5.5 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 250mm (1461530250 and 1461531250)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT	
5.5.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.5.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.5.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	2.4 dBi	3.2 dBi
5.5.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>66%	>63%
5.5.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.5.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

5.6 ELECTRICAL REQUIREMENTS FOR CABLE LENGTH 300mm (1461530300 and 1461531300)

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT	
5.6.1	Frequency Range	2.4GHz~5.85GHz	2.4GHz~2.5GHz	4.9GHz~5.85GHz
5.6.2	Return Loss	Antenna loaded on PC/ABS housing with 100mm long, 1.13mm diameter micro coaxial cable. Measured by VNA5071C	< -10 dB	
5.6.3	Peak Gain	Measure antenna on recommended PC/ABS housing through OTA chamber	2.2 dBi	2.8 dBi
5.6.4	Total Efficiency	Measure antenna on recommended PC/ABS housing through OTA chamber	>63%	>59%
5.6.5	Polarization	Measure antenna through the OTA chamber	Linear	
5.6.6	Input Impedance	Measure antenna on recommended PC/ABS housing through VNA E5071C	50 Ohms	

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	5 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Sary Song 2017/12/07



PRODUCT SPECIFICATION

5.7 CABLE LOSS

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENTS	
5.7.1	Frequency Range	2GHz~6GHz	2GHz~3GHz	5GHz~6GHz
5.7.2	Attenuation	1m cable measured by VNA5071C	≤3.5dB/m	≤5dB/m

5.8 CABLE LENGTH AFFECT THE ANTENNA PERFORMANCE

Balance antenna resonance is insensitive by cable's length, but the cable's loss will affect the totally efficiency. Refer to 5.7

5.9 MECHANICAL REQUIREMENTS

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT
5.9.1	Pull test	Test machine : Max intelligent load tester Stick the Flex antenna in a PC block, pull cable in horizontal direction	Pull force > 8N

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	6 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Stary Song 2017/12/07



PRODUCT SPECIFICATION

5.10 ENVIRONMENTAL REQUIREMENTS

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT
5.10.1	Temperature /Humidity cycling	Test condition: 1) The device under test is kept for 30 mins in an environment with a temperature of -40 °C. 2) Kept for 4 Hours in an environment with a temperature of 85 degrees and a relative humidity of 95%. 3) Kept for 2 Hours in an environment with a temperature of 125 degrees and a relative humidity of 95%. 4) The cycle is repeated until a total of 40 cycles have been completed. Hereafter the conditions are stabilized at room temperature.	1) Parts should meet RF spec before and after test. 2) No cosmetic problem
5.10.2	Temperature Shock	Test condition: The device under test at -40 °C ⇔ 125 °C by 100 cycles, Dwell of 30 mins, transition time between Dwell 30 secs (~ 61 mins / cycle) and each item should be measured after exposing them in normal temperature and humidity for 24 h.	1) Parts should meet RF spec before and after test. 2) No cosmetic problem
5.10.3	High Temperature	Test condition: 1) Temperature: 125°C , time: 1008 hours 2) There is no substantial obstruction to air flow across and around the samples, and the samples are not touching each other	1) Parts should meet RF spec before and after test. 2) No cosmetic problem
5.10.4	Salt mist test	1. Test condition: The device under test is exposed to a spray of a 5% (by volume) resolution of NaCl in water for 2 hours. Thereafter the device under test is left for 1 week in room temperature at a relative humidity of 95%. The cycle is repeated until a total of 2 cycles have been completed. Here after the conditions are stabilized at room temperature.	1) Parts should meet RF spec before and after test. 2) No visible corrosion. Discoloration accept.

The meaning of text “**No Cosmetic Problem**” in the table above is:

- a. No soldering problem
- b. No adhesion problem of glue

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
D1	EC No: 169066 DATE: 2017/12/07	2.4/5GHz BALANCE FLEX ANTENNA	7 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-146153-100	Kang Cheng 2017/12/07	Colin Xu 2017/12/07	Stary Song 2017/12/07



PRODUCT SPECIFICATION

6.0 TEST GROUPINGS

Test Item	Description	Group1	Group2	Group3	Group4	Group5
5.9.1	Pull test	X				
5.10.1	Temperature /Humidity cycling		X			
5.10.2	Temperature Shock			X		
5.10.3	High Temperature				X	
5.10.4	Salt mist test					X
Sample Quantity		5	5	5	5	5

7.0 PACKAGING

Refer to the Molex related packaging drawings of 1461530100.

REVISION: D1	ECR/ECN INFORMATION: EC No: 169066 DATE: 2017/12/07	TITLE: 2.4/5GHz BALANCE FLEX ANTENNA	SHEET No. 8 of 8
DOCUMENT NUMBER: PS-146153-100	CREATED / REVISED BY: Kang Cheng 2017/12/07	CHECKED BY: Colin Xu 2017/12/07	APPROVED BY: Stary Song 2017/12/07