



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay to be ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O

Complementary

[Ie] rated operational current	50 A AC-3
Motor power kW	15 kW at 220/230 V AC 50/60 Hz 22 kW at 380/400 V AC 50/60 Hz 25 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz 30 kW at 500 V AC 50/60 Hz 33 kW at 660/690 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	50 A
[Uc] control circuit voltage	380 V AC 50/60 Hz
Cable entry number	1 cable entry : ISO32 top 3 cable entry : 1 ISO20 + 2 ISO32 bottom
Width	200 mm
Height	300 mm
Depth	158.4 mm
Product weight	4.85 kg
Compatibility code	LE1D

Environment

Material	Sheet steel
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0801 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual