



Part Number: 9536

RS-232, #24-6c, SR-PVC, O/A Foil, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
24	7x32	TC - Tinned Copper	6

Conductor Count:	6
AWG Size:	24

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.01 in

Color Chart

Number	Color
1	Black
2	White
3	Red
4	Green
5	Brown
6	Blue

Outer Shield Material

Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.209 in	0.032 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
25 Ohm/1000ft	18 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
33 pF/ft	65 pF/ft	12.8 pF/m

High Frequency (Nominal/Typical)

Nom. Insertion Loss
12.7 dB/100m

Current

Max. Recommended Current [A]

1.75 Amps per conductor @ 25°C A

Current Table Note: 10C Temperature Rise

Voltage

UL Voltage Rating

300V RMS

Temperature Range

UL Temp Rating: 80°C (UL AWM Style 2464)

Operating Temp Range: -30°C To +80°C

Mechanical Characteristics

Bulk Cable Weight: 24 lbs/1000ft

Max Recommended Pulling Tension: 33 lbs

Min Bend Radius/Minor Axis: 2.25 in

Standards

NEC Articles: 800

NEC/(UL) Specification: CMG

CEC/C(UL) Specification: CMG

UL AWM Style: 2464 (300 V 80°C)

CPR Euroclass: Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2005-04-01

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Suitability

Suitability - Indoor: Yes

Flammability, LSOH, Toxicity Testing

UL Flammability: UL1685 FT4 Loading

CSA Flammability: FT4

Part Number

Plenum (Y/N): No

Variants

Item #	Color	Footnote
9536.001525	Chrome	
9536.0030	Chrome	
9536.00U152	Chrome	
9536.00U305	Chrome	
9536.01152	Chrome	
9536.01305	Chrome	
9536 060100	Chrome	
9536 0601000	Chrome	C
9536 060500	Chrome	C
9536 0605000	Chrome	
9536 060U1000	Chrome	
9536 060U500	Chrome	

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.