RS-232 ⇔ RS-422 Interface Converter

Provides Transient Protection






Description

The ASeries A440 allows any RS-232 serial device to communicate with any RS-422 serial device. As well as transferring data the A440 provides one pair of handshaking lines, i.e. DTR/DSR or CTS/RTS for the control of the data flow.


Simple to use and cost effective, the A440 has been engineered for use in both industrial and commercial environments.

Applications

Connect any incompatible devices using the A440 interface converter.



Use two A440 converters to connect RS-232 devices over a long distance.



Features

- Bidirectional RS-232 <> RS-422 interface conversion in asynchronous mode
- Transient Protection on RS-422 lines
- Supports Xon/Xoff Software Handshaking
- Supports DTR/DSR or CTS/RTS Handshaking
- Transmits data reliably at up to 64Kbps
- Switch selectable RS-422 termination resistors for cable distances exceeding 50 metres
- Switchable DCE/DTE selection for RS-232 port
- LED indicators for data activity
- Nickel plated metal case will withstand rugged applications
- Very LOW COST Very BIG FEATURES

Specifications - ASeries A440

RS-232 Port: Asynchronous RS-232

DB-25 female connector Switch Selectable DCE/DTE Transfer up to 64Kbps

RS-422 Port: DB-25 female connector

120 $\!\Omega$ termination resistor selection for handshaking lines 'RD' & 'DSR'

Protection: Transient Voltage Supression Diodes

RS-422 - Transmit Data Lines - Receive Data Lines - DTR & DSR handshake lines

LED Indicators: Receive Data RS-232

Receive Data 20mA Current Loop

Power On

Power Supply: 9V (200mA) DC

Reverse Polarity Protection

Dimensions: 84m x 58mm x 23mm

Weight: 160 grams

All Specifications subject to change without notice



Alfatron Pty Ltd ACN 005 410 819 PO Box 4161 Unit 9, 36 New St. Ringwood VIC 3134 AUSTRALIA

Tel: +61-3-9876 9011 Fax: +61-3-9876 9044 Email: sales@alfatron.com.au Web Site: www.alfatron.com.au

