

# RAYNGER ST SERIES

The Raynger ST Series of handheld, noncontact thermometers uses infrared technology to measure the temperature of materials up close, or from a distance. You simply aim, pull the trigger, and read the temperature on a large, backlit LCD display. Lightweight, compact, and easy-to-use, the Raynger ST can safely measure hot, hazardous, or hard-to-reach materials without contaminating or damaging the material's surface. For safe and accurate temperature measurement, reach for a Raytek.

## **Choice of models**

- The Raynger ST2 allows you to simultaneously read current and maximum temperatures. It includes 0.95 fixed emissivity and 8:1 optics.
- *The ST3 is the lowest-priced noncontact thermometer with laser sighting on the market today.* It offers the same reliable features as the ST2, in addition to laser sighting.
- The Raynger ST6 lets you view maximum, minimum, average, and differential, as well as current readings. In addition you can set HI/LO alarms, recall last reading, and adjust emissivity.
- The Raynger ST8 is the full-featured model with an extended temperature range and 30:1 optics. The expanded optics allows you to increase your distance from the target and measure a smaller spot size.

## **Applications**

- **AUTOMOTIVE**—Troubleshoot engines, including ignition system problems and fuel/air adjustments. Diagnose cooling systems, including thermostats and coolant sensors; radiators; catalytic converters; brakes, and tires. Perform climate control maintenance with precision.
- **HVAC**—Balance room temperatures, monitor supply/return registers, and test duct work; examine steam traps and check furnace performance; perform energy audits.
- **FOOD SAFETY**—Perform HACCP temperature measurements at receiving. Check cold and hot cooking, holding, and serving temperatures, and ensure safe and uniform storage and transportation temperatures. Maintain freezers, walk-ins, ovens, ranges, and dishwashers. Food inspectors can quickly confirm application temperatures.
- **INDUSTRIAL/ELECTRICAL**—Detect and troubleshoot facility electrical and process maintenance problems...before they happen, including vehicle and fleet maintenance. Check electrical panels for hot spots, find defective transformers, and detect loose electrical connections.
- **AND MORE**—Roofing, asphalt, and concrete applications; commercial printing; plastics molding; fire detection/prevention; race car, aviation, and marine maintenance.

# RAYTEK PORTABLE NONCONTACT THERMOMETERS

## FEATURES

Models	ST2	ST3	ST6	ST8
Emissivity	Pre-set to 0.95		adjustable 0.3 to 1.0	
Laser (Class II)*		✓	✓	✓
MAX, MIN, DIF and AVG temperature	MAX only	MAX only	✓	✓
Recall last reading			✓	✓
Display hold (7 seconds)	✓	✓	✓	✓
HI/LO audible and visible alarms			✓	✓
LCD backlight	✓	✓	✓	✓
Temperature display	10th degree to 199°, °C or °F selectable			
D:S (distance to spot size) (90% energy)	8:1	8:1	8:1	30:1
Hard carrying case		✓	✓	✓

\* Laser is offset 1.2 cm above center of target spot.

## SPECIFICATIONS

Temperature Range	
ST2/ST3	-32 to 400°C (-25 to 750°F)
ST6	-32 to 500°C (-25 to 932°F)
ST8	-32 to 540°C (-25 to 1000°C)
Accuracy	±1% of reading or ±1°C (±2°F), whichever is greater @ 23°C (73°F) ambient operating temperature
	-18 to 25°C (0 to 77°F) ±2°C (±3°F)
	-26 to -18°C (-15 to 0°F) ±2.5°C (±4°F)
	-32 to -26°C (-25 to -15°F) ±3°C (±5°F)
Repeatability	±1% of reading or ±1°C (±2°F), whichever is greater
Response Time	500 mSec, 95% response
Ambient Operating Range	0 to 50°C (32 to 120°F)
Power	9V Alkaline or NiCad battery
Dimensions	137 x 41 x 196 mm (5.4 x 1.6 x 7.7 in)
Weight	270 g (9.5 oz)

Specifications subject to change without notice.

## OPTIONS / ACCESSORIES

- Soft Pouch with Belt Clip and Wrist Strap
- Hard Case with Belt Clip (standard with ST3, ST6, ST8)
- NIST/DKD Certification



Specifications subject to change without notice © 1998 Raytek Corporation ST0598

### WORLDWIDE HEADQUARTERS

Raytek Corporation  
1201 Shaffer Road, PO Box 1820  
Santa Cruz, CA 95061-1820 USA

Portable Products Division  
**800 866 5478**

Phone 408 458 1110  
Fax 408 425 4561

### WORLD WIDE WEB

www.raytek.com

### JAPAN

Raytek Japan, Inc.  
Tokyo, Japan  
Phone 81 3 3822 5715  
Fax 81 3 3822 5712

### EUROPEAN HEADQUARTERS

Raytek GmbH  
Berlin, Germany  
Phone 49 30 478 0080  
Fax 49 30 471 0251

### CHINA

Raytek China Company  
Beijing, China  
Phone 86 10 6437 0284  
Fax 86 10 6437 0285

### FRANCE

Raytek France  
Palaiseau, France  
Phone 33 1 64 53 15 40  
Fax 33 1 64 53 15 44

### SOUTH AMERICAN HEADQUARTERS

Raytek do Brasil  
Sorocaba, Brasil  
Phone 55 15 233 6338  
Fax 55 15 233 6826



### MEXICO

Raytek de Mexico  
Puebla, Mexico  
Phone 52 22 30 4380  
Fax 52 22 30 4438


### UNITED KINGDOM

Raytek UK  
Milton Keynes, UK  
Phone 44 1908 630800  
Fax 44 1908 630900


### DISTRIBUTED BY:



### ST2, ST3, ST6 Target Spot Sizes



### ST8 Target Spot Sizes



**Raytek®**