## Product data sheet Characteristics

# XB5AG33 SELECTOR SWITCH 230VAC 2AMP XB5 +OPTIONS



#### Main

Range of product	Harmony XB5
Product or component type	Complete selector switch
Device short name	XB5
Bezel material	Plastic
Mounting diameter	22 mm
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Stay put
Operator profile	Key switch
Operator position information	3 positions +/- 45°
Type of keylock	Ronis 455
Contacts type and composition	2 NO
Contact operation	Slow-break
Connections - terminals	Screw clamp terminals : <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals : >= 1 x 0.22 mm² without cable end conforming to EN/IEC 60947-1

### Complementary

Main	
Range of product	Harmony XB5
Product or component type	Complete selector switch
Device short name	XB5
Bezel material	Plastic
Mounting diameter	22 mm
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Stay put
Operator profile	Key switch
Operator position information	3 positions +/- 45°
Type of keylock	Ronis 455
Contacts type and composition	2 NO
Contact operation	Slow-break
Connections - terminals	Screw clamp terminals : $<= 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN/IEC 60947-1 Screw clamp terminals : $>= 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN/IEC 60947-1
Complementary	
Height	42 mm
Width	30 mm
Depth	96 mm
Terminals description ISO n°1	(13-14)NO
Product weight	0.831 kg
Resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m
Key withdrawal position	Center
Contacts usage	Standard contacts
Positive opening	Without positive opening
Torque value	0.14 N.m NO changing electrical state

Mechanical durability	1000000 cycles				
Tightening torque	0.81.2 N.m conforming to EN 60947-1				
Shape of screw head	Cross head compatible with Philips no 1 screwdriver Cross head compatible with pozidriv No 1 screwdriver Slotted head compatible with flat Ø 4 mm screwdriver Slotted head compatible with flat Ø 5.5 mm screwdriver				
Contacts material	Silver alloy (Ag/Ni)				
Short-circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1				
[lth] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1				
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN 60947-1				
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-1				
[le] rated operational current	1.2 A 600 V AC-15 A600 EN/IEC 60947-5-1 0.27 A 250 V DC-13 Q600 EN/IEC 60947-5-1 0.1 A 600 V DC-13 Q600 EN/IEC 60947-5-1 3 A 240 V AC-15 A600 EN/IEC 60947-5-1 0.55 A 125 V DC-13 Q600 EN/IEC 60947-5-1 6 A 120 V AC-15 A600 EN/IEC 60947-5-1				
Electrical durability	1000000 cycles, AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C				
Electrical reliability	$\Lambda$ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4 $\Lambda$ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4				


## Environment

Protective treatment	TH
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
Electrical shock protection class	Class II conforming to IEC 60536
IP degree of protection	IP69 IP67 IP66 conforming to IEC 60529 IP69K
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK06 conforming to IEC 50102
Standards	EN/IEC 60947-5-4 EN/IEC 60947-1 EN/IEC 60947-5-1 JIS C 4520 CSA C22.2 No 14 UL 508
Product certifications	LROS (Lloyds register of shipping) GL BV UL DNV RINA CSA
Vibration resistance	5 gn (f = 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

## Contractual warranty

	Warranty period	18 months			
--	-----------------	-----------	--	--	--


### **Dimensions**



e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

### Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


#### Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. Ø22.5 mm recommended (Ø22.3  $_0^{+0.4}$ ) / Ø0.89 in. recommended (Ø0.88 in.  $_0^{+0.016}$ )
- (2) (3)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

## **Detail of Lug Recess**



- Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  $\emptyset$ 22.5 mm recommended ( $\emptyset$ 22.3  $_0$   $^{+0.4}$ ) /  $\emptyset$ 0.89 in. recommended ( $\emptyset$ 0.88 in.  $_0$   $^{+0.016}$ )
- (1) (2) (3)