




DESIGN KIT

WCAP-CSSA

Safety MLCC X1/Y2, X2/Y3, 250V AC



Size:

1808 / 1812 / 2211

Technical Data:

Capacitance Range: 33 ~ 2,200pF

Rated Voltage: 250V AC

Dielctrics: NPO, X7R

Safety Classes: X1/Y2, X2/Y3

Approvals:


TUV, cULus

Order Code 885 300

Version 1.0

WCAP-CSSA

Safety MLCC X1/Y2, X2/Y3, 250V AC



1808	885 352 010 007 X1 / Y2 33pF; ±5%; H=1.4mm DF≤0.1%; IR≥100GΩ	885 362 010 009 X2 / Y3 33pF; ±5%; H=1.4mm DF≤0.1%; IR≥100GΩ	1808	885 362 010 011 X2 / Y3 47pF; ±5%; H=1.6mm DF≤0.1%; IR≥100GΩ	885 362 010 017 X2 / Y3 100pF; ±5%; H=2mm DF≤0.1%; IR≥100GΩ	885 362 210 009 X2 / Y3 470pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ	885 362 210 013 X2 / Y3 680pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ
	885 352 010 007 X1 / Y2 33pF; ±5%; H=1.4mm DF≤0.1%; IR≥100GΩ	885 362 010 009 X2 / Y3 33pF; ±5%; H=1.4mm DF≤0.1%; IR≥100GΩ		885 362 010 011 X2 / Y3 47pF; ±5%; H=1.6mm DF≤0.1%; IR≥100GΩ	885 362 010 017 X2 / Y3 100pF; ±5%; H=2mm DF≤0.1%; IR≥100GΩ	885 362 210 009 X2 / Y3 470pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ	885 362 210 013 X2 / Y3 680pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ
	885 352 210 013 X1 / Y2 1000pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ	885 362 210 017 X2 / Y3 1000pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ		885 352 211 001 X1 / Y2 470pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ	885 352 211 002 X1 / Y2 680pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ	885 352 211 003 X1 / Y2 1000pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 362 211 011 X2 / Y3 1000pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ
	885 352 210 013 X1 / Y2 1000pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ	885 362 210 017 X2 / Y3 1000pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ		885 352 211 001 X1 / Y2 470pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ	885 352 211 002 X1 / Y2 680pF; ±10%; H=2mm DF≤2.5%; IR≥10GΩ	885 352 211 003 X1 / Y2 1000pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 362 211 011 X2 / Y3 1000pF; ±10%; H=1.6mm DF≤2.5%; IR≥10GΩ
	885 362 211 015 X2 / Y3 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 362 211 015 X2 / Y3 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ		885 352 213 011 X1 / Y2 1000pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 352 213 015 X1 / Y2 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ		
	885 362 211 015 X2 / Y3 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 362 211 015 X2 / Y3 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ		885 352 213 011 X1 / Y2 1000pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ	885 352 213 015 X1 / Y2 2200pF; ±10%; H=2.5mm DF≤2.5%; IR≥10GΩ		
Safety Class	Impulse Voltage						
X1 / Y2	5000V						
X2 / Y3	2500V						
Dielectric	Capacitance Characteristics*						
NP0	± 30ppm/°C; ±0.54%/°C						
X7R	± 15%						

*within Operating Temperature Range

Approvals:

TUV (EN 60384 -14:2005), File number: R 50268363
cULus, File numbers: E345659, E331896

Technical Data:

Rated Voltage: 250V AC
Operating Temperature: -55°C to +125°C
Termination: Ag/Ni/Sn



Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications.
Würth Elektronik eSOS GmbH & Co. KG, EMC & Inductive Solutions. © 2015

**All products
ex stock!**