



MPN	Description
RAFGBI2-S6-M20	Cable Tie Mounts



The right angle base in black accepts a flat cable width of 2.0" (50.8 mm) and is made of nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. It is designed for indoor environments.

Specifications

Mount Method	#6 (M3) Screw
Overall Length (In.)	NA
Overall Length (mm)	NA
Color	Black
Overall Width (In.)	0.63
Overall Width (mm)	16

Overall Height (In.)	2.78
Overall Height (mm)	70.6
Open Length (mm)	NA
Static Load Capacity (Kg)	NA
Compatible Screw Size (In.)	NA
Compatible Screw Size (mm)	NA
Environment	Indoor
Flammability Rating	UL94V-2
Material	Nylon 6.6
CE Compliant	Yes
CE Marking	Yes
UL Recognized	E136577
UL Recognized (File #E136577)	Yes

Max. Flat Cable Width (In.)	2.00
Max. Flat Cable Width (mm)	50.8
Hole Diameter (mm)	3.7
Screw Size	#6 (M3)
Screw Size Metric	M3
Length (In.)	2.78
Length (mm)	70.6
Compatible Cable Tie	I
Max. Continuous Use Temperature	-40 °F - 185 °F (-40 °C - 85 °C)
Type	Right Angle Bases
RoHS Compliancy Status	Compliant